## 4Z057Y-000 | F0SC400-D5/FR-36-2-NGV-A



FOSC® 400 D5 Fire Retardant Fiber Optic Splice Closure, Heat Shrink Cable sealing, two pre-installed 36-splice trays, with test valve

- Single-ended, O-ring sealed dome closure for splicing feeder and distribution cables
- Compatible with most common cable types: e.g. loose tube, central core, ribbon fiber
- FOSC splice trays hinged for access to any splice without disturbing other trays
- Closure can be used in aerial, pedestal and underground (up to 5 meters) environments
- Compatible with CommScope's CWDM modules and optical splitter trays

#### **Product Classification**

Regional Availability

Latin America | North America

**Product Type** Single-ended, round fiber closure

Product Brand FOSC®

Product Series FOSC 400

### General Specifications

 Cable Blocking Components
 None

 Cable Entry Drop Port Style
 Round

 Cable Entry Main Port Style
 Oval

Cable Ports Quantity, total1 oval port (2 cables) + 5 round ports

Cable Sealing Type Heat shrink

Closure Sealing Type Dome-to-base clamp with 0-ring

Closure Style Single-ended

**Color** Black

Flash Test Valve Pre-installed

Ground Feed-through Included

Mounting Pole | Strand | Wall

Network Area Type Feeder

Splice Tray Included, quantity 2

Splice Tray Type Included 36-way, heat shrink

Splicing Capacity, Mass Fusion, maximum1152Splicing Capacity, Single Fusion, maximum576Splicing Capacity, Single Splice, 12 fibers, maximum576

Page 1 of 3



# 4Z057Y-000 | FOSC400-D5/FR-36-2-NGV-A

Splicing Capacity, Single Splice, 6 fibers, maximum

288

**Splicing Type, Supported** 

Single fusion

**Dimensions** 


**Length** 710 mm | 27.953 in

**Diameter** 240 mm | 9.449 in

Diameter, with clamp 260 mm | 10.236 in

Main Cable Diameter, maximum 25 mm | 0.984 in


### Dimension Drawing



Ordering Tree



## 4Z057Y-000 | F0SC400-D5/FR-36-2-NGV-A



\*Note: SMOUV (1120-01-US) splice protection sleeves should be used with SM12 splice modules.

### Material Specifications

Material Type Impact-resistant polymer

#### **Environmental Specifications**

Environmental Space Below ground | Buried

**Qualification Standards** IEC 61300, 6 m waterhead

Water Resistance Flash test valve at 5 psi (40 kPa)

#### Packaging and Weights

Packaging quantity

Packaging TypeBox| CartonWeight, net6 kg | 13.228 lb

### Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

**COMMSCOPE®**