

# 760236119 | DM12iP-24LC-WB-ULL

G2 ULL Multimode OM5 MPO-12 Distribution Module, 2x12F MPO unpinned to 24F LC Lime Green, Method B Enhanced, iPatch Ready



## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber module
<b>Product Brand</b>	SYSTIMAX ULL

## General Specifications

<b>Functionality</b>	Breakout
<b>Adapters, quantity, front</b>	12
<b>Adapters, quantity, rear</b>	2
<b>Color, front</b>	Lime green
<b>Color, rear</b>	Lime green
<b>Data Module Type</b>	G2
<b>Intelligence Type</b>	iPatch® ready
<b>Interface, front</b>	LC/UPC
<b>Interface, rear</b>	MPO
<b>Interface Feature, rear</b>	Key up   MPO Non-Pinned
<b>Polarity</b>	Method B Enhanced (ULL)
<b>Shuttered</b>	No
<b>Total Fibers, quantity</b>	24
<b>Total Ports, quantity, front</b>	24

## Dimensions

<b>Height</b>	24.64 mm   0.97 in
<b>Width</b>	94 mm   3.701 in

# 760236119 | DM12iP-24LC-WB-ULL

---

**Depth** 113.28 mm | 4.46 in

## Optical Specifications

**Fiber Mode** Multimode  
**Fiber Type** OM5, LazrSPEED® wideband  
**Insertion Loss Change, temperature** 0.3 dB  
**Insertion Loss, maximum** 0.35 dB

## Environmental Specifications

**Qualification Standards** TIA/EIA-568-C.3  
**Safety Standard** cUL US 1863

## Packaging and Weights

**Packaging quantity** 1

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant



## \* Footnotes

**Insertion Loss Change, temperature** Maximum insertion loss change from -10 °C to +60 °C (+14 °F to +140 °F)