

FOSC® 450 D6 Fiber Optic Splice Closure, Gel Cable sealing, pre-installed D ribbon tray, 6 cable attachments, with test valve

- Single-ended, O-ring sealed dome closure for splicing feeder and distribution cables
- Gel cable sealing technology allows easy adding or removing of a wide size range of cables
- Compatible with most common cable types: e.g. loose tube, central core, ribbon fiber
- FOSC splice trays hinged for access to any splice without disturbing other trays
- Closure can be used in aerial, pedestal and underground (up to 5 meters) environments
- Compatible with CommScope's CWDM modules and optical splitter trays

Product Classification

 Regional Availability
 Latin America | North America

 Product Type
 Single-ended, round fiber closure

Product Brand FOSC®
Product Series FOSC 450

General Specifications

Cable Entry Drop Port StyleRoundCable Entry Main Port StyleRound

Cable Ports Quantity, total 6 round ports

Cable Sealing TypeCompressed gel

Closure Sealing Type Dome-to-base clamp with O-ring

Closure Style Single-ended

Color Black

Fiber Storage Basket Type Tall size

Flash Test Valve Pre-installed

Ground Feed-through None

Mounting Pole | Strand | Wall

Network Area Type Feeder

Splice Tray Included, quantity

Splice Tray Type Included 12-way, ribbon

Splicing Capacity, Mass Fusion, maximum 3456
Splicing Capacity, maximum 3456



Splicing Capacity, Single Fusion, maximum768Splicing Capacity, Single Splice, 12 fibers, maximum576Splicing Capacity, Single Splice, 6 fibers, maximum288

Splicing Type, Supported Mass fusion | Single fusion

Dimensions


 Length
 753 mm | 29.646 in

 Diameter
 254 mm | 10 in


 Diameter, with clamp
 292 mm | 11.496 in

 Main Cable Diameter, maximum
 25 mm | 0.984 in

Dimension Drawing



Ordering Tree



Material Specifications

Material Type Impact-resistant polymer

Environmental Specifications

Environmental Space Below ground | Buried

Qualification Standards IEC 61300, 5 m waterhead

Water Resistance Flash test valve at 5 psi (40 kPa)

1

Packaging and Weights

Packaging quantity

Packaging Type Box | Carton

Weight, net 9.07 kg | 19.996 lb

COMMSCOPE®

Regulatory Compliance/Certifications

lassification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

