760237022 | CPPR-5E-DM-1U-24



Unshielded Recessed Angled Distribution Module Panel, Cat 5e, 1U, 24 port, Black

Product Classification

| Regional Availability | Asia Australia/New Zealand EMEA Latin America North America | |
|--|--|--|
| Portfolio | CommScope® | |
| Product Type | RJ45 patch panel | |
| General Specifications | | |
| ANSI/TIA Category | 5e | |
| Cable Type | Unshielded | |
| Color | Black | |
| Conductor Type | Solid Stranded | |
| Modules, quantity | 4 | |
| Panel Style | Angled recessed | |
| Rack Type | EIA 19 in | |
| Rack Units | 1 | |
| Termination Type | IDC | |
| Total Ports, quantity | 24 | |
| Transmission Standards | ANSI/TIA-568.2-D ISO/IEC 11801 Class D | |
| Wiring | T568A T568B | |
| Dimensions | | |
| Height | 44.45 mm 1.75 in | |
| Width | 482.6 mm 19 in | |
| Depth, with cable management | 137.16 mm 5.4 in | |
| Compatible Diameter Over Dielectric, maximum | 1.168 mm 0.046 in | |
| Compatible Diameter Over Dielectric, minimum | 0.762 mm 0.03 in | |
| Compatible Conductor Gauge, solid | 22 AWG 24 AWG | |
| Compatible Conductor Gauge, stranded | 22 AWG 24 AWG | |

Page 1 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: December 6, 2024



760237022 | CPPR-5E-DM-1U-24

Electrical Specifications

| Current Rating at Temperature | 1.5 A @ 20 °C 1.5 A @ 68 °F |
|---|--|
| Dielectric Withstand Voltage, RMS, conductive surface | 1,500 Vac @ 60 Hz |
| Dielectric Withstand Voltage, RMS, contact-to-contact | 1,000 Vac @ 60 Hz |
| Insulation Resistance, minimum | 500 MOhm |
| Remote Powering | Fully complies with the recommendations set forth by IEEE 802.3bt (Type 4) for the safe delivery of power over LAN cable when installed according to ISO/IEC 14763-2, CENELEC EN 50174-1, CENELEC EN 50174-2 or TIA TSB-184-A |
| Material Specifications | |
| Contact Plating Material | Precious metals |
| Material Type | High-impact, flame retardant, thermoplastic Powder- coated steel |
| Termination Contact Plating | Nickel |
| Mechanical Specifications | |
| Plug Insertion Life, minimum | 750 times |
| Plug Insertion Life, test plug | IEC 60603-7 compliant plug |
| Plug Retention Force, minimum | 133 N 29.9 lbf |
| | |
| Environmental Specifications | |
| Operating Temperature | -10 °C to +60 °C (+14 °F to +140 °F) |
| Storage Temperature | -40 °C to +70 °C (-40 °F to +158 °F) |
| Relative Humidity | Up to 95%, non-condensing |
| Flammability Rating | UL 94 V-0 |
| Safety Standard | UL cUL |
| Packaging and Weights | |

Packaging Material

Packaging quantity

Eco-friendly, single-use plastics-free 1

Regulatory Compliance/Certifications

Agency

CHINA-ROHS

Classification

Below maximum concentration value

Page 2 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: December 6, 2024

COMMSCOPE°

760237022 | CPPR-5E-DM-1U-24

| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |
|---------------|--|
| RCM | Compliant to electrical safety & telecommunications requirements |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant |
| UK-ROHS | Compliant |
| | |



©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: December 6, 2024

COMMSCOPE®