

FPS-FMTSP-ANN01

FMT Fiber Optic Splitter Patch Panel, 1U, 19 in, 1x32 splitter, SC/UPC splitter and output connect., 1 splitter



Product Classification

Regional Availability	North America
Portfolio	CommScope®
Product Type	Splitter patch panel
Product Series	FMT

General Specifications

Device Type	Plug-and-play module
Functionality	Splitting
Circuits, quantity	1
Distribution Type	1 x 32 splitter
Interface, front	SC/UPC
Rack Units	1
Split Ratio	Symmetrical
Splitter, quantity	1

Dimensions

Height	71.88 mm 2.83 in
Width	17.27 mm 0.68 in
Depth	177.8 mm 7 in

Optical Specifications

Directivity, minimum	60 dB
Insertion Loss, Splitter, maximum	16.7 dB
Insertion Loss, Splitter, typical	16.5 dB

FPS-FMTSP-ANN01

Environmental Specifications

Operating Temperature -55 °C to +85 °C (-67 °F to +185 °F)

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency

CHINA-ROHS

REACH-SVHC

ROHS

Classification

Above maximum concentration value

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

Compliant/Exempted

