## 760240514 | FACT-4ELHPLFS



FACT® Fiber Optic Patch/Splice Chassis, gray, 4E high, 192-port, singlemode, loaded with LC/UPC adapters and B-grade pigtails, SMOUV splice tray type, left-hand patch

- Designed for use with the all-purpose all-front-access FACT frames and FIST-GR3 frames supporting up to 2,688 LC or 1,344 SC connections in a single frame (FACT-IC frame 2880 LC or 1440 SC)
- Reduced installation and maintenance time via the toolless snap-on design supporting both interconnect and cross-connect applications
- Flexible customization enabled by 4 chassis types (patch-only, patch-splice, pre-cabled and splice-only) to support all ODF applications
- High density through the single FACT element height (1E) being 30% less tall compared to the industry standard panel height (1HU)

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

**Product Type** Fiber patch/splice chassis

Product Brand FACT®

Product Series FACT

### General Specifications

Functionality Patching | Splicing

**Application** Compatible with FIST-GR3-style frames

**Body Style** Left-hand patch

**Color** Gray

 Growth Configuration
 Fully loaded

 Interface, front
 LC/UPC

 Patch Cord Routing
 Left sided

Pigtail Assembly Type 12-fiber, stranded

Pigtails Included, quantity 192

Rack Type EIA 19 in

Rack Units 2.8

Shelf Movement Sliding

Splicing Capacity, maximum 192

COMMSCOPE®

# 760240514 | FACT-4ELHPLFS

**Splicing Type** SMOUV

Total Ports, quantity 192

**Transmission Standards** ETSI EN 300 019-1-3 | IEC 61300-3-30


#### **Dimensions**

 Height
 123.8 mm | 4.874 in

 Width
 524 mm | 20.63 in

 Depth
 283 mm | 11.142 in

### Ordering Tree



## **Optical Specifications**

Fiber Mode Singlemode

**Fiber Type** G.657.A1

**Performance Grade** Superior B grade

Insertion Loss, maximum0.5 dBReturn Loss, minimum50 dB



# 760240514 | FACT-4ELHPLFS

## **Environmental Specifications**

Operating Temperature  $-40 \,^{\circ}\text{C}$  to  $+70 \,^{\circ}\text{C}$  (-40  $^{\circ}\text{F}$  to  $+158 \,^{\circ}\text{F}$ )

Storage Temperature  $-20 \,^{\circ}\text{C}$  to  $+85 \,^{\circ}\text{C}$  (-4  $^{\circ}\text{F}$  to  $+176 \,^{\circ}\text{F}$ )

Flammability Rating UL 94 V-0

Packaging and Weights

**Included** Mounting hardware for FACT frame

Packaging quantity 1

### Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted



#### \* Footnotes

**Performance Grade** Guarantee to meet IEC 61755-1 Random Mating requirement

