

Fiber Indexing Terminal, 4F Branching, Dielectric Loose Tube Cable, 750 Feet

- Fiber Indexing terminals are access terminals using hardened connectivity technology that withstand the rugged outside plant environment
- Fiber Indexing terminals eliminate splicing and use 12-strand fiber cable in a daisy-chain topology, reducing the total required cable length by up to 70%
- Hardened adapters are factory-terminated and environmentally sealed to ensure rapid plug-and play drop cable installations

Product Classification

Regional Availability

North America

Product Type Access terminal, indexed without splitter/tap

Product Series NDX

General Specifications

Cable TypeDielectric - Flat - Loose Tube

Cable, quantity

Distribution Type 4 ports

Enclosure Color Black

Mounting Handhole | Pedestal | Pole

Port Type Hardened multi-fiber (HMFOC) jack, male/pinned

Port, quantity 4
Splitter, quantity 0

Stub Type Hardened multi-fiber (HMFOC) plug

Dimensions

Height 297.8 mm | 11.724 in

Width 130.3 mm | 5.13 in


Depth 90.4 mm | 3.559 in

Cable Length, stub 750 ft (228 m)


Cable Outer Diameter 4.5 x 8.1 mm (0.18 x 0.32 in)

Dimension Drawing





Ordering Tree



Material Specifications

Enclosure Material Type

Gasketed hardened plastic

COMMSCOPE®

Optical Specifications

Fiber Type G.652.D

Operating Wavelength Range 1260 – 1635 nm

Attenuation Cable Coefficient, maximum 0.30 dB/km @ 1550 nm | 0.40 dB/km @ 1310 nm

Attenuation Terminal Connectors, maximum0.45 dBDirectivity, minimum60 dBInsertion Loss, Stub Connector, maximum0.45 dBInsertion Loss, Stub Connector, typical0.16 dBInsertion Loss, Terminal Connector, typical0.16 dB

Return Loss, Connector, minimum 65 dB

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ ($-40 \,^{\circ}\text{F}$ to $+158 \,^{\circ}\text{F}$)

Relative Humidity 5%-100%, condensing

Environmental Space Above ground | Below ground | Buried

Flammability Rating UL 94 V-0

Qualification Standards IEC 60529, IP68 + 2 m waterhead | NEMA, Type 6 + 10 ft

waterhead | Telcordia GR-3120-CORE | Telcordia GR-326-

CORE | Telcordia GR-771-CORE

UV Resistance UV stabilized

Packaging and Weights

Included Enclosure (1) | Universal mounting bracket (1)

Packaging quantity 1

Packaging TypeBox | CartonWeight, without cable1 kg | 2.205 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted





Included Products

MST-UMB-MINI – DLX® Mini-MST, Fiber Optic Universal Mounting Bracket