


# OTE200-04MH-14-S12-G-W



Mini-OTE 200-Series, Optical Terminal Enclosure, 4-port full-size connector, 1:4 splitter, gray, wall mount

- Optical Terminal Enclosures incorporate hardened connector technology that is designed to withstand the rugged outside plant environment
- Functionality to splice and store feeder cable in the field with the possibility to splice in the field two extra branch cables
- Hardened adapters are factory-terminated and environmentally sealed to ensure rapid plug-and-play drop cable installations
- Integrated external cable fixation guarantees easy, fast and reliable cable manipulations

## Product Classification

Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America
Product Type	Access terminal, with splitter
Product Series	Mini-OTE 200

## General Specifications


Cable Type	No cable (stubless)
Cable, quantity	0
Distribution Type	1 x 4 splitter
Enclosure Color	Gray
Mounting	Handhole   Pole   Wall
Port Type	Hardened full-size SC/APC
Port, quantity	4
Splitter, quantity	1
Stub Type	No tail

## Dimensions


Height	358.5 mm   14.114 in
Width	166 mm   6.535 in
Depth	129.3 mm   5.091 in
Cable Length, stub	0 ft (0 m)

## Dimension Drawing

# OTE200-04MH-14-S12-G-W



## Ordering Tree



## Material Specifications

### Enclosure Material Type

Glass filled polypropylene (GF-PP)

## Optical Specifications

### Fiber Type

G.652.D

### Operating Wavelength Range

1260 – 1635 nm

### Attenuation Splitter, maximum

7.1 dB

# OTE200-04MH-14-S12-G-W

Attenuation Terminal Connectors, maximum	0.4 dB
Directivity, minimum	60 dB
Insertion Loss, Splitter, typical	6.7 dB
Insertion Loss, Terminal Connector, typical	0.16 dB
Return Loss, Connector, minimum	65 dB
Return Loss, Single Ports, minimum	55 dB

## Environmental Specifications

Operating Temperature	-40 °C to +65 °C (-40 °F to +149 °F)
Relative Humidity	5%–100%, condensing
Environmental Space	Above ground   Below ground   Buried
Qualification Standards	IEC 60529, IP68 + 3 m waterhead
UV Resistance	UV stabilized

## Packaging and Weights

Included	Cable termination unit (2)   Enclosure (1)   Fiber pigtail cassette (1)   Optical splitter (1)   Splice Cassette (2)
Packaging quantity	1
Packaging Type	Box   Carton

## Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

## Included Products

CW8094-002	–	TENIO™ Cable Termination Unit kit
TENIO-CTU-L(10)		