

760092049 | RK12-45AM



Equipment Rack, 2-Post, 12 in (305 mm) Channel x 7ft (2135 mm) H - 19 in (482.6 mm) Alu (45U) M6 Tapped Rails, Black

OBSOLETE

This product was discontinued on: November 30, 2018

Replaced By:

760090159 RK12-45S	Equipment Rack, 2-Post, 12 in (305 mm) Channel x 7ft (2135 mm) H - 19 in (482.6 mm) Steel (45U) 3/8 Sq Punch, Black
-----------------------	---

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	2 post rack

General Specifications

Color	Black
Rack Type	EIA 19 in
Rack Units	45
Rail Mounting Hole	M6

Dimensions

Height	2,133.6 mm 84 in
Channel Width	304.8 mm 12 in
Width	518.16 mm 20.4 in
Depth	609.6 mm 24 in
Dimensional Standards	EIA-310-E

Material Specifications

Finish	Powder-coated, textured
Material Type	Aluminum

760092049 | RK12-45AM

Mechanical Specifications

Load Rating 453.592 kg | 1000 lb

Packaging and Weights

Included Four M6 x 12 mm mounting screws | Instruction sheet | Twelve 3/8 in split lock washers | Twelve 3/8-16 UNC x 1 in hex head bolts | Twelve 3/8-16 hex nuts | Two extruded base angles | Two extruded top angles | Two vertical rack rails

Packaging quantity 1

Packaging Type Flat packed

Weight, net 24.49 kg | 53.991 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system