



SYSTIMAX 360™ iPatch® G2-1U-MOD LC 5PK imVision Upgrade Kit

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	SYSTIMAX®
Product Type	Upgrade kit
Product Brand	SYSTIMAX 360™ iPatch®

General Specifications

Color	Cool gray
Intelligence Type	iPatch® enabled
Total Ports, quantity	24

Dimensions

Height	31.75 mm 1.25 in
Width	393.7 mm 15.5 in
Depth	12.7 mm 0.5 in

Material Specifications

Material Type	Acrylonitrile butadiene styrene (ABS) Polycarbonate (PC)
----------------------	--

Environmental Specifications

Operating Temperature	-5 °C to +50 °C (+23 °F to +122 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Relative Humidity	Up to 95%, non-condensing
Flammability Rating	UL 94 V-0
Safety Standard	ACMA CE UL cUL

Packaging and Weights

Packaging quantity	5
Weight, net	0.113 kg 0.25 lb

Regulatory Compliance/Certifications

760105148 | 360-iP-UP-KIT-G2-LC

Agency

CHINA-ROHS

ISO 9001:2015

REACH-SVHC

ROHS

Classification

Above maximum concentration value

Designed, manufactured and/or distributed under this quality management system

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

Compliant/Exempted

