


760109561 | 360G2 Cassette 6-SC-SM-BL-Pigtails B



360G2 Cassette 6 SC Singlemode Blue with Pigtails B

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber cassette with pigtails

General Specifications

Adapter Color	Blue
Interface Feature, front	Standard
Interface, front	SC
Total Fibers, quantity	6
Total Ports, quantity, front	6

Dimensions

Height	30.48 mm 1.2 in
Width	91.44 mm 3.6 in
Pigtail Length	1.5 m 4.921 ft
Depth	119.38 mm 4.7 in

Optical Specifications

Fiber Type	G.652.D and G.657.A1 , TeraSPEED® OS2
Insertion Loss, typical	0.4 dB
Return Loss, minimum	55 dB

Environmental Specifications

Safety Standard	UL
------------------------	----

760109561 | 360G2 Cassette 6-SC-SM-BL-Pigtails B

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency

ISO 9001:2015

REACH-SVHC

Classification

Designed, manufactured and/or distributed under this quality management system

Compliant as per SVHC revision on www.commscope.com/ProductCompliance



Included Products

760049783 — TeraSPEED® SC Multiport Shuttered Adapter, Blue, Single Pack
SFA-SC06-BL-SHUTTERED

860240738 — TeraSPEED® SC 0.9 mm Pigtail, red, 1.5 m

860240746 — TeraSPEED® SC 0.9 mm Pigtail, black, 1.5 m

860240753 — TeraSPEED® SC 0.9 mm Pigtail, yellow, 1.5 m

860240761 — TeraSPEED® SC 0.9 mm Pigtail, violet, 1.5 m

860240779 — TeraSPEED® SC 0.9 mm Pigtail, rose, 1.5 m

860240787 — TeraSPEED® SC 0.9 mm Pigtail, aqua, 1.5 m

TeraSPEED® SC Multiport Shuttered Adapter, Blue, Single Pack

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber adapter
Product Brand	TeraSPEED®
Product Series	SFA

General Specifications

Body Style	Ganged
Color	Blue
Interface	SC
Interface Feature	Standard
Mounting	No flange
Shuttered	Yes
Total Ports, quantity	6

Material Specifications

Alignment Sleeve Material	Zirconia
----------------------------------	----------

Optical Specifications

Fiber Mode	Singlemode
-------------------	------------

Packaging and Weights

Packaging quantity	1
---------------------------	---

Regulatory Compliance/Certifications

760049783 | SFA-SC06-BL-SHUTTERED

Agency

CHINA-ROHS

ISO 9001:2015

REACH-SVHC

ROHS



Classification


Below maximum concentration value

Designed, manufactured and/or distributed under this quality management system

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

Compliant

TeraSPEED® SC 0.9 mm Pigtail, red, 1.5 m



Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber pigtail, simplex
Product Brand	TeraSPEED®

General Specifications

Construction Type	Pigtail, jacketed
Interface, Connector A	SC/UPC
Jacket Color	Red
Total Fibers, quantity	1

Mechanical Specifications

Cable Retention Strength, maximum	1.00 lb @ 0 ° 1.00 lb @ 90 °
--	--------------------------------

Optical Specifications

Fiber Type	G.652.D and G.657.A1 , TeraSPEED® OS2
-------------------	---

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Environmental Space	Plenum


Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

860240738



TeraSPEED® SC 0.9 mm Pigtail, black, 1.5 m



Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber pigtail, simplex
Product Brand	TeraSPEED®

General Specifications

Construction Type	Pigtail, jacketed
Interface, Connector A	SC/UPC
Jacket Color	Black
Total Fibers, quantity	1

Mechanical Specifications

Cable Retention Strength, maximum	1.00 lb @ 0 ° 1.00 lb @ 90 °
--	--------------------------------

Optical Specifications

Fiber Type	G.652.D and G.657.A1 , TeraSPEED® OS2
-------------------	---

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Environmental Space	Plenum


Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

860240746



TeraSPEED® SC 0.9 mm Pigtail, yellow, 1.5 m



Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber pigtail, simplex
Product Brand	TeraSPEED®

General Specifications

Construction Type	Pigtail, jacketed
Interface, Connector A	SC/UPC
Jacket Color	Yellow
Total Fibers, quantity	1

Mechanical Specifications

Cable Retention Strength, maximum	1.00 lb @ 0 ° 1.00 lb @ 90 °
--	--------------------------------

Optical Specifications

Fiber Type	G.652.D and G.657.A1 , TeraSPEED® OS2
-------------------	---

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Environmental Space	Plenum


Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

860240753



TeraSPEED® SC 0.9 mm Pigtail, violet, 1.5 m



Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber pigtail, simplex
Product Brand	TeraSPEED®

General Specifications

Construction Type	Pigtail, jacketed
Interface, Connector A	SC/UPC
Jacket Color	Violet
Total Fibers, quantity	1

Mechanical Specifications

Cable Retention Strength, maximum	1.00 lb @ 0 ° 1.00 lb @ 90 °
--	--------------------------------

Optical Specifications

Fiber Type	G.652.D and G.657.A1 , TeraSPEED® OS2
-------------------	---

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Environmental Space	Plenum


Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

860240761



TeraSPEED® SC 0.9 mm Pigtail, rose, 1.5 m



Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber pigtail, simplex
Product Brand	TeraSPEED®

General Specifications

Construction Type	Pigtail, jacketed
Interface, Connector A	SC/UPC
Jacket Color	Rose
Total Fibers, quantity	1

Mechanical Specifications

Cable Retention Strength, maximum	1.00 lb @ 0 ° 1.00 lb @ 90 °
--	--------------------------------

Optical Specifications

Fiber Type	G.652.D and G.657.A1 , TeraSPEED® OS2
-------------------	---

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Environmental Space	Plenum


Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

860240779



TeraSPEED® SC 0.9 mm Pigtail, aqua, 1.5 m



Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber pigtail, simplex
Product Brand	TeraSPEED®

General Specifications

Construction Type	Pigtail, jacketed
Interface, Connector A	SC/UPC
Jacket Color	Aqua
Total Fibers, quantity	1

Mechanical Specifications

Cable Retention Strength, maximum	1.00 lb @ 0 ° 1.00 lb @ 90 °
--	--------------------------------

Optical Specifications

Fiber Type	G.652.D and G.657.A1 , TeraSPEED® OS2
-------------------	---

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Environmental Space	Plenum

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

860240787

