FFWSASA42

Base Product



Singlemode SC APC to SC APC, Fiber Patch Cord, 1.6 mm Duplex, Low Smoke Zero Halogen (LSZH)

Product Classification

| Regional Availability | Asia Australia/New Zealand China Europe India Latin America Middle East/Africa North America |
|-----------------------|--|
| Portfolio | CommScope® |
| Product Type | Fiber patch cord, duplex |
| Product Brand | SYSTIMAX InstaPATCH® 360 |
| Product Series | FFW |
| Ordering Note | For lengths greater than 999 ft (304 m), orders must be in meters Minimum length may vary based on cable configuration |

General Specifications

| Color, boot A | Green |
|---------------------------------|----------------|
| Color, connector A | Green |
| Color, boot B | Green |
| Color, connector B | Green |
| Interface, Connector A | SC/APC |
| Interface, Connector B | SC/APC |
| Jacket Color | Yellow |
| Polarity | Pairs, flipped |
| Total Fibers, quantity | 2 |
| Dimensions | |
| Cable Assembly Length Range (m) | 1 – 999 |

| Cable Assembly Length Range (m) | 1 – 999 |
|----------------------------------|-------------------|
| Cable Assembly Length Range (ft) | 1 – 999 |
| Diameter Over Jacket | 1.6 mm 0.063 in |


Page 1 of 8

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 12, 2024



FFWSASA42

Ordering Tree



Mechanical Specifications

 Cable Retention Strength, maximum
 11.24 lb @ 0 ° | 4.40 lb @ 90 °

Optical Specifications

| Fiber Mode | Singlemode |
|------------|--------------------------------|
| Fiber Type | G.652.D G.657.A1, TeraSPEED® |

Environmental Specifications

| Operating Temperature | -10 °C to +60 ° |
|-----------------------|-----------------|
| Environmental Space | Dual Rated LSZ |

-10 °C to +60 °C (+14 °F to +140 °F) Dual Rated LSZH/Riser

Packaging and Weights

Packaging quantity

1

Regulatory Compliance/Certifications

| ANATEL Compliant | Agency | Classification |
|--|---------------|--|
| | ANATEL | Compliant |
| CHINA-ROHS Above maximum concentration value | CHINA-ROHS | Above maximum concentration value |
| ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system | ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |
| ROHS Compliant/Exempted | ROHS | Compliant/Exempted |
| UK-ROHS Compliant/Exempted | UK-ROHS | Compliant/Exempted |



Included Products

Page 2 of 8

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 12, 2024

COMMSCOPE




| 760021675 N-002-ZC-8W-F16YL/E | - | Fiber Indoor Cable, TeraSPEED® 1.6mm Low Smoke Zero Halogen Riser, 2-fiber Zipcord, Singlemode G.652.D and G.657.A1, Feet jacket marking, Yellow jacket color, Eca Flame Rating |
|----------------------------------|---|--|
| 860648957 | _ | SC/APC Connector, Singlemode, Green |

Page 3 of 8

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 12, 2024



760021675 | N-002-ZC-8W-F16YL/E



Fiber Indoor Cable, TeraSPEED® 1.6mm Low Smoke Zero Halogen Riser, 2-fiber Zipcord, Singlemode G.652.D and G.657.A1, Feet jacket marking, Yellow jacket color, Eca Flame Rating

Product Classification

| Regional Availability | Asia Australia/New Zealand EMEA Latin America North America |
|------------------------|--|
| Portfolio | CommScope® |
| Product Type | Fiber indoor cable |
| Product Series | N-ZC |
| General Specifications | |
| Cable Type | Cordage |
| Construction Type | Non-armored |
| Subunit Type | Gel-free |
| Jacket Color | Yellow |
| Jacket Marking | Feet |
| Total Fiber Count | 2 |
| Dimensions | |
| Height Over Jacket | 1.7 mm 0.067 in |
| Width Over Jacket | 3.5 mm 0.138 in |


Representative Image

Page 4 of 8

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 3, 2024



760021675 | N-002-ZC-8W-F16YL/E



Mechanical Specifications

| Minimum Bend Radius, loaded | 38 mm 1.496 in |
|-----------------------------------|---------------------------------------|
| Minimum Bend Radius, unloaded | 15 mm 0.591 in |
| Tensile Load, long term, maximum | 53 N 11.915 lbf |
| Tensile Load, short term, maximum | 178 N 40.016 lbf |
| Compression | 10 N/mm 57.101 lb/in |
| Compression Test Method | FOTP-41 IEC 60794-1 E3 |
| Flex | 300 cycles |
| Flex Test Method | FOTP-104 IEC 60794-1 E6 |
| Impact | 0.74 N-m 6.55 in lb |
| Impact Test Method | FOTP-25 IEC 60794-1 E4 |
| Strain | See long and short term tensile loads |
| Strain Test Method | FOTP-33 IEC 60794-1 E1 |
| Twist | 10 cycles |
| Twist Test Method | FOTP-85 IEC 60794-1 E7 |
| Vertical Rise, maximum | 500 m 1,640.42 ft |
| Optical Specifications | |

Fiber Type

G.652.D and G.657.A1, TeraSPEED®

Environmental Specifications

Installation temperature

-20 °C to +60 °C (-4 °F to +140 °F)

Page 5 of 8

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 3, 2024



760021675 | N-002-ZC-8W-F16YL/E

| Operating Temperature | -20 °C to +70 °C (-4 °F to +158 °F) |
|--|--|
| Storage Temperature | -40 °C to +70 °C (-40 °F to +158 °F) |
| Cable Qualification Standards | ANSI/ICEA S-83-596 Telcordia GR-409 |
| EN50575 CPR Cable EuroClass Fire Performance | Eca |
| Environmental Space | Low Smoke Zero Halogen (LSZH) Riser |
| Flame Test Listing | NEC OFNR-ST1 (ETL) and c(ETL) |
| Flame Test Method | IEC 60332-1-2 IEC 60332-3 IEC 60754-2 IEC 61034-2 UL 1666 UL 1685 |

Environmental Test Specifications

| Heat Age | -20 °C to +85 °C (-4 °F to +185 °F) |
|-------------------------------|-------------------------------------|
| Heat Age Test Method | IEC 60794-1 F9 |
| Low High Bend | -20 °C to +70 °C (-4 °F to +158 °F) |
| Low High Bend Test Method | FOTP-37 IEC 60794-1 E11 |
| Temperature Cycle | -20 °C to +70 °C (-4 °F to +158 °F) |
| Temperature Cycle Test Method | FOTP-3 IEC 60794-1 F1 |

Packaging and Weights

Cable weight

6 kg/km | 4.032 lb/kft

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| CENELEC | EN 50575 compliant, Declaration of Performance (DoP) available |
| CHINA-ROHS | Below maximum concentration value |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant |
| UK-ROHS | Compliant |
| | |

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable

Page 6 of 8

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 3, 2024





Product Classification

SC/APC Connector, Singlemode, Green

| Regional Availability | Asia Australia/New Zealand EMEA Latin America North America |
|------------------------------------|---|
| Portfolio | CommScope® |
| Product Type | Fiber connector |
| General Specifications | |
| Color, boot | Green |
| Color, housing | Green |
| Interface | SC/APC |
| Dimensions | |
| Length | 48 mm 1.89 in |
| Compatible Cable Diameter | 1.6 mm 0.063 in 2 mm 0.079 in |
| Material Specifications | |
| Ferrule Material | Zirconia |
| Mechanical Specifications | |
| Cable Retention Strength, maximum | 15.73 lb @ 0 ° |
| Optical Specifications | |
| Fiber Mode | Singlemode |
| Insertion Loss Change, mating | 0.2 dB |
| Optical Components Standard | ANSI/TIA-568. 3-D IEC 61753-1 |
| Insertion Loss Change, temperature | 0.2 dB |
| Insertion Loss, maximum | 0.4 dB |
| Return Loss, minimum | 65 dB |

Page 7 of 8

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 9, 2024



860648957

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHSAbove maximum concentration valueROHSCompliant/ExemptedUK-ROHSCompliant/Exempted



* Footnotes

Insertion Loss Change, mating TIA-568: Maximum insertion loss change after 500 matings

Insertion Loss Change, temperature Maximum insertion loss change from -10 °C to +60 °C (+14 °F to +140 °F)

Page 8 of 8

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 9, 2024

