## **FJVMPMPAF**

#### Base Product

**Product Brand** 



OM5 MPO (Unpinned) to MPO (Unpinned), InstaPATCH® 360 Preterminated Trunk Cable, 24-Fiber, Low Smoke Zero Halogen

 LazrSPEED® WideBand extends the capability of OM4 across enough spectrum to support at least four low-cost wavelengths

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | China | Europe | India | Latin

America | Middle East/Africa | North America

Portfolio CommScope®

**Product Type** Fiber trunk cable assembly

Ordering Note For additional jacket colors, please contact a CommScope Sales Representative | For

lengths greater than 999 ft (304 m), orders must be in meters | Minimum length may

vary based on cable configuration

SYSTIMAX InstaPATCH® 360

## General Specifications

Color, boot A Black

Color, connector A Lime green

Color, boot B Black

Color, connector BLime greenConstruction TypeStrandedFurcation ColorLime green

 Interface, Connector A
 MPO-12/UPC Female

 Interface, Connector B
 MPO-12/UPC Female

 Jacket Color
 Lime green

 Polarity
 Method B (LL)

Fibers per Subunit, quantity 12

Total Fibers, quantity 24

**Dimensions** 

Breakout Length 33 in

Cable Assembly Length Range (m) 3 - 999


COMMSCOPE®

# **FJVMPMPAF**

#### Cable Assembly Length Range (ft)

10 - 999

## Ordering Tree



## Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0 ° | 4.40 lb @ 90 °

Optical Specifications

**Fiber Mode** Multimode

**Fiber Type** OM5, LazrSPEED®

**Environmental Specifications** 

**Operating Temperature**  $-10 \,^{\circ}\text{C}$  to  $+60 \,^{\circ}\text{C}$  (+14  $^{\circ}\text{F}$  to +140  $^{\circ}\text{F}$ )

Page 2 of 8

## **FJVMPMPAF**

#### **Environmental Space**

Dual Rated LSZH/Riser | Indoor

## Regulatory Compliance/Certifications

Agency Classification

ANATEL Compliant

CHINA-ROHS Above maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted






### Included Products

760229054 – Fiber indoor cable, LazrSPEED®, Low Smoke Zero Halogen Riser MPO Trunk, 24 fiber with 12 N-024-MP-5G-F12LM/D fiber subunits, Gel-free, Multimode OM5, Feet jacket marking, Lime green jacket color, Dca

flame rating

860647056 – MPO12, LOW LOSS, FEMALE, OM5, LIME, 3mm

# 760229054 | N-024-MP-5G-F12LM/D



Fiber indoor cable, LazrSPEED®, Low Smoke Zero Halogen Riser MPO Trunk, 24 fiber with 12 fiber subunits, Gel-free, Multimode OM5, Feet jacket marking, Lime green jacket color, Dca flame rating

### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North

America

Portfolio CommScope®

Product Type Fiber indoor cable

**Product Series** N-MP

General Specifications

Cable TypeMPO trunk cable

Construction Type Non-armored

**Subunit Type** Gel-free

Jacket Color Lime green

Jacket Marking Feet

Subunit, quantity 2

Fibers per Subunit, quantity 12

Total Fiber Count 24


Dimensions

Height Over Jacket5.2 mm | 0.205 inWidth Over Jacket8.2 mm | 0.323 inBuffer Tube/Subunit Diameter3 mm | 0.118 in

Representative Image



# 760229054 | N-024-MP-5G-F12LM/D



### Mechanical Specifications

Minimum Bend Radius, loaded78 mm | 3.071 inMinimum Bend Radius, unloaded52 mm | 2.047 inTensile Load, long term, maximum200 N | 44.962 lbf

**Tensile Load, short term, maximum** 667 N | 149.948 lbf

 Compression
 10 N/mm | 57.101 lb/in

 Compression Test Method
 FOTP-41 | IEC 60794-1 E3

Flex 300 cycles

Flex Test Method FOTP-104 | IEC 60794-1 E6

**Impact** 2.94 N-m | 26.021 in lb

Impact Test Method FOTP-25 | IEC 60794-1 E4

Strain See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

Vertical Rise, maximum 491 m | 1,610.892 ft

Optical Specifications

Fiber Type OM5, LazrSPEED® wideband | OM5, LazrSPEED® wideband

### **Environmental Specifications**

Installation temperature  $-20 \,^{\circ}\text{C}$  to  $+60 \,^{\circ}\text{C}$  (-4 °F to +140 °F)

Operating Temperature  $-20 \,^{\circ}\text{C}$  to  $+70 \,^{\circ}\text{C}$  (-4 °F to +158 °F)

Storage Temperature  $-40 \,^{\circ}\text{C}$  to  $+70 \,^{\circ}\text{C}$  (-40 °F to +158 °F)

Page 5 of 8



# 760229054 | N-024-MP-5G-F12LM/D

Cable Qualification Standards ANSI/ICEA S-83-596 | Telcordia GR-409

EN50575 CPR Cable EuroClass Fire PerformanceDcaEN50575 CPR Cable EuroClass Smoke Ratings1aEN50575 CPR Cable EuroClass Droplets Ratingd1EN50575 CPR Cable EuroClass Acidity Ratinga1

Environmental Space Low Smoke Zero Halogen (LSZH) | Riser

Flame Test Listing NEC OFNR-ST1 (ETL) and c(ETL)

Flame Test Method | IEC 60332-3 | IEC 60754-2 | IEC 61034-2 | UL 1666 | UL 1685

**Environmental Test Specifications** 

**Heat Age**  $-20 \,^{\circ}\text{C}$  to  $+85 \,^{\circ}\text{C}$   $(-4 \,^{\circ}\text{F}$  to  $+185 \,^{\circ}\text{F})$ 

**Heat Age Test Method** IEC 60794-1 F9

**Low High Bend**  $-20 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \, (-4 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$ 

**Low High Bend Test Method** FOTP-37 | IEC 60794-1 E11

**Temperature Cycle**  $-20 \,^{\circ}\text{C to} + 70 \,^{\circ}\text{C} \left(-4 \,^{\circ}\text{F to} + 158 \,^{\circ}\text{F}\right)$ 

**Temperature Cycle Test Method** FOTP-3 | IEC 60794-1 F1

Packaging and Weights

**Cable weight** 42 kg/km | 28.223 lb/kft

## Regulatory Compliance/Certifications

#### Agency Classification

CENELEC EN 50575 compliant, Declaration of Performance (DoP) available

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

ROHS Compliant UK-ROHS Compliant



### \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable



## 860647056



### MPO12, LOW LOSS, FEMALE, OM5, LIME, 3mm

### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

Product Type Fiber connector

General Specifications

**Color** Lime green

Color, boot Black
Ferrule Geometry Flat

Interface MPO/UPC Female

Interface Feature Unpinned

Total Fiber Count 12

**Dimensions** 

**Length** 60.1 mm | 2.366 in

**Compatible Cable Diameter** 3 mm | 0.118 in

Material Specifications

Ferrule Material Polymer

Mechanical Specifications

Cable Retention Strength, maximum  $11.24 \text{ lb} @ 0 ^{\circ}$ 

Optical Specifications

**Fiber Mode** Multimode

**Fiber Type** OM5

**Insertion Loss Change, mating** 0.3 dB

Optical Components Standard ANSI/TIA-568-C.3

**Insertion Loss Change, temperature** 0.3 dB

COMMSC PE®

## 860647056

Insertion Loss, maximum0.25 dBReturn Loss, minimum27 dB

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

\* Footnotes

**Insertion Loss Change, mating**TIA-568: Maximum insertion loss change after 500 matings

Insertion Loss Change, temperature Maximum insertion loss change from -10 °C to +60 °C (+14 °F to +140 °F)

