



Mini-OTE 300-Series, Optical Terminal Enclosure, 4-port full-size connector, w/ integrated 1x4 splitter, black, w/ grounding, external mounting. Splitter outputs connected to terminal housing ports, maximum 26 splices Build America Buy America (BABA)

- Hardened connectors are factory-terminated and environmentally sealed for use in optical drop cable deployments
- Plug and play adapter ports ensure rapid cable installment in the outside plant access section of the network
- Optical Terminal Enclosures incorporate hardened connector technology that is designed to withstand the rugged outside plant environment
- Accommodates CommScope’s field installable splitters and compact CWDMs
- *CommScope intends to release this product at a future date. At such time, this product will comply with the requirements of the Build America, Buy America Act and/or applicable waivers. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

Product Classification


Regional Availability	Asia EMEA Latin America North America
Product Type	Access terminal, with splitter
Product Series	Mini-OTE 300
Government Requirements	Build America Buy America (BABA) coming soon*

General Specifications

Application	For central core tube ribbon shielded/unshielded fiber cable For flat drop with/without trace wire fiber cable For loose buffer tube standard (72 F) and micro (144 F) fiber cable For round armored up to 0.50 in/12.7 mm diameter fiber cable
Cable Type	No cable (stubless)
Cable, quantity	0
Distribution Type	1 x 4 splitter
Enclosure Color	Black
Location of Manufacturing	Maple Grove, Minnesota
Mounting	Handhole Pedestal Pole Strand
Port Type	Hardened full-size SC/APC
Port, quantity	4
Splitter, quantity	1

Stub Type	No tail
Dimensions	
Height	342.9 mm 13.5 in
Width	182.88 mm 7.2 in
Depth	121.92 mm 4.8 in
Cable Length, stub	0 ft (0 m)

Dimension Drawing



Ordering Tree

OTE - M - - G

Number of ports

02	2 ports
04	4 ports
06	6 ports
08	8 ports
12	12 ports

Type of adapter

H	Full-size
X	DLX miniaturized

Passive optical module options

NN	No splitter
12	1:2 splitter (FBT)
14	1:4 splitter (planar)
18	1:8 splitter (planar)
2C	2 channel CCWDM
4C	4 channel CCWDM
8C	8 channel CCWDM

Number of trays

03	3 trays (standard)— 2 fiber splicing trays, 1 fiber storage tray
----	------------------------------------------------------------------------

Optional features

EXT	External mounting
##	Starting CCWDM wavelength, 20nm spacing
##A	Starting CCWDM wavelength, skipped channels

Example: OTE-04MX-14-EXTG03

4 Port Mini-OTE with 1x4 splitter, external mounting,
grounding, 3 trays

Material Specifications

Enclosure Material Type

Engineered plastic

Optical Specifications

Operating Wavelength Range

1260 – 1635 nm

Attenuation Splitter, maximum

7.1 dB

Attenuation Terminal Connectors, maximum

0.4 dB

Directivity, minimum

60 dB

Insertion Loss, Splitter, typical

6.7 dB

Insertion Loss, Terminal Connector, typical

0.16 dB

Return Loss, Connector, minimum

65 dB

Return Loss, Single Ports, minimum

55 dB

Environmental Specifications

Operating Temperature

-40 °C to +60 °C (-40 °F to +140 °F)

Relative Humidity

5%–100%, condensing

Environmental Space

Above ground | Below ground | Buried

Qualification Standard Note

See test report CTR-1016 for details and exceptions

Qualification Standards	IEC 60529, IP68 + 2 m waterhead Telcordia GR-771-CORE, Issue 2
UV Resistance	UV stabilized
Packaging and Weights	
Included	Enclosure (1) Gel-sealed input ports for butt applications (4) Gel-sealed input ports for inline applications (1) Integrated slack storage tray (1) Integrated splice tray (2) Optical splitter (1) Pedestal mounting hardware (1)
Packaging quantity	1
Packaging Type	Box Carton
Weight, without cable	2.83 kg 6.239 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted



Included Products

760242289	–	Mini-OTE 300-Series, Optical Terminal Pole Cable Retention
OTE-M-CABLERET		Kit



Mini-OTE 300-Series, Optical Terminal Pole Cable Retention Kit

Product Classification

Regional Availability	North America
Product Type	Mounting bracket
Product Series	Mini-OTE 300

Environmental Specifications

Environmental Space	Outdoor
---------------------	---------

Packaging and Weights

Packaging quantity	5
Packaging Type	Bag Carton