

### FOSC® 450 A4 Fiber Optic Splice Closure with one 2-port tap, 15 dB

- Single-ended, O-ring sealed dome closure for splicing feeder and distribution cables
- Gel cable sealing technology allows easy adding or removing of a wide size range of cables
- Compatible with most common cable types: e.g. loose tube, central core, ribbon fiber
- FOSC splice trays hinged for access to any splice without disturbing other trays
- Closure can be used in aerial, pedestal and underground (up to 5 meters) environments
- Compatible with CommScope's CWDM modules and optical splitter trays

### Product Classification

Regional Availability	Latin America   North America	
Product Type	Single-ended, round fiber closure	
Product Brand	FOSC®	
Product Series	FOSC 450	
General Specifications		
Cable Entry Drop Port Style	Round	
Cable Entry Main Port Style	Round	
Cable Ports Quantity, total	4 round ports	
Cable Sealing Type	Compressed gel	
Closure Sealing Type	Dome-to-base clamp with O-ring	
Closure Style	Single-ended	
Color	Black	
Flash Test Valve	None	
Ground Feed-through	None	
Mounting	Pole   Strand   Wall	
Network Area Type	Drop	
Splice Tray Included, quantity	1	
Splice Tray Type Included	12-way, heat shrink	
Splicing Capacity, Mass Fusion, maximum	144	
Splicing Capacity, maximum	144	
Splicing Capacity, Single Fusion, maximum	96	
Splicing Capacity, Single Splice, 12 fibers, maximum	96	

Page 1 of 4

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: December 6, 2024



Splicing Capacity, Single Splice, 6 fibers, maximum

#### Splicing Type, Supported

### Dimensions

Length
--------

Diameter

Diameter, with clamp


Main Cable Diameter, maximum

## Dimension Drawing

### 48

Mass fusion | Single fusion

485 mm	I	19.094 in
150 mm	I	5.906 in
205 mm	I	8.071 in
25 mm	C	).984 in



## Ordering Tree

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: December 6, 2024

**COMMSCOPE**°

## FOSC 450 - A4 - TAP - XX - XX

### **Tap Tray Configuration**

2P	2-port tap tray	
4P	4-port tap tray	
8P	8-port tap tray	

#### **Tap Value and Type**

04T	4 dB, terminating tap
05	5 dB, non-terminating tap
07	7 dB, non-terminating tap
07T	7 dB, terminating tap
08	8 dB, non-terminating tap
09	9 dB, non-terminating tap
10	10 dB, non-terminating tap
11	11 dB, non-terminating tap
11T	11 dB, terminating tap
12	12 dB, non-terminating tap
13	13 dB, non-terminating tap
14	14 dB, non-terminating tap
15	15 dB, non-terminating tap
17	17 dB, non-terminating tap
19	19 dB, non-terminating tap
21	21 dB, non-terminating tap

### Material Specifications

Material Type

Impact-resistant polymer

### **Environmental Specifications**

Environmental Space	Below ground   Buried	
Qualification Standards	IEC 61300, 5 m waterhead	
Water Resistance	Flash test valve at 5 psi (40 kPa)	
Packaging and Weights		

Packaging quantity	1
Packaging Type	Box   Carton
Weight, net	2.72 kg   5.997 lb

### Regulatory Compliance/Certifications

Classification

#### Agency

CHINA-ROHS

Below maximum concentration value

Page 3 of 4

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: December 6, 2024

**COMMSCOPE**<sup>®</sup>

ISO 9001:2015

REACH-SVHC

ROHS

UK-ROHS



Designed, manufactured and/or distributed under this quality management system Compliant as per SVHC revision on www.commscope.com/ProductCompliance Compliant Compliant

Page 4 of 4

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: December 6, 2024

