

FOSC® 450 B6 Fiber Optic Splice Closure, Gel Cable sealing, no preinstalled tray, 2 cable attachments, three ground feedthrough lugs, with test valve

- Single-ended, O-ring sealed dome closure for splicing feeder and distribution cables
- Gel cable sealing technology allows easy adding or removing of a wide size range of cables
- Compatible with most common cable types: e.g. loose tube, central core, ribbon fiber
- FOSC splice trays hinged for access to any splice without disturbing other trays
- Closure can be used in aerial, pedestal and underground (up to 5 meters) environments
- Compatible with CommScope's CWDM modules and optical splitter trays

864

#### **Product Classification**

 Regional Availability
 Latin America | North America

 Product Type
 Single-ended, round fiber closure

Product Brand FOSC®
Product Series FOSC 450

## General Specifications

 Cable Entry Drop Port Style
 Round

 Cable Entry Main Port Style
 Round

Cable Ports Quantity, total6 round portsCable Sealing TypeCompressed gel

Closure Sealing Type Dome-to-base clamp with O-ring

Closure Style Single-ended

**Color** Black

Fiber Storage Basket TypeNo basketFlash Test ValvePre-installed

Ground Feed-through Included

Mounting Pole | Strand | Wall

Network Area Type Feeder

Splice Tray Included, quantity 0

Splice Tray Type Included No trays

Splicing Capacity, Mass Fusion, maximum 864

Splicing Capacity, maximum

COMMSC PE°

Splicing Capacity, Single Fusion, maximum 144
Splicing Capacity, Single Splice, 12 fibers, maximum 144
Splicing Capacity, Single Splice, 6 fibers, maximum 72

Splicing Type, Supported Mass fusion | Single fusion

#### **Dimensions**


 Length
 610 mm | 24.016 in

 Diameter
 254 mm | 10 in

 Diameter, with clamp
 291 mm | 11.457 in


 Main Cable Diameter, maximum
 25 mm | 0.984 in

### Dimension Drawing



## Ordering Tree





## Material Specifications

Material Type Impact-resistant polymer

## **Environmental Specifications**

Environmental Space Below ground | Buried

**Qualification Standards**IEC 61300, 5 m waterhead

Water Resistance Flash test valve at 5 psi (40 kPa)

1

Packaging and Weights

Packaging quantity

Packaging Type Box | Carton

**Weight, net** 5.9 kg | 13.007 lb

COMMSCOPE®

## Regulatory Compliance/Certifications

1
1

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

