# 727952-000 | FOSC450-B6-4-12-1-B3V



FOSC® 450 B6 Fiber Optic Splice Closure, Gel Cable sealing, one preinstalled 12-splice tray, 4 cable attach., three ground feedthrough lugs, valve

- Single-ended, O-ring sealed dome closure for splicing feeder and distribution cables
- Gel cable sealing technology allows easy adding or removing of a wide size range of cables
- Compatible with most common cable types: e.g. loose tube, central core, ribbon fiber
- FOSC splice trays hinged for access to any splice without disturbing other trays
- Closure can be used in aerial, pedestal and underground (up to 5 meters) environments
- Compatible with CommScope's CWDM modules and optical splitter trays

### Product Classification

Regional Availability	Latin America   North America
Product Type	Single-ended, round fiber closure
Product Brand	FOSC®
Product Series	FOSC 450
General Specifications	
Cable Entry Drop Port Style	Round
Cable Entry Main Port Style	Round
Cable Ports Quantity, total	6 round ports
Cable Sealing Type	Compressed gel
Closure Sealing Type	Dome-to-base clamp with O-ring
Closure Style	Single-ended
Color	Black
Fiber Storage Basket Type	B6, BS standard size
Flash Test Valve	Pre-installed
Ground Feed-through	Included
Mounting	Pole   Strand   Wall
Network Area Type	Feeder
Splice Tray Included, quantity	1
Splice Tray Type Included	12-way, heat shrink
Splicing Capacity, Mass Fusion, maximum	864
Splicing Capacity, maximum	864

Page 1 of 4


©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: December 6, 2024



# 727952-000 | FOSC450-B6-4-12-1-B3V

Splicing Capacity, Single Fusion, maximum	144
Splicing Capacity, Single Splice, 12 fibers, maximum	144
Splicing Capacity, Single Splice, 6 fibers, maximum	72
Splicing Type, Supported	Mass fusion   Single fusion
Dimensions	
Length	610 mm   24.016 in
Diameter	254 mm   10 in
Diameter, with clamp	291 mm   11.457 in
Main Cable Diameter, maximum	25 mm   0.984 in

## Dimension Drawing



# Ordering Tree

Page 2 of 4

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: December 6, 2024

**COMMSCOPE**°

#### 727952-000 FOSC450-B6-4-12-1-B3V

Valve for Flash Testing

N No Valve

0 No grounding

**Slack Basket Type** 

N No Basket

T Tall Size

A4 Standard Size B6. BS Standard Size

C6 Standard Size

S Stackable Trays in D Closure

D D6 Standard Size

V Valve (standard)

Note: We recommend flash test valves for FOSC closures. However, non-valved closures are available upon request.

1 ground feed-through lug (A4 only, N/A for BS)

3 ground feed-through lugs (B6, C6, and D6 closures only, N/A for BS)

6 ground feed-through lugs (C6 and D6 closure only, N/A for BS)

Special Bulkhead Basket arrangement for B, BS closures only

Size closures with "N" option include backbone used to route ribbons to ribbon trays. A and B-size closures include storage "socks".

Impact-resistant polymer

Below ground | Buried

IEC 61300, 5 m waterhead

Flash test valve at 5 psi (40 kPa)

Note: FEG and MEG kits provide optional ground isolation for FOSC 450 closures.

Number of Ground Feed-through Lugs

## FOSC 450 - XX - X - XX - X - X X X

Closure Size (inches)			
A	4	4 cable entry ports; 8 dia. x 19 long	
В	S	6 cable entry ports; 9 dia. x 19.5 long	

6 cable entry ports; 10 dia. x 24 long 6 cable entry ports; 11.5 dia. x 23 long 6 cable entry ports; 11.5 dia. x 30 long Termination Hardware Quantity for the Kit 2 cable attachments included 4 cable attachments included 6 cable attachments included (N/A for A size) Capacity and Type of Splice Tray NT No tray installed in factory A, B, or C tray with two SM6 splice modules A, B, or C tray with two SM12 splice modules 36 D tray with six SM6 splice modules 72\* D tray with six SM12 splice modules A, B size ribbon tray (accommodates 12 ribbons/144 fibers) R2 D size ribbon tray (24 ribbons/288 fibers) R3 C size ribbon tray (18 ribbons/216 fibers) Stackable single fusion trays (12 splices) \*Note: SMOUV (1120-01) splice protection sleeves are highly recommended for use with SM12 splice modules.

#### Quantity of Splice Trays Factory Installed

Choose either "0" trays (no trays installed) or "1" tray installed. Additional trays sold separately.

### Material Specifications

Material Type

### **Environmental Specifications**

**Environmental Space** 

**Oualification Standards** 

Water Resistance

### Packaging and Weights

Included	Cable blocking components
Packaging quantity	1
Packaging Type	Box   Carton
Weight, net	5.9 kg   13.007 lb

Page 3 of 4

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: December 6, 2024



# 727952-000 | FOSC450-B6-4-12-1-B3V

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

Page 4 of 4

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: December 6, 2024

