

760237707 | FOSC-OPGW-B4NT-0/6-NNC



FOSC® OPGW B Fiber Optic Splice Closure, Heat Shrink Cable sealing, butt type, no pre-installed trays

Product Classification

Regional Availability

Asia | EMEA | Latin America | North America

Product Type

Single-ended, round fiber closure

Product Brand

FOSC®

Product Series

FOSC OPGW

General Specifications

Cable Entry Drop Port Style

Round

Cable Entry Main Port Style

Round

Cable Ports Quantity, total

1 oval port (2 cables) + 4 round ports

Cable Sealing Type

Heat shrink

Closure Sealing Type

Dome-to-base clamp with O-ring

Closure Style

Single-ended

Color

Black

Ground Feed-through

None

Mounting

Pole | Strand | Wall

Network Area Type

Feeder

Splice Tray Included, quantity

0

Splice Tray Type Included

No trays

Splicing Capacity, Mass Fusion, maximum

144

Splicing Capacity, Single Fusion, maximum

96

Splicing Capacity, Single Splice, 12 fibers, maximum

96

Splicing Capacity, Single Splice, 6 fibers, maximum

48

Splicing Type, Supported

Mass fusion | Single fusion

Dimensions

Height

240 mm | 9.449 in

760237707 | FOSC-OPGW-B4NT-0/6-NNC

Width	202 mm 7.953 in
Length	730 mm 28.74 in
Main Cable Diameter, maximum	19 mm 0.748 in

Ordering Tree

FOSC - OPGW - XX XXX - X - X X X

Closure size

A4	FOSC 400 A4
B4	FOSC 400 B4

Type of splicing trays

Tray Options		
Closure Size	Splices at Tray edges	Splices at modules
A4	S08, S24, A24	12, 24
B4	S12, S24, A24	12, 24

(S or A for SMOUV or ANT splice protectors)
(S08, S12, S24 European style splice trays)

Pre-installed trays

1, 2 or 3	For A4 closures
1, 2 ...6	For B4 closures

Shot gun protection enclosure

C	With protection enclosure
N	Without protection enclosure

Type of splicing trays

OPGW cable type (*)				
Cable type	Cable dia. (mm)	OPGW cable type (*)		Select
		(A) CC with plastic loose tube	(B) Metal loose tubes only	
OPGW	9-12	7.5	3	A
	12-14	10.5	3	B
	14-16	12.5	3	C
	16-18	14	3	D
FO cable	5-19	N/A	N/A	E

1st cable feed-through

Same options are for 2nd cable feed-through, except option E

Material Specifications

Material Type	Impact-resistant polymer
----------------------	--------------------------

Environmental Specifications

Environmental Space	Above ground
Qualification Standards	IEC 61300, 6 m waterhead

Packaging and Weights

Packaging quantity	1
Packaging Type	Box Carton
Weight, net	18 kg 39.683 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system