760238072 | FOSC450-3DQD1204NN2T-U23

FOSC® 450/D Fiber Optic Splice Closure, Gel Cable sealing, with integrated DWDM, 40 channels + upgrade port, demultiplexing, 2 test ports

- Single-ended, O-ring sealed dome closure for splicing feeder and distribution cables
- Gel cable sealing technology allows easy adding or removing of a wide size range of cables
- Compatible with most common cable types: e.g. loose tube, central core, ribbon fiber
- FOSC splice trays hinged for access to any splice without disturbing other trays
- Closure can be used in aerial, pedestal and underground (up to 5 meters) environments
- Compatible with CommScope's CWDM modules and optical splitter trays

Product Classification

Regional Availability	Latin America | North America
Product Type	Single-ended, round fiber closure
Product Brand	FOSC®
Product Series	FOSC 450

General Specifications

Cable Entry Drop Port Style	Round
Cable Entry Main Port Style	Round
Cable Ports Quantity, total	6 round ports
Cable Sealing Type	Compressed gel
Closure Sealing Type	Dome-to-base clamp with O-ring
Closure Style	Single-ended
Color	Black
Flash Test Valve	None
Ground Feed-through	None
Mounting	Pole | Strand | Wall
Network Area Type	Feeder
Splice Tray Included, quantity	6
Splice Tray Type Included	12-way, heat shrink
Splicing Type, Supported	Mass fusion | Single fusion

Dimensions

COMMSCOPE®

760238072 | FOSC450-3DQD1204NN2T-U23

Length	610 mm	24.016 in
Diameter	180 mm	7.087 in
Diameter, with clamp	232 mm	9.134 in
Main Cable Diameter, maximum	25 mm	0.984 in

Material Specifications

Material Type	Impact-resistant polymer

Environmental Specifications

Environmental Space	Below ground	Buried
Qualification Standards	IEC 61300, 5 m waterhead

Packaging and Weights

Included	Multiplexer (2)
Packaging quantity	1
Packaging Type	Box	Carton
Weight, net	5.5 kg	12.125 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

COMMSCOPE®