FPX-5FRR08-2883



FPX Fiber Optic Termination/Splice Module, 5RU, 19in, Singlemode, 288 fiber, LC/UPC Connector, putty white

Product Classification

Regional Availability Latin America | North America

Portfolio CommScope®
Product Type Fiber patch panel

Product Series FPX

General Specifications

Functionality Patching

Adapter Packs Included, quantity 12

Body Style

Color

Putty white

Color, front

Putty white

Growth Configuration

Fully loaded

Interface, front

LC/UPC

Patching Capacity, maximum

Symmetrical

Putty white

LC/UPC

Rack Type EIA 19 in | EIA 23 in

Rack Units 5

Shelf MovementSlidingTotal Fibers, quantity288Total Ports, quantity288

Dimensions

 Height
 222.25 mm | 8.75 in


 Width
 482.6 mm | 19 in

 Depth
 304.8 mm | 12 in

Ordering Tree



FPX-5FRR08-2883



Material Specifications

Finish Powder coated

Material Type Steel

Optical Specifications

Fiber Mode Singlemode

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C to} +85 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to} +185 \,^{\circ}\text{F})$

Storage Temperature $-40 \,^{\circ}\text{C} \text{ to } +85 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +185 \,^{\circ}\text{F})$

Packaging and Weights

Included Mounting hardware



FPX-5FRR08-2883

Packaging quantity

1

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

