


# OTE200-06MH-NN-S12-B-W



Mini-OTE 200-Series, Optical Terminal Enclosure, 6-port full-size connector, no splitter, black, wall mount

- Optical Terminal Enclosures incorporate hardened connector technology that is designed to withstand the rugged outside plant environment
- Functionality to splice and store feeder cable in the field with the possibility to splice in the field two extra branch cables
- Hardened adapters are factory-terminated and environmentally sealed to ensure rapid plug-and-play drop cable installations
- Integrated external cable fixation guarantees easy, fast and reliable cable manipulations

## Product Classification

Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America
Product Type	Access terminal, without splitter/tap
Product Series	Mini-OTE 200

## General Specifications


Cable Type	No cable (stubless)
Cable, quantity	0
Distribution Type	6 ports
Enclosure Color	Black
Mounting	Handhole   Pole   Wall
Port Type	Hardened full-size SC/APC
Port, quantity	6
Splitter, quantity	0
Stub Type	No tail

## Dimensions


Height	358.5 mm   14.114 in
Width	166 mm   6.535 in
Depth	129.3 mm   5.091 in
Cable Length, stub	0 ft (0 m)

## Dimension Drawing

# OTE200-06MH-NN-S12-B-W



## Ordering Tree



## Material Specifications

**Enclosure Material Type** Glass filled polypropylene (GF-PP)

## Optical Specifications

**Fiber Type** G.652.D

**Operating Wavelength Range** 1260 – 1635 nm

**Attenuation Terminal Connectors, maximum** 0.4 dB

# OTE200-06MH-NN-S12-B-W

Insertion Loss, Terminal Connector, typical	0.16 dB
Return Loss, Connector, minimum	65 dB

## Environmental Specifications

Operating Temperature	-40 °C to +65 °C (-40 °F to +149 °F)
Relative Humidity	5%–100%, condensing
Environmental Space	Above ground   Below ground   Buried
Qualification Standards	IEC 60529, IP68 + 3 m waterhead
UV Resistance	UV stabilized

## Packaging and Weights

Included	Cable termination unit (2)   Enclosure (1)   Fiber pigtail cassette (1)   Splice Cassette (2)
Packaging quantity	1
Packaging Type	Box   Carton


## Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

## Included Products

CW8094-002 TENIO-CTU-L-(10)	– TENIO™ Cable Termination Unit kit
--------------------------------	-------------------------------------

TENIO™ Cable Termination Unit kit



Product Classification

Regional Availability	EMEA
Product Type	Cable termination kit
Product Series	TENIO

Environmental Specifications

Environmental Space	Outdoor
---------------------	---------

Packaging and Weights

Packaging quantity	1
Packaging Type	Bag   Carton

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="https://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

