

CJJGG | IP06-24LUTP-PG2H-PG1S

Base Product



InstaPATCH® Cu GigaSPEED XL® U/UTP LSZH Preterminated Copper Cable, dual row high density RJ45 plug to single row standard density RJ45 plug, 24 links

This product will be discontinued on: January 31, 2025

Product Classification

| | |
|------------------------------|---|
| Regional Availability | Asia Australia/New Zealand EMEA Latin America North America |
| Portfolio | CommScope® |
| Product Type | Copper trunk cable assembly |
| Product Brand | GigaSPEED XL® InstaPATCH® Cu |

General Specifications

| | |
|---------------------------------------|-------------------------|
| ANSI/TIA Category | 6 |
| Cable Type | U/UTP (unshielded) |
| Conductor Type | Solid |
| Interface, Connector A | RJ45 plug |
| Interface Feature, connector A | Dual row High density |
| Interface, Connector B | RJ45 plug |
| Interface Feature, connector B | Single row Standard |
| Link Count | 24 |
| Wiring | T568B |

Dimensions

| | |
|---|---------|
| Cable Assembly Length Range (m) | 2 – 100 |
| Cable Assembly Length Range (ft) | 7 – 328 |

Electrical Specifications

| | |
|-------------------------------|---------|
| dc Resistance, maximum | 0.3 ohm |
| Safety Voltage Rating | 300 V |

CJJGG | IP06-24LUTP-PG2H-PG1S

Ordering Tree

1 2 3 4 5 6 7 8 9 10 11 12
 C A A A C - 1 1 H A B B F 0 5 0

| Cable Type | Connector B | Orientation A | Orientation B |
|---------------------------------------|--|-------------------------|-------------------------|
| A Cat 6A X10D – U/UTP (Plenum) | A Outlet* – Single Row Standard Density | 1 Trident Series Flat | 1 Trident Series Flat |
| B Cat 6A X10D – U/UTP (Riser) | B Outlet* – Dual Row Standard Density | 2 Right Paired Flat | 2 Right Paired Flat |
| C Cat 6A X10D – U/UTP (LSZH) | C Outlet* – Dual Row High Density | 3 Right Series Flat | 3 Right Series Flat |
| D Cat 6A X10D – F/UTP (Plenum) | G RJ45 Plug* – Single Row Standard Density | 4 Left Paired Flat | 4 Left Paired Flat |
| E Cat 6A X10D – F/UTP (Riser) | H RJ45 Plug* – Dual Row Standard Density | 5 Left Series Flat | 5 Left Series Flat |
| F Cat 6A X10D – F/UTP (LSZH) | J RJ45 Plug* – Dual Row High Density | 6 Trident Paired Flat | 6 Trident Paired Flat |
| G Cat 6 XL – U/UTP (Plenum) | N 1100 Module | A Trident Series Angled | A Trident Series Angled |
| H Cat 6 XL – U/UTP (Riser) | R 360 1100 Evolve Module | B Right Paired Angled | B Right Paired Angled |
| J Cat 6 XL – U/UTP (LSZH) | S OneLink 2x6 | C Right Series Angled | C Right Series Angled |
| Q Cat 6A X10D – S/FTP (LSZH) | T OneLink 2x4 | D Left Paired Angled | D Left Paired Angled |
| R Cat 6 – U/UTP Class B Rated (LSZH) | | E Left Series Angled | E Left Series Angled |
| S Cat 6A – U/UTP Class B Rated (LSZH) | | F Trident Paired Angled | F Trident Paired Angled |
| Y Cat 6A X10D SD – U/UTP (Riser) | | | X Not Applicable |

| Connector A | Link | Outlet Color | UOM | Length |
|--|------|------------------|---------|--------|
| A Outlet* – Single Row Standard Density | B 6 | 0 Not Applicable | F Foot | 12 XXX |
| B Outlet* – Dual Row Standard Density | C 8 | 1 Black (BK) | M Meter | |
| C Outlet* – Dual Row High Density | D 12 | 2 Blue (BL) | | |
| G RJ45 Plug* – Single Row Standard Density | E 16 | 8 White (WH) | | |
| H RJ45 Plug* – Dual Row Standard Density | F 18 | | | |
| J RJ45 Plug* – Dual Row High Density | G 24 | | | |
| N 1100 Module | | | | |
| R 360 1100 Evolve Module | | | | |
| S OneLink 2x6 | | | | |
| T OneLink 2x4 | | | | |
| X Unterminated | | | | |

| Bundling | Jacket Color | Labeling |
|---------------|--------------|-----------------|
| H Hook-n-Loop | B White (WH) | A Generic Label |
| S Sleaving | C Slate (SL) | |
| | Z Blue (BL) | |

- Cords > 1m are authorized for use in channels and are an effective standalone method used to connect active devices
- Cords < 1m are also valid elements for use in a channel or as an equipment interconnect, but due to their limited length are not guaranteed to meet component compliance requirements that were developed to assess the quality of longer cords

Environmental Specifications

| | |
|------------------------------|--------------------------------------|
| Operating Temperature | -10 °C to +60 °C (+14 °F to +140 °F) |
| Environmental Space | Low Smoke Zero Halogen (LSZH) |
| Flammability Rating | UL 94 V-0 |

Regulatory Compliance/Certifications

| | |
|---------------|--|
| Agency | Classification |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |

Included Products

- 2071E-4/23 – GigaSPEED XL® 2071E ETL Verified Category 6 U/UTP Cable, plenum, 4 pair count

2071E-4/23



GigaSPEED XL® 2071E ETL Verified Category 6 U/UTP Cable, plenum, 4 pair count

Product Classification

| | |
|------------------------------|---|
| Regional Availability | Asia Australia/New Zealand EMEA Latin America North America |
| Portfolio | SYSTIMAX® |
| Product Type | Twisted pair cable |
| Product Brand | GigaSPEED XL® |

General Specifications

| | |
|--------------------------------|---|
| Product Number | 2071E |
| ANSI/TIA Category | 6 |
| Cable Component Type | Horizontal |
| Cable Type | U/UTP (unshielded) |
| Conductor Type, singles | Solid |
| Conductors, quantity | 8 |
| Pairs, quantity | 4 |
| Separator Type | Bisector |
| Transmission Standards | ANSI/TIA-568.2-D CENELEC EN 50288-6-1 ISO/IEC 11801 Class E |

Dimensions

| | |
|--------------------------------------|---------------------|
| Diameter Over Jacket, nominal | 5.74 mm 0.226 in |
| Jacket Thickness | 0.559 mm 0.022 in |
| Conductor Gauge, singles | 23 AWG |

Cross Section Drawing



Electrical Specifications

| | |
|--|---|
| dc Resistance Unbalance, maximum | 5 % |
| dc Resistance, maximum | 7.61 ohms/100 m 2.32 ohms/100 ft |
| Dielectric Strength, minimum | 1500 Vac 2500 Vdc |
| Mutual Capacitance at Frequency | 5.6 nF/100 m @ 1 kHz |
| Nominal Velocity of Propagation (NVP) | 71 % |
| Operating Frequency, maximum | 300 MHz |
| Operating Voltage, maximum | 80 V |
| Remote Powering | Fully complies with the recommendations set forth by IEEE 802.3bt (Type 4) for the safe delivery of power over LAN cable when installed according to ISO/IEC 14763-2, CENELEC EN 50174-1, CENELEC EN 50174-2 or TIA TSB-184-A |

Material Specifications

| | |
|----------------------------|----------------------------|
| Conductor Material | Bare copper |
| Insulation Material | FEP Polyolefin |
| Jacket Material | PVC |
| Separator Material | Flame retardant polyolefin |

Mechanical Specifications

2071E-4/23

Pulling Tension, maximum 11.34 kg | 25 lb

Environmental Specifications

Installation temperature 0 °C to +60 °C (+32 °F to +140 °F)

Operating Temperature -20 °C to +60 °C (-4 °F to +140 °F)

Environmental Space Plenum

Temperature Rating, UL 75 °C | 167 °F

Flame Test Method CMP/FT6

Smoke Test Method CMP/FT6

Packaging and Weights

Cable weight 43.157 kg/km | 29 lb/kft

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |