AFGSFSGL1

Base Product



Fiber Patch Cord, Singlemode G.657.A2, Grade B, SC/UPC to SC/APC, Simplex, 1.6 mm LSZH jacket

Product Classification


Regional Availability	Asia Australia/New Zealand Europe Latin America Middle East /Africa North America
Portfolio	CommScope®
Product Type	Fiber patch cord, simplex
Product Series	AFG
General Specifications	
Connector A, quantity	1
Color, connector A	Blue
Connector B, quantity	1
Color, connector B	Green
Interface, Connector A	SC/UPC
Interface, Connector B	SC/APC
Total Fibers, quantity	1
Transmission Standards	IEC 61755
Dimensions	
Cable Assembly Length Range (m)	1 – 999
Cable Assembly Length Range (ft)	1 – 999
Diameter Over Jacket	1.6 mm 0.063 in

Ordering Tree

Page 1 of 9



AFGSFSGL1



Mechanical Specifications

Minimum Bend Radius, loaded	50 mm 1.969 in
Minimum Bend Radius, unloaded	30 mm 1.181 in
Tensile Load, long term, maximum	33 N 7.419 lbf
Tensile Load, short term, maximum	110 N 24.729 lbf
Cable Crush Resistance, maximum	3.5 N/mm 19.986 lb/in
Mating Durability, maximum	0.2 dB @ 500 cycles

Optical Specifications

Singlemode
G.657.A2, TeraSPEED®
IEC Random Mating Grade B
0.25 dB
0.25 dB
50 dB
65 dB

Environmental Specifications

Operating Temperature	-20 °C to +60 °C (-4 °F to +140 °F)
Environmental Space	Dual Rated LSZH/Riser
Packaging and Weights	
Packaging quantity	1

Regulatory Compliance/Certifications

Page 2 of 9



AFGSFSGL1

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted
50	

Included Products

460159816	-	Fiber indoor cable, Low Smoke Zero Halogen YL G.657 .A2, 1 fiber, Singlemode G.657.A2, 1.6 mm diameter, Feet jacket marking, Yellow jacket color
860645407	_	TeraSPEED® SC/UPC Connector Kit for 2.0 mm Fiber, Singlemode, Blue, Short Boot
860645408	_	TeraSPEED® SC/APC Connector Kit for 2.0 mm Fiber, Singlemode, Green, Short Boot
* Footpotoc		

* Footnotes

Page 3 of 9



Fiber indoor cable, Low Smoke Zero Halogen YL G.657 .A2, 1 fiber, Singlemode G.657.A2, 1.6 mm diameter, Feet jacket marking, Yellow jacket color

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America	
Portfolio	CommScope®	
Product Type	Fiber indoor cable	
Product Series	L-MP	

General Specifications

Cable Type	Cordage
Inner Jacket Color	Yellow
Jacket Color	Yellow
Jacket Marking	Feet
Total Fiber Count	1

Dimensions

Diameter Over Jacket	1.6 mm 0.063 in

Optical Specifications

Environmental Specifications

Installation temperature	-20 °C to +60 °C (-4 °F to +140 °F)
Operating Temperature	-20 °C to +70 °C (-4 °F to +158 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Environmental Space	Low Smoke Zero Halogen (LSZH)

Environmental Test Specifications

Heat Age	-20 °C to +85 °C (-4 °F to +185 °F)
Low High Bend	-20 °C to +70 °C (-4 °F to +158 °F)
Temperature Cycle	-20 °C to +70 °C (-4 °F to +158 °F)

Packaging and Weights

Page 4 of 9



460159816

Cable weight

3.6 kg/km | 2.419 lb/kft

Regulatory Compliance/Certifications

Agency

Classification

Compliant

CHINA-ROHS REACH-SVHC Below maximum concentration value Compliant as per SVHC revision on www.commscope.com/ProductCompliance Compliant

ROHS UK-ROHS



* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable

Page 5 of 9



TeraSPEED® SC/UPC Connector Kit for 2.0 mm Fiber, Singlemode, Blue, Short Boot

Product Classification

Regional Availability Portfolio Product Type Product Brand	Asia Australia/New Zealand EMEA Latin America North America CommScope® Fiber connector TeraSPEED®
General Specifications	
Color	Blue
Interface	SC/UPC
Dimensions	
Length	50.3 mm 1.98 in
Compatible Cable Diameter	2 mm 0.079 in
Material Specifications	
Ferrule Material	Zirconia
Mechanical Specifications	
Cable Retention Strength, maximum	11.24 lb @ 0 °
Optical Specifications	
Fiber Type	G.652.D and G.657.A1, TeraSPEED® OS2
Optical Components Standard	ANSI/TIA-568-C.3 GR-326-CORE
Insertion Loss, ULL, maximum	0.25 dB
Return Loss, minimum	50 dB
Packaging and Weights	

Packaging quantity

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS

Below maximum concentration value

1

Page 6 of 9



860645407

REACH-SVHC

ROHS

UK-ROHS

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

Compliant Compliant

Page 7 of 9



TeraSPEED® SC/APC Connector Kit for 2.0 mm Fiber, Singlemode, Green, Short Boot

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber connector
Product Brand	TeraSPEED®
General Specifications	
Color	Green
Interface	SC/UPC
Dimensions	
Length	50.3 mm 1.98 in
Compatible Cable Diameter	2 mm 0.079 in
Material Specifications	
Ferrule Material	Zirconia
Mechanical Specifications	
Cable Retention Strength, maximum	11.24 lb @ 0 °
Optical Specifications	
Fiber Type	G.652.D and G.657.A1, TeraSPEED® OS2
Optical Components Standard	ANSI/TIA-568-C.3 GR-326-CORE
Insertion Loss, ULL, maximum	0.25 dB
Return Loss, minimum	50 dB
Packaging and Weights	

Packaging quantity

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS

Below maximum concentration value

1

Page 8 of 9



860645408

REACH-SVHC

ROHS

UK-ROHS

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

Compliant Compliant



