


# FAWL5UCOC

## Base Product



Singlemode LC/UPC Keyed Orange to Unconnectorized, Fiber Pigtail, 0.9 mm Tight Buffer, 12-Fiber Kit Blue - Aqua (1-12)

## Product Classification

|                              |  |
|------------------------------|--|
| <b>Regional Availability</b> | Asia   Australia/New Zealand   Europe   Latin America   Middle East /Africa   North America                              |
| <b>Portfolio</b>             | CommScope®   |
| <b>Product Type</b>          | Fiber pigtail, unjacketed  |
| <b>Product Brand</b>         | SYSTIMAX InstaPATCH® 360   |
| <b>Product Series</b>        | FAW  |
| <b>Ordering Note</b>         | For lengths greater than 999 ft (304 m), orders must be in meters   Minimum length may vary based on cable configuration |

## General Specifications


|                                       |        |
|---------------------------------------|--------|
| <b>Color, boot A</b>                  | Blue   |
| <b>Color, connector A</b>             | Orange |
| <b>Interface, Connector A</b>         | LC/UPC |
| <b>Interface Feature, connector A</b> | Keyed  |
| <b>Total Fibers, quantity</b>         | 12     |

## Dimensions

|   |        |
|---|--------|
| <b>Cable Assembly Length Range (m)</b>  | 1 – 20 |
| <b>Cable Assembly Length Range (ft)</b> | 1 – 66 |

## Ordering Tree

# FAWL5UCOC



## Mechanical Specifications

**Cable Retention Strength, maximum** 1.00 lb @ 0° | 1.00 lb @ 90°

## Optical Specifications

**Fiber Mode** Singlemode

**Fiber Type** G.652.D | G.657.A1, TeraSPEED®

## Environmental Specifications

**Operating Temperature** -10 °C to +60 °C (+14 °F to +140 °F)

**Environmental Space** Unrated

## Regulatory Compliance/Certifications

### Agency

ISO 9001:2015



### Classification

Designed, manufactured and/or distributed under this quality management system

## Included Products

- 760102988 SFC-LCR-09-KOR – TeraSPEED® Behind The Wall Keyed LC Connector for 0.9 mm Fiber, Singlemode, orange
- X-TB-8W – TeraSPEED® 900µm Tight Buffered Fiber