

CGJNG | IP06-24PUTP-PG2H-1100L

Base Product



InstaPATCH® Cu GigaSPEED XL® U/UTP Plenum Preterminated Copper Cable, dual row high density RJ45 plug to 1100 module, 24 links

This product will be discontinued on: January 31, 2025

Product Classification

| | |
|-----------------------|---|
| Regional Availability | Asia Australia/New Zealand EMEA Latin America North America |
| Portfolio | CommScope® |
| Product Type | Copper trunk cable assembly |
| Product Brand | GigaSPEED XL® InstaPATCH® Cu |

General Specifications

| | |
|--------------------------------|-------------------------|
| ANSI/TIA Category | 6 |
| Cable Type | U/UTP (unshielded) |
| Conductor Type | Solid |
| Interface, Connector A | RJ45 plug |
| Interface Feature, connector A | Dual row High density |
| Interface, Connector B | 1100 module |
| Interface Feature, connector B | Standard |
| Link Count | 24 |
| Wiring | T568B |

Dimensions

| | |
|----------------------------------|--------|
| Cable Assembly Length Range (m) | 2 – 30 |
| Cable Assembly Length Range (ft) | 7 – 98 |

Electrical Specifications

| | |
|------------------------|---------|
| dc Resistance, maximum | 0.3 ohm |
| Safety Voltage Rating | 300 V |

Ordering Tree

123456789101112

CAC-11HABBF050

Cable Type

| | |
|---|-------------------------------------|
| A | Cat 6A X10D – U/UTP (Plenum) |
| B | Cat 6A X10D – U/UTP (Riser) |
| C | Cat 6A X10D – U/UTP (LSZH) |
| D | Cat 6A X10D – F/UTP (Plenum) |
| E | Cat 6A X10D – F/UTP (Riser) |
| F | Cat 6A X10D – F/UTP (LSZH) |
| G | Cat 6 XL – U/UTP (Plenum) |
| H | Cat 6 XL – U/UTP (Riser) |
| J | Cat 6 XL – U/UTP (LSZH) |
| Q | Cat 6A X10D – S/FTP (LSZH) |
| R | Cat 6 – U/UTP Class B Rated (LSZH) |
| S | Cat 6A – U/UTP Class B Rated (LSZH) |
| Y | Cat 6A X10D SD – U/UTP (Riser) |

Connector A

| | |
|---|--|
| A | Outlet* – Single Row Standard Density |
| B | Outlet* – Dual Row Standard Density |
| C | Outlet* – Dual Row High Density |
| G | RJ45 Plug* – Single Row Standard Density |
| H | RJ45 Plug* – Dual Row Standard Density |
| J | RJ45 Plug* – Dual Row High Density |
| N | 1100 Module |
| R | 360 1100 Evolve Module |
| S | OneLink 2x6 |
| T | OneLink 2x4 |
| X | Unterminated |

Connector B

| | |
|---|--|
| A | Outlet* – Single Row Standard Density |
| B | Outlet* – Dual Row Standard Density |
| C | Outlet* – Dual Row High Density |
| G | RJ45 Plug* – Single Row Standard Density |
| H | RJ45 Plug* – Dual Row Standard Density |
| J | RJ45 Plug* – Dual Row High Density |
| N | 1100 Module |
| R | 360 1100 Evolve Module |
| S | OneLink 2x6 |
| T | OneLink 2x4 |

Orientation A

| | |
|---|-----------------------|
| 1 | Trident Series Flat |
| 2 | Right Paired Flat |
| 3 | Right Series Flat |
| 4 | Left Paired Flat |
| 5 | Left Series Flat |
| 6 | Trident Paired Flat |
| A | Trident Series Angled |
| B | Right Paired Angled |
| C | Right Series Angled |
| D | Left Paired Angled |
| E | Left Series Angled |
| F | Trident Paired Angled |

Orientation B

| | |
|---|-----------------------|
| 1 | Trident Series Flat |
| 2 | Right Paired Flat |
| 3 | Right Series Flat |
| 4 | Left Paired Flat |
| 5 | Left Series Flat |
| 6 | Trident Paired Flat |
| A | Trident Series Angled |
| B | Right Paired Angled |
| C | Right Series Angled |
| D | Left Paired Angled |
| E | Left Series Angled |
| F | Trident Paired Angled |
| X | Not Applicable |

Link

| | |
|---|----|
| B | 6 |
| C | 8 |
| D | 12 |
| E | 16 |
| F | 18 |
| G | 24 |

Outlet Color

| | |
|---|----------------|
| 0 | Not Applicable |
| 1 | Black (BK) |
| 2 | Blue (BL) |
| 8 | White (WH) |

UOM

| | |
|---|-------|
| F | Foot |
| M | Meter |

Length

| | |
|----|-----|
| 12 | XXX |
|----|-----|

Bundling

| | |
|---|-------------|
| H | Hook-n-loop |
| S | Sleeving |

Jacket Color

| | |
|---|------------|
| 8 | White (WH) |
| C | Slate (SL) |
| Z | Blue (BL) |

Labeling

| | |
|---|---------------|
| A | Generic Label |
|---|---------------|

Cords > 1m are authorized for use in channels and are an effective standalone method used to connect active devices

Cords < 1m are also valid elements for use in a channel or as an equipment interconnect, but due to their limited length are not guaranteed to meet component compliance requirements that were developed to assess the quality of longer cords

Environmental Specifications

| | |
|-----------------------|--------------------------------------|
| Operating Temperature | -10 °C to +60 °C (+14 °F to +140 °F) |
| Environmental Space | Plenum |
| Flammability Rating | UL 94 V-0 |

Regulatory Compliance/Certifications

| | |
|---------------|--|
| Agency | Classification |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |


Included Products

| | |
|------------|---|
| 2071E-4/23 | – GigaSPEED XL® 2071E ETL Verified Category 6 U/UTP Cable, plenum, 4 pair count |
|------------|---|

Page 2 of 5

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see <https://www.commscope.com/trademarks>. All product names, trademarks and registered trademarks are property of their respective owners. Revised: August 15, 2024

COMMScope®



GigaSPEED XL® 2071E ETL Verified Category 6 U/UTP Cable, plenum, 4 pair count

Product Classification

| | |
|-----------------------|---|
| Regional Availability | Asia Australia/New Zealand EMEA Latin America North America |
| Portfolio | SYSTIMAX® |
| Product Type | Twisted pair cable |
| Product Brand | GigaSPEED XL® |

General Specifications

| | |
|-------------------------|---|
| Product Number | 2071E |
| ANSI/TIA Category | 6 |
| Cable Component Type | Horizontal |
| Cable Type | U/UTP (unshielded) |
| Conductor Type, singles | Solid |
| Conductors, quantity | 8 |
| Pairs, quantity | 4 |
| Separator Type | Bisector |
| Transmission Standards | ANSI/TIA-568.2-D CENELEC EN 50288-6-1 ISO/IEC 11801 Class E |

Dimensions

| | |
|-------------------------------|---------------------|
| Diameter Over Jacket, nominal | 5.74 mm 0.226 in |
| Jacket Thickness | 0.559 mm 0.022 in |
| Conductor Gauge, singles | 23 AWG |

Cross Section Drawing



Electrical Specifications

| | |
|---------------------------------------|---|
| dc Resistance Unbalance, maximum | 5 % |
| dc Resistance, maximum | 7.61 ohms/100 m 2.32 ohms/100 ft |
| Dielectric Strength, minimum | 1500 Vac 2500 Vdc |
| Mutual Capacitance at Frequency | 5.6 nF/100 m @ 1 kHz |
| Nominal Velocity of Propagation (NVP) | 71 % |
| Operating Frequency, maximum | 300 MHz |
| Operating Voltage, maximum | 80 V |
| Remote Powering | Fully complies with the recommendations set forth by IEEE 802.3bt (Type 4) for the safe delivery of power over LAN cable when installed according to ISO/IEC 14763-2, CENELEC EN 50174-1, CENELEC EN 50174-2 or TIA TSB-184-A |

Material Specifications

| | |
|---------------------|----------------------------|
| Conductor Material | Bare copper |
| Insulation Material | FEP Polyolefin |
| Jacket Material | PVC |
| Separator Material | Flame retardant polyolefin |

Mechanical Specifications

2071E-4/23

Pulling Tension, maximum 11.34 kg | 25 lb

Environmental Specifications

| | |
|---------------------------------|-------------------------------------|
| Installation temperature | 0 °C to +60 °C (+32 °F to +140 °F) |
| Operating Temperature | -20 °C to +60 °C (-4 °F to +140 °F) |
| Environmental Space | Plenum |
| Temperature Rating, UL | 75 °C 167 °F |
| Flame Test Method | CMP/FT6 |
| Smoke Test Method | CMP/FT6 |

Packaging and Weights

Cable weight 43.157 kg/km | 29 lb/kft

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |