UGVMPMXAM

Base Product



Ultra Low Loss (ULL) OM5, MP012 Unpinned to MP012 Pinned, Fiber Trunk Cable Assembly, 144-Fiber, Plenum

Product Classification

Regional Availability	Asia Australia/New Zealand China Europe India Latin America Middle East/Africa North America
Portfolio	CommScope®
Product Type	Fiber trunk cable assembly
Product Brand	SYSTIMAX ULL
Ordering Note	For additional jacket colors, please contact a CommScope Sales Representative For lengths greater than 999 ft (304 m), orders must be in meters Minimum length may vary based on cable configuration
General Specifications	
Color, boot A	Black
Color, connector A	Lime green
Color, boot B	Black
Color, connector B	Lime green
Construction Type	Stranded
Furcation Color	Lime green
Interface, Connector A	MPO-12/UPC Female
Interface, Connector B	MPO-12/UPC Male
Jacket Color	Lime green
Polarity	Method B Enhanced (ULL)
Fibers per Subunit, quantity	12
Total Fibers, quantity	144

Dimensions

Breakout Length	33 in
Cable Assembly Length Range (m)	3 – 999
Cable Assembly Length Range (ft)	10 - 999

Page 1 of 10



UGVMPMXAM

Ordering Tree

Jacket Color Breakout Length / Option		L	ength		
J	Lime green	Α	33 inch breakout, no gland		
		В	33 inch breakout, with gland		
		С	33 inch breakout, with pulling grip		
		1	33/60 inch breakout, no gland		
		2	33/60 inch breakout, with gland on side A	l	лом
		3	33/60 inch breakout, with pulling grip and gland on side A	F	Feet Meter
		4	33/120 inch breakout, no gland		
		5	33/120 inch breakout, with gland on side A		
		6	33/120 inch breakout, with pulling grip and gland on side A		
		т	33 inch breakout, with gland on side A		
		U	33 inch breakout, with pulling grip and gland on side A		
		v	60 inch breakout, no gland		
		W	60 inch breakout, with pulling grip		
		Ρ	120 inch breakout, no gland		
		Q	120 inch breakout, with pulling grip		

Mechanical Specifications

Cable Retention Strength, maximum	11.24 lb @ 0 ° 4.40 lb @ 90 °
Optical Specifications	
Fiber Mode	Multimode
Fiber Type	OM5, LazrSPEED®

Environmental Specifications

Operating Temperature

-10 °C to +60 °C (+14 °F to +140 °F)

Page 2 of 10



UGVMPMXAM

Environmental Space

Indoor | Plenum

Regulatory Compliance/Certifications

Agency ANATEL

Compliant

Classification

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system



Included Products

760223024 P-144-MP-5G-F12LM	-	Fiber indoor cable, LazrSPEED® Plenum MPO Trunk, 144 fiber multi-unit with 12 fiber subunits, Multimode OM5, Gel-free, Feet jacket marking, Lime green jacket color
860617232	-	MP012, ULTRA LOW LOSS, FEMALE, OM5, LIME, 3mm
860617240	-	MP012, ULTRA LOW LOSS, MALE, OM5, LIME, 3mm



760223024 | P-144-MP-5G-F12LM



Fiber indoor cable, LazrSPEED® Plenum MPO Trunk, 144 fiber multi-unit with 12 fiber subunits, Multimode OM5, Gel-free, Feet jacket marking, Lime green jacket color

Product Classification


Regional Availability	Asia Australia/New Zealand Latin America Middle East /Africa North America
Portfolio	CommScope®
Product Type	Fiber indoor cable
Product Series	P-MP
General Specifications	
Cable Type	MPO trunk cable
Construction Type	Non-armored
Subunit Type	Gel-free
Jacket Color	Lime green
Jacket Marking	Feet
Subunit, quantity	12
Fibers per Subunit, quantity	12
Total Fiber Count	144
Dimensions	
Buffer Tube/Subunit Diameter	3 mm 0.118 in
Diameter Over Jacket	14.12 mm 0.556 in

Representative Image

Page 4 of 10



760223024 | P-144-MP-5G-F12LM



Mechanical Specifications

Minimum Bend Radius, loaded	197 mm 7.756 in
Minimum Bend Radius, unloaded	131 mm 5.157 in
Tensile Load, long term, maximum	400 N 89.924 lbf
Tensile Load, short term, maximum	1335 N 300.12 lbf
Compression	10 N/mm 57.101 lb/in
Compression Test Method	FOTP-41 IEC 60794-1 E3
Flex	300 cycles
Flex Test Method	FOTP-104 IEC 60794-1 E6
Impact	0.74 N-m 6.55 in lb
Impact Test Method	FOTP-25 IEC 60794-1 E4
Strain	See long and short term tensile loads
Strain Test Method	FOTP-33 IEC 60794-1 E1
Twist	10 cycles
Twist Test Method	FOTP-85 IEC 60794-1 E7
Vertical Rise, maximum	250 m 820.21 ft
Optical Specifications	

Fiber Type

OM5, LazrSPEED® wideband | OM5, LazrSPEED® wideband

Environmental Specifications

Installation temperature	0 °C to +70 °C (+32 °F to +158 °F)
Operating Temperature	0 °C to +70 °C (+32 °F to +158 °F)

Page 5 of 10



760223024 | P-144-MP-5G-F12LM

Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Cable Qualification Standards	ANSI/ICEA S-83-596 Telcordia GR-409
Environmental Space	Plenum
Flame Test Listing	NEC OFNP (ETL) and c(ETL)
Flame Test Method	NFPA 130 NFPA 262

Environmental Test Specifications

Heat Age	0 °C to +85 °C (+32 °F to +185 °F)
Heat Age Test Method	IEC 60794-1 F9
Low High Bend	0 °C to +70 °C (+32 °F to +158 °F)
Low High Bend Test Method	FOTP-37 IEC 60794-1 E11
Temperature Cycle	0 °C to +70 °C (+32 °F to +158 °F)
Temperature Cycle Test Method	FOTP-3 IEC 60794-1 F1

Packaging and Weights

Cable weight

163 kg/km | 109.531 lb/kft

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable

Page 6 of 10

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: February 7, 2025

COMMSCOPE°



Product Classification

MP012, ULTRA LOW LOSS, FEMALE, OM5, LIME, 3mm

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber connector
Product Brand	LazrSPEED®
General Specifications	
Color	Lime green
Color, boot	Black
Ferrule Geometry	Flat
Interface	MPO/UPC Female
Interface Feature	Unpinned
Total Fiber Count	12
Dimensions	
Length	60.1 mm 2.366 in
Compatible Cable Diameter	3 mm 0.118 in
Material Specifications	
Ferrule Material	Polymer
Mechanical Specifications	
Cable Retention Strength, maximum	11.24 lb @ 0 °
Optical Specifications	
Fiber Mode	Multimode
Fiber Type	OM5, LazrSPEED® wideband
Insertion Loss Change, mating	0.3 dB
Optical Components Standard	ANSI/TIA-568-C.3

Page 7 of 10



Insertion Loss Change, temperature	0.3 dB
Insertion Loss, maximum	0.2 dB
Return Loss, minimum	27 dB

Packaging and Weights

Packaging quantity

1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

* Footnotes

Insertion Loss Change, mating	TIA-568: Maximum insertion loss change after 500 matings
Insertion Loss Change, temperature	Maximum insertion loss change from -10 °C to +60 °C (+14 °F to +140 °F)

Page 8 of 10





Product Classification

MP012, ULTRA LOW LOSS, MALE, OM5, LIME, 3mm

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber connector
Product Brand	LazrSPEED®
General Specifications	
Color	Lime green
Color, boot	Black
Ferrule Geometry	Flat
Interface	MPO/UPC Male
Interface Feature	Pinned
Total Fiber Count	12
Dimensions	
Length	60.1 mm 2.366 in
Compatible Cable Diameter	3 mm 0.118 in
Material Specifications	
Ferrule Material	Polymer
Mechanical Specifications	
Cable Retention Strength, maximum	11.24 lb @ 0 °
Optical Specifications	
Fiber Mode	Multimode
Fiber Type	OM5, LazrSPEED® wideband
Insertion Loss Change, mating	0.3 dB
Optical Components Standard	ANSI/TIA-568-C.3

Page 9 of 10



Insertion Loss Change, temperature	0.3 dB
Insertion Loss, maximum	0.2 dB
Return Loss, minimum	27 dB

Packaging and Weights

Packaging quantity

1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant
50	

* Footnotes

Insertion Loss Change, mating	TIA-568: Maximum insertion loss change after 500 matings
Insertion Loss Change, temperature	Maximum insertion loss change from -10 °C to +60 °C (+14 °F to +140 °F)

Page 10 of 10

