## UGVMXMXAH

#### **Base Product**



Ultra Low Loss (ULL) OM5 MPO12 (Pinned) to MPO12 (Pinned), Fiber Trunk Cable Assembly, 48-Fiber, Plenum

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | China | Europe | India | Latin

America | Middle East/Africa | North America

Portfolio CommScope®

Product Type Fiber trunk cable assembly

Product Brand SYSTIMAX ULL

Ordering Note For lengths greater than 999 ft (304 m), orders must be in meters | Minimum length

may vary based on cable configuration

## General Specifications

Color, boot A Black

Color, connector A Lime green

Color, boot B Black

Color, connector BLime greenConstruction TypeStrandedFurcation ColorLime green

 Interface, Connector A
 MPO-12/UPC Male

 Interface, Connector B
 MPO-12/UPC Male

Jacket Color Lime green

Polarity Method B Enhanced (ULL)

Fibers per Subunit, quantity 12

Total Fibers, quantity 48

**Dimensions** 

Breakout Length 33 in

**COMMSCOPE®** 

## UGVMXMXAH


Cable Assembly Length Range (m)

3 – 999

Cable Assembly Length Range (ft)

10 - 999

## Ordering Tree



### Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0 ° | 4.40 lb @ 90 °

**Optical Specifications** 

**Fiber Mode** Multimode

**Fiber Type** OM5, LazrSPEED®

**Environmental Specifications** 

**COMMSCOPE®** 

## UGVMXMXAH

**Operating Temperature**  $-10 \,^{\circ}\text{C} \text{ to } +60 \,^{\circ}\text{C} \text{ (+14 }^{\circ}\text{F to } +140 \,^{\circ}\text{F)}$ 

Environmental Space Indoor | Plenum

### Regulatory Compliance/Certifications

Agency Classification

ANATEL Compliant

CHINA-ROHS Above maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system
REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted





760222992 – Fiber indoor cable, LazrSPEED® Plenum MPO Trunk, 48 fiber multi-unit with 12 fiber subunits, P-048-MP-5G-F12LM Multimode OM5, Gel-free, Feet jacket marking, Lime green jacket color

860617240 - MPO12, ULTRA LOW LOSS, MALE, OM5, LIME, 3mm



# 760222992 | P-048-MP-5G-F12LM



Fiber indoor cable, LazrSPEED® Plenum MPO Trunk, 48 fiber multi-unit with 12 fiber subunits, Multimode OM5, Gel-free, Feet jacket marking, Lime green jacket color

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | Latin America | Middle East

/Africa | North America

Portfolio CommScope®

Product Type Fiber indoor cable

**Product Series** P-MP

General Specifications

Cable Type MPO trunk cable

Construction Type Non-armored

Subunit Type Gel-free

Jacket Color Lime green

Jacket Marking Feet

Subunit, quantity 4

Fibers per Subunit, quantity 12

Total Fiber Count 48

**Dimensions** 


**Buffer Tube/Subunit Diameter** 3 mm | 0.118 in

**Diameter Over Jacket** 9.1 mm | 0.358 in

Representative Image



## 760222992 | P-048-MP-5G-F12LM



### Mechanical Specifications

Minimum Bend Radius, loaded 136 mm | 5.354 in

Minimum Bend Radius, unloaded 91 mm | 3.583 in

Tensile Load, long term, maximum 400 N | 89.924 lbf

Tensile Load, short term, maximum 1335 N | 300.12 lbf

**Compression** 10 N/mm | 57.101 lb/in

Compression Test Method FOTP-41 | IEC 60794-1 E3

Flex 300 cycles

Flex Test Method FOTP-104 | IEC 60794-1 E6

**Impact** 0.74 N-m | 6.55 in lb

Impact Test Method FOTP-25 | IEC 60794-1 E4

**Strain** See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

**Vertical Rise, maximum** 500 m | 1,640.42 ft

**Optical Specifications** 

Fiber Type OM5, LazrSPEED® wideband | OM5, LazrSPEED® wideband

### **Environmental Specifications**

Installation temperature  $0 \,^{\circ}\text{C to} + 70 \,^{\circ}\text{C (+32 °F to} + 158 \,^{\circ}\text{F)}$ Operating Temperature  $0 \,^{\circ}\text{C to} + 70 \,^{\circ}\text{C (+32 °F to} + 158 \,^{\circ}\text{F)}$ 

Page 5 of 8



# 760222992 | P-048-MP-5G-F12LM

Storage Temperature  $-40 \,^{\circ}\text{C}$  to  $+70 \,^{\circ}\text{C}$  ( $-40 \,^{\circ}\text{F}$  to  $+158 \,^{\circ}\text{F}$ )

Cable Qualification Standards ANSI/ICEA S-83-596 | Telcordia GR-409

Environmental Space Plenum

**Flame Test Listing** NEC OFNP (ETL) and c(ETL)

Flame Test Method NFPA 130 | NFPA 262

**Environmental Test Specifications** 

**Heat Age** 0 °C to +85 °C (+32 °F to +185 °F)

**Heat Age Test Method** IEC 60794-1 F9

**Low High Bend** 0 °C to +70 °C (+32 °F to +158 °F)

**Low High Bend Test Method** FOTP-37 | IEC 60794-1 E11

**Temperature Cycle**  $0 \,^{\circ}\text{C to } +70 \,^{\circ}\text{C (+32 °F to } +158 \,^{\circ}\text{F)}$ 

**Temperature Cycle Test Method** FOTP-3 | IEC 60794-1 F1

Packaging and Weights

 Cable weight
 76 kg/km | 51.07 lb/kft

## Regulatory Compliance/Certifications

#### Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



#### \* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable





#### MPO12, ULTRA LOW LOSS, MALE, OM5, LIME, 3mm

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

 Portfolio
 CommScope®

 Product Type
 Fiber connector

 Product Brand
 LazrSPEED®

General Specifications

ColorLime greenColor, bootBlackFerrule GeometryFlat

Interface MPO/UPC Male

Interface Feature Pinned

Total Fiber Count 12

**Dimensions** 

Length60.1 mm | 2.366 inCompatible Cable Diameter3 mm | 0.118 in

Material Specifications

Ferrule Material Polymer

Mechanical Specifications

Cable Retention Strength, maximum  $11.24 \text{ lb} @ 0 ^{\circ}$ 

**Optical Specifications** 

**Fiber Mode** Multimode

**Fiber Type** OM5, LazrSPEED® wideband

**Insertion Loss Change, mating** 0.3 dB

Optical Components Standard ANSI/TIA-568-C.3

Page 7 of 8

## 860617240

Insertion Loss Change, temperature0.3 dBInsertion Loss, maximum0.2 dBReturn Loss, minimum27 dB

### Packaging and Weights

Packaging quantity 1

### Regulatory Compliance/Certifications

#### Agency Classification

CHINA-ROHS Above maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted

UK-ROHS Compliant



#### \* Footnotes

**Insertion Loss Change, mating**TIA-568: Maximum insertion loss change after 500 matings

**Insertion Loss Change, temperature** Maximum insertion loss change from -10 °C to +60 °C (+14 °F to +140 °F)

