

# CHRXF | IP06-18RUTP-1100E-BLUNT

Base Product



InstaPATCH® Cu GigaSPEED XL® U/UTP Riser Preterminated Copper Cable, 360 1100 Evolve module to unterminated, 18 links

This product will be discontinued on: January 31, 2025

## Product Classification

Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America   North America
Portfolio	CommScope®
Product Type	Copper trunk cable assembly
Product Brand	GigaSPEED XL®   InstaPATCH® Cu

## General Specifications

ANSI/TIA Category	6
Cable Type	U/UTP (unshielded)
Conductor Type	Solid
Interface, Connector A	360 1100 Evolve module
Interface Feature, connector A	Standard
Interface, Connector B	Unterminated
Link Count	18
Wiring	T568B

## Dimensions

Cable Assembly Length Range (m)	2 – 90
Cable Assembly Length Range (ft)	7 – 295

## Electrical Specifications

dc Resistance, maximum	0.3 ohm
Safety Voltage Rating	300 V

## Ordering Tree

# CHRXF | IP06-18RUTP-1100E-BLUNT

123456789101112

C A A A C - 1 1 H A B B F 0 5 0

Cable Type

1

A

Cat 6A X10D – U/UTP (Plenum)

B

Cat 6A X10D – U/UTP (Riser)

C

Cat 6A X10D – U/UTP (LSZH)

D

Cat 6A X10D – F/UTP (Plenum)

E

Cat 6A X10D – F/UTP (Riser)

F

G

H

J

Q

R

S

Y

Connector B

3

A

Outlet\* – Single Row Standard Density

B

Outlet\* – Dual Row Standard Density

C

Outlet\* – Dual Row High Density

G

H

J

N

R

S

T

Orientation A

5

1

Trident Series Flat

2

Right Paired Flat

3

Right Series Flat

4

5

6

A

B

C

D

E

F

Orientation B

6

1

Trident Series Flat

2

Right Paired Flat

3

Right Series Flat

4

5

6

A

B

C

D

E

F

X

Connector A

2

A

Outlet\* – Single Row Standard Density

B

Outlet\* – Dual Row Standard Density

C

Outlet\* – Dual Row High Density

G

H

J

N

R

S

T

X

Link

4

B

6

C

8

D

12

E

F

G

Outlet Color

9

0

Not Applicable

1

Black (BK)

2

Blue (BL)

8

Jacket Color

10

8

White (WH)

C

Slate (SL)

Z

Blue (BL)

UOM

11

F

Foot

M

Meter

Length

12

XXX

Cords > 1m are authorized for use in channels and are an effective standalone method used to connect active devices

Cords < 1m are also valid elements for use in a channel or as an equipment interconnect, but due to their limited length are not guaranteed to meet component compliance requirements that were developed to assess the quality of longer cords

## Environmental Specifications

**Operating Temperature** -10 °C to +60 °C (+14 °F to +140 °F)

**Environmental Space** Riser

**Flammability Rating** UL 94 V-0

## Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

## Included Products

1071E-4/23	–	GigaSPEED XL® 1071E ETL Verified Category 6 U/UTP Cable, non-plenum, 4 pair count
760151167	–	SYSTIMAX 360™ GigaSPEED XL® 1100GS3 Evolve Category 6 U/UTP Distribution Module, 6 port
360-IPR-1100-GS3-DM6		