# UGXMPMXAD

**Base Product** 



# Ultra Low Loss (ULL) OM4 MPO12 (Unpinned) to MPO12 (Pinned), Fiber Trunk Cable Assembly, 12-Fiber, Plenum

# Product Classification

Regional Availability	Asia   Australia/New Zealand   China   Europe   India   Latin America   Middle East/Africa   North America
Portfolio	CommScope®
Product Type	Fiber trunk cable assembly
Product Brand	SYSTIMAX ULL
Ordering Note	For additional jacket colors, please contact a CommScope Sales Representative   For lengths greater than 999 ft (304 m), orders must be in meters   Minimum length may vary based on cable configuration

## General Specifications

deneral specifications	
Color, boot A	Black
Color, connector A	Aqua
Color, boot B	Black
Color, connector B	Aqua
Construction Type	Stranded
Furcation Color	Aqua
Interface, Connector A	MPO-12/UPC Female
Interface, Connector B	MPO-12/UPC Male
Jacket Color	Aqua
Polarity	Method B Enhanced (ULL)
Fibers per Subunit, quantity	12
Total Fibers, quantity	12
Dimensions	
Breakout Length	33 in
Cable Assembly Length Range (m)	3 – 999
Cable Assembly Length Range (ft)	10 - 999

Page 1 of 10



# UGXMPMXAD

# Ordering Tree

	E	BASE C	ODE – M	Ļ	
Jac	ket Color	Breakout Length / Option			ength
М	Aqua	A	33 inch breakout, no gland		
		В	33 inch breakout, with gland		
		С	33 inch breakout, with pulling grip		
		1	33/60 inch breakout, no gland		
		2	33/60 inch breakout, with gland on side A		юм
		3	33/60 inch breakout, with pulling grip and gland on side A	F	Feet Meter
		4	33/120 inch breakout, no gland		
		5	33/120 inch breakout, with gland on side A		
		6	33/120 inch breakout, with pulling grip and gland on side A		
		т	33 inch breakout, with gland on side A		
		U	33 inch breakout, with pulling grip and gland on side A		
		v	60 inch breakout, no gland		
		w	60 inch breakout, with pulling grip		
		Р	120 inch breakout, no gland		
		Q	120 inch breakout, with pulling grip		

# Mechanical Specifications

Cable Retention Strength, maximum	11.24 lb @ 0 °   4.40 lb @ 90 °	
Optical Specifications		
Fiber Mode	Multimode	
Fiber Type	OM4, LazrSPEED®	

### **Environmental Specifications**

**Operating Temperature** 

-10 °C to +60 °C (+14 °F to +140 °F)

Page 2 of 10



# UGXMPMXAD

**Environmental Space** 

Indoor | Plenum

# Regulatory Compliance/Certifications

Classification

#### Agency ANATEL

Compliant

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system




## Included Products

760051656 P-012-MP-5K-F12AQ	-	Fiber indoor cable, LazrSPEED® Plenum for MPO Trunks, 12 fiber, Multimode OM4, Feet jacket marking, Aqua jacket color
860366210	-	MP012, ULTRA LOW LOSS, FEMALE, OM3/4, AQUA, 3mm
860366228	-	MP012, ULTRA LOW LOSS, MALE, OM3/4, AQUA, 3mm



# 760051656 | P-012-MP-5K-F12AQ



Fiber indoor cable, LazrSPEED® Plenum for MPO Trunks, 12 fiber, Multimode OM4, Feet jacket marking, Aqua jacket color

# Product Classification


Regional Availability	Asia   Australia/New Zealand   Latin America   Middle East /Africa   North America
Portfolio	CommScope®
Product Type	Fiber indoor cable
Product Series	P-MP
General Specifications	
Cable Type	MPO trunk cable
Construction Type	Non-armored
Subunit Type	Gel-free
Jacket Color	Aqua
Jacket Marking	Feet
Total Fiber Count	12
Dimensions	
Buffer Tube/Subunit Diameter	3 mm   0.118 in
Diameter Over Jacket	4.9 mm   0.193 in

## Representative Image

Page 4 of 10



# 760051656 | P-012-MP-5K-F12AQ



# Mechanical Specifications

Minimum Bend Radius, loaded	74 mm   2.913 in
Minimum Bend Radius, unloaded	49 mm   1.929 in
Tensile Load, long term, maximum	200 N   44.962 lbf
Tensile Load, short term, maximum	667 N   149.948 lbf
Compression	10 N/mm   57.101 lb/in
Compression Test Method	FOTP-41   IEC 60794-1 E3
Flex	300 cycles
Flex Test Method	FOTP-104   IEC 60794-1 E6
Impact	0.74 N-m   6.55 in lb
Impact Test Method	FOTP-25   IEC 60794-1 E4
Strain	See long and short term tensile loads
Strain Test Method	FOTP-33   IEC 60794-1 E1
Twist	10 cycles
Twist Test Method	FOTP-85   IEC 60794-1 E7
Vertical Rise, maximum	500 m   1,640.42 ft
Optical Specifications	
Fiber Type	OM4, LazrSPEED® 550   OM4, LazrSPEED® 550

### **Environmental Specifications**

Installation temperature

0 °C to +70 °C (+32 °F to +158 °F)

Page 5 of 10



# 760051656 | P-012-MP-5K-F12AQ

Operating Temperature	0 °C to +70 °C (+32 °F to +158 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Cable Qualification Standards	ANSI/ICEA S-83-596   Telcordia GR-409
Environmental Space	Plenum
Flame Test Listing	NEC OFNP (ETL) and c(ETL)
Flame Test Method	NFPA 130   NFPA 262

## Environmental Test Specifications

Heat Age	0 °C to +85 °C (+32 °F to +185 °F)
Heat Age Test Method	IEC 60794-1 F9
Low High Bend	0 °C to +70 °C (+32 °F to +158 °F)
Low High Bend Test Method	FOTP-37   IEC 60794-1 E11
Temperature Cycle	0 °C to +70 °C (+32 °F to +158 °F)
Temperature Cycle Test Method	FOTP-3   IEC 60794-1 F1

## Packaging and Weights

#### Cable weight

23 kg/km | 15.455 lb/kft

### Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



# \* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable

Page 6 of 10





Product Classification

# MPO12, ULTRA LOW LOSS, FEMALE, OM3/4, AQUA, 3mm

Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America   North America
Portfolio	CommScope®
Product Type	Fiber connector
Product Brand	LazrSPEED®
General Specifications	
Color	Aqua
Color, boot	Black
Ferrule Geometry	Flat
Interface	MPO/UPC Female
Interface Feature	Unpinned
Total Fiber Count	12
Dimensions	
Length	60.1 mm   2.366 in
Compatible Cable Diameter	3 mm   0.118 in
Material Specifications	
Ferrule Material	Polymer
Mechanical Specifications	
Cable Retention Strength, maximum	11.24 lb @ 0 °
Optical Specifications	
Fiber Mode	Multimode
Fiber Type	OM3   OM4
Insertion Loss Change, mating	0.3 dB

Page 7 of 10



Optical Components Standard	ANSI/TIA-568-C.3
Insertion Loss Change, temperature	0.3 dB
Insertion Loss, maximum	0.2 dB
Return Loss, minimum	27 dB

# Packaging and Weights

1

# Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

# \* Footnotes

Insertion Loss Change, mating	TIA-568: Maximum insertion loss change after 500 matings
Insertion Loss Change, temperature	Maximum insertion loss change from -10 °C to +60 °C (+14 °F to +140 °F)

Page 8 of 10





Product Classification

# MPO12, ULTRA LOW LOSS, MALE, OM3/4, AQUA, 3mm

Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America   North America
Portfolio	CommScope®
Product Type	Fiber connector
Product Brand	LazrSPEED®
General Specifications	
Color	Aqua
Color, boot	Black
Ferrule Geometry	Flat
Interface	MPO/UPC Male
Interface Feature	Pinned
Total Fiber Count	12
Dimensions	
Length	60.1 mm   2.366 in
Compatible Cable Diameter	3 mm   0.118 in
Material Specifications	
Ferrule Material	Polymer
Mechanical Specifications	
Cable Retention Strength, maximum	11.24 lb @ 0 °
Optical Specifications	
Fiber Mode	Multimode
Fiber Type	OM3   OM4
Insertion Loss Change, mating	0.3 dB
Optical Components Standard	ANSI/TIA-568-C.3

Page 9 of 10



Insertion Loss Change, temperature	0.3 dB
Insertion Loss, maximum	0.2 dB
Return Loss, minimum	27 dB

# Packaging and Weights

Packaging quantity

1

# Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant
50)	

## \* Footnotes

Insertion Loss Change, mating	TIA-568: Maximum insertion loss change after 500 matings
Insertion Loss Change, temperature	Maximum insertion loss change from -10 °C to +60 °C (+14 °F to +140 °F)

Page 10 of 10

