## **UJGMXMXDH**

#### **Base Product**



Ultra Low Loss (ULL) Singlemode MPO12 Pinned to MPO12 Pinned, Fiber Trunk Cable Assembly, 48-Fiber, Indoor/Outdoor, Low Smoke Zero Halogen/Riser

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | China | Europe | India | Latin

America | Middle East/Africa | North America

Portfolio CommScope®

**Product Type** Fiber trunk cable assembly

Product Brand SYSTIMAX ULL

Ordering Note For additional jacket colors, please contact a CommScope Sales Representative | For

lengths greater than 999 ft (304 m), orders must be in meters | Minimum length may

vary based on cable configuration

#### General Specifications

Color, boot ABlackColor, connector AGreenColor, boot BBlackColor, connector BGreenConstruction TypeStranded

Furcation Color Yellow

 Interface, Connector A
 MPO-12/APC Male

 Interface, Connector B
 MPO-12/APC Male

Jacket Color Black

Polarity Method B Enhanced (ULL)

Fibers per Subunit, quantity 12

Total Fibers, quantity 48

#### **Dimensions**

Breakout Length 33 in

Cable Assembly Length Range (m) 3 - 999


Cable Assembly Length Range (ft) 10 - 999

Page 1 of 8



## **UJGMXMXDH**

### Ordering Tree



### Mechanical Specifications

Cable Retention Strength, maximum  $11.24 \text{ lb} @ 0 \degree | 4.40 \text{ lb} @ 90 \degree$ 

Optical Specifications

**Fiber Mode** Singlemode

**Fiber Type** G.657.A2, TeraSPEED®

**Environmental Specifications** 

Operating Temperature -10 °C to +60 °C (+14 °F to +140 °F)

**COMMSCOPE®** 

# **UJGMXMXDH**

#### **Environmental Space**

Dual Rated LSZH/Riser | Indoor/Outdoor

### Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted



### Included Products

760238828 – Fiber Indoor/Outdoor cable, Low Smoke Zero Halogen Riser MPO Trunk, 48 fiber multi-unit with Z-048-MP-8G-F12BK/D 12 fiber subunits, Singlemode G.657.A2/B2, Feet jacket marking, Black jacket color, Dca flame

ating

860638317 – MPO12, ULTRA LOW LOSS, MALE, Singlemode, GREEN, 3mm



# 760238828 | Z-048-MP-8G-F12BK/D



Fiber Indoor/Outdoor cable, Low Smoke Zero Halogen Riser MPO Trunk, 48 fiber multi-unit with 12 fiber subunits, Singlemode G.657.A2/B2, Feet jacket marking, Black jacket color, Dca flame rating

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North

America

Portfolio CommScope®

Product Type Fiber indoor/outdoor cable

**Product Series** Z-MP

General Specifications

Cable TypeMPO trunk cable

Construction Type Non-armored

**Subunit Type** Gel-free

Jacket Color Black

Jacket Marking Feet

Subunit, quantity 4

Fibers per Subunit, quantity 12

Total Fiber Count 48

**Dimensions** 


**Buffer Tube/Subunit Diameter** 3 mm | 0.118 in

**Diameter Over Jacket** 9.75 mm | 0.384 in

Representative Image



# 760238828 | Z-048-MP-8G-F12BK/D



### Mechanical Specifications

Minimum Bend Radius, loaded 146 mm | 5.748 in

Minimum Bend Radius, unloaded 98 mm | 3.858 in

**Tensile Load, long term, maximum** 400 N | 89.924 lbf

Tensile Load, short term, maximum 1335 N | 300.12 lbf

**Compression** 10 N/mm | 57.101 lb/in

**Compression Test Method** FOTP-41 | IEC 60794-1 E3

Flex 300 cycles

Flex Test Method FOTP-104 | IEC 60794-1 E6

**Impact** 2.94 N-m | 26.021 in lb

Impact Test Method FOTP-25 | IEC 60794-1 E4

**Strain** See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

**Vertical Rise, maximum** 500 m | 1,640.42 ft

Optical Specifications

**Fiber Type** G.657.A2/B2 | G.657.A2/B2

### **Environmental Specifications**

Installation temperature  $-30 \,^{\circ}\text{C} \, \text{to} + 60 \,^{\circ}\text{C} \, (-22 \,^{\circ}\text{F to} + 140 \,^{\circ}\text{F})$ Operating Temperature  $-40 \,^{\circ}\text{C} \, \text{to} + 70 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to} + 158 \,^{\circ}\text{F})$ Storage Temperature  $-40 \,^{\circ}\text{C} \, \text{to} + 75 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to} + 167 \,^{\circ}\text{F})$ 

Page 5 of 8



# 760238828 | Z-048-MP-8G-F12BK/D

Cable Qualification Standards ANSI/ICEA S-83-596 | Telcordia GR-409

EN50575 CPR Cable EuroClass Fire PerformanceDcaEN50575 CPR Cable EuroClass Smoke Ratings1bEN50575 CPR Cable EuroClass Droplets Ratingd2EN50575 CPR Cable EuroClass Acidity Ratinga2

Environmental Space Low Smoke Zero Halogen (LSZH) | Riser

Flame Test Listing NEC OFNR-ST1 (ETL) and c(ETL)

Flame Test Method | IEC 60332-3 | IEC 60754-2 | IEC 61034-2 | UL 1666 | UL 1685

Jacket UV Resistance UV stabilized

**Environmental Test Specifications** 

Cable Freeze Test Method IEC 60794-1 F15

**Heat Age** -20 °C to +85 °C (-4 °F to +185 °F)

**Heat Age Test Method** IEC 60794-1 F9

**Low High Bend**  $-20 \,^{\circ}\text{C to } +70 \,^{\circ}\text{C } (-4 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$ 

**Low High Bend Test Method** FOTP-37 | IEC 60794-1 E11

**Temperature Cycle**  $-20 \,^{\circ}\text{C to } +70 \,^{\circ}\text{C } (-4 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$ 

**Temperature Cycle Test Method** FOTP-3 | IEC 60794-1 F1

Packaging and Weights

**Cable weight** 72 kg/km | 48.382 lb/kft

#### Regulatory Compliance/Certifications

#### Agency Classification

CENELEC EN 50575 compliant, Declaration of Performance (DoP) available

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



#### \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable

Page 6 of 8





#### MPO12, ULTRA LOW LOSS, MALE, Singlemode, GREEN, 3mm

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

 Portfolio
 CommScope®

 Product Type
 Fiber connector

 Product Brand
 TeraSPEED®

General Specifications

ColorGreenColor, bootBlackFerrule GeometryAngled

Interface MPO/APC Male

Interface FeaturePinnedTotal Fiber Count12

**Dimensions** 

Length 60.1 mm | 2.366 in Compatible Cable Diameter 3 mm | 0.118 in

Material Specifications

Ferrule Material Polymer

Mechanical Specifications

Cable Retention Strength, maximum $11.24 \text{ lb} @ 0 \degree$ Mechanical Components StandardIEC 61754-7

**Optical Specifications** 

**Fiber Mode** Singlemode

Fiber Type G.652.D and G.657.A1, TeraSPEED® | OS2

**Insertion Loss Change, mating** 0.3 dB

Page 7 of 8

# 860638317

Optical Components Standard ANSI/TIA-568-C.3

Insertion Loss Change, temperature0.3 dBInsertion Loss, maximum0.35 dBReturn Loss, minimum65 dB

### Packaging and Weights

Packaging quantity

### Regulatory Compliance/Certifications

#### Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



#### \* Footnotes

**Insertion Loss Change, mating**TIA-568: Maximum insertion loss change after 500 matings

**Insertion Loss Change, temperature** Maximum insertion loss change from -10 °C to +60 °C (+14 °F to +140 °F)

