FJXMPMPDF

Base Product



OM4 MPO (Unpinned) to MPO (Unpinned), InstaPATCH® 360 Preterminated Indoor/Outdoor Trunk Cable, 24-Fiber, Low Smoke Zero Halogen

Product Classification

Regional Availability

Asia | Australia/New Zealand | China | Europe | India | Latin

America | Middle East/Africa | North America

Portfolio CommScope®

Product Type Fiber trunk cable assembly
Product Brand SYSTIMAX InstaPATCH® 360

Ordering Note For lengths greater than 999 ft (304 m), orders must be in meters | Minimum length

may vary based on cable configuration

General Specifications

Color, boot ABlackColor, connector AAquaColor, boot BBlackColor, connector BAqua

Construction Type InstaPATCH® 360 trunk/extension/cross-connect, indoor/outdoor

Furcation Color Aqua

 Interface, Connector A
 MPO-12/UPC Female

 Interface, Connector B
 MPO-12/UPC Female

Jacket Color Black

Polarity Method B (LL)

Fibers per Subunit, quantity 12

Total Fibers, quantity 24

Dimensions


Cable Assembly Length Range (m) 3 - 999

Cable Assembly Length Range (ft) 10 - 999

COMMSCOPE®

FJXMPMPDF

Ordering Tree



Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0 ° | 4.40 lb @ 90 °

Optical Specifications

Fiber Mode Multimode

Fiber Type OM4, LazrSPEED®

Environmental Specifications

Operating Temperature $-40 \, ^{\circ}\text{C} \text{ to } +70 \, ^{\circ}\text{C} \, (-40 \, ^{\circ}\text{F to } +158 \, ^{\circ}\text{F})$

Environmental Space Dual Rated LSZH/Riser | Indoor/Outdoor | Outdoor

COMMSCOPE®

FJXMPMPDF

Regulatory Compliance/Certifications

Classification **Agency**

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system **REACH-SVHC** Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant **UK-ROHS** Compliant



Included Products

Fiber Indoor/Outdoor cable, LazrSPEED®, Low Smoke Zero Halogen Riser MPO Trunk Cable, 24 760159996 Z-024-MP-5K-F12BK/D

fiber with 12 fiber subunits, Gel-free, Multimode OM4, Feet jacket marking, Black jacket color,

Dca flame rating

MPO12, LOW LOSS, FEMALE, OM3/4, AQUA, 3mm 860647054





Fiber Indoor/Outdoor cable, LazrSPEED®, Low Smoke Zero Halogen Riser MPO Trunk Cable, 24 fiber with 12 fiber subunits, Gel-free, Multimode OM4, Feet jacket marking, Black jacket color, Dca flame rating

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North

America

Portfolio CommScope®

Product Type Fiber indoor/outdoor cable

Product Series Z-MP

General Specifications

Cable TypeMPO trunk cable

Construction Type Non-armored

Subunit Type Gel-free

Jacket Color Black

Jacket Marking Feet

Subunit, quantity 2

Fibers per Subunit, quantity 12


Total Fiber Count 24

Dimensions

Height Over Jacket5.2 mm | 0.205 inWidth Over Jacket8.2 mm | 0.323 inBuffer Tube/Subunit Diameter3 mm | 0.118 in

Representative Image





Mechanical Specifications

Minimum Bend Radius, loaded78 mm | 3.071 inMinimum Bend Radius, unloaded52 mm | 2.047 inTensile Load, long term, maximum267 N | 60.024 lbfTensile Load, short term, maximum890 N | 200.08 lbf

 Compression
 10 N/mm | 57.101 lb/in

 Compression Test Method
 FOTP-41 | IEC 60794-1 E3

Flex 300 cycles

Flex Test Method FOTP-104 | IEC 60794-1 E6

Impact 2.94 N-m | 26.021 in lb

Impact Test Method FOTP-25 | IEC 60794-1 E4

Strain See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

Vertical Rise, maximum 500 m | 1,640.42 ft

Optical Specifications

Fiber Type OM4, LazrSPEED® 550 | OM4, LazrSPEED® 550

Environmental Specifications

Installation temperature $-30 \,^{\circ}\text{C}$ to $+60 \,^{\circ}\text{C}$ (-22 °F to +140 °F)

Operating Temperature $-40 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ (-40 °F to +158 °F)

Storage Temperature $-40 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ (-40 °F to +158 °F)

Page 5 of 9



Cable Qualification Standards ANSI/ICEA S-104-696 | Telcordia GR-20 (water

penetration) | Telcordia GR-409

EN50575 CPR Cable EuroClass Fire PerformanceDcaEN50575 CPR Cable EuroClass Smoke Ratings1bEN50575 CPR Cable EuroClass Droplets Ratingd2EN50575 CPR Cable EuroClass Acidity Ratinga2

Environmental Space Low Smoke Zero Halogen (LSZH) | Riser

Flame Test Listing NEC OFNR-ST1 (ETL) and c(ETL)

Flame Test Method | IEC 60332-3 | IEC 60754-2 | IEC 61034-2 | UL 1666 | UL 1685

Jacket UV Resistance UV stabilized

Water Penetration 24 h

Water Penetration Test Method FOTP-82 | IEC 60794-1 F5

Environmental Test Specifications

Cable Freeze Test Method IEC 60794-1 F15

Heat Age -40 °C to +85 °C (-40 °F to +185 °F)

Heat Age Test Method IEC 60794-1 F9

Low High Bend $-30 \,^{\circ}\text{C} \text{ to } +60 \,^{\circ}\text{C} \, (-22 \,^{\circ}\text{F to } +140 \,^{\circ}\text{F})$

Low High Bend Test Method FOTP-37 | IEC 60794-1 E11

Temperature Cycle $-40 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$

Temperature Cycle Test Method FOTP-3 | IEC 60794-1 F1

Packaging and Weights

Cable weight 42 kg/km | 28.223 lb/kft

Regulatory Compliance/Certifications

Agency Classification

CENELEC EN 50575 compliant, Declaration of Performance (DoP) available

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system
REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant





* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable



MPO12, LOW LOSS, FEMALE, OM3/4, AQUA, 3mm

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Product Type CommScope®

Fiber connector

General Specifications

ColorAquaColor, bootBlackFerrule GeometryFlat

Interface MPO/UPC Female

Interface Feature Unpinned

Total Fiber Count 12

Dimensions

Length60.1 mm | 2.366 inCompatible Cable Diameter3 mm | 0.118 in

Material Specifications

Ferrule Material Polymer

Mechanical Specifications

Cable Retention Strength, maximum $11.24 \text{ lb} @ 0 ^{\circ}$

Optical Specifications

Fiber ModeMultimodeFiber TypeOM3 | OM4

Insertion Loss Change, mating 0.2 dB

Optical Components Standard ANSI/TIA-568-C.3

COMMSCOPE®

860647054

Insertion Loss Change, temperature0.2 dBInsertion Loss, maximum0.25 dBReturn Loss, minimum27 dB

Packaging and Weights

Packaging quantity

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

* Footnotes

Insertion Loss Change, matingTIA-568: Maximum insertion loss change after 500 matings

Insertion Loss Change, temperature Maximum insertion loss change from -10 °C to +60 °C (+14 °F to +140 °F)

