## **UJGMXUCAM**

#### **Base Product**



Ultra Low Loss (ULL) Singlemode, MPO12 Pinned to Unconnectorized, Fiber Trunk Cable Assembly, 144-Fiber, Low Smoke Zero Halogen/Riser

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | China | Europe | India | Latin

America | Middle East/Africa | North America

Portfolio CommScope®

**Product Type** Fiber trunk cable assembly

Product Brand SYSTIMAX ULL

Ordering Note For additional jacket colors, please contact a CommScope Sales Representative | For

lengths greater than 999 ft (304 m), orders must be in meters | Minimum length may

vary based on cable configuration

## General Specifications

Color, boot ABlackColor, connector AGreenConstruction TypeStrandedFurcation ColorYellow

Interface, Connector A MPO-12/APC Male

Interface, Connector B Unterminated

Jacket Color Yellow

Polarity Method B Enhanced (ULL)

Fibers per Subunit, quantity 12

Total Fibers, quantity 144

**Dimensions** 

Breakout Length 33 in

Cable Assembly Length Range (m) 3 - 999




## **UJGMXUCAM**

#### Cable Assembly Length Range (ft)

10 - 999

## Ordering Tree



## Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0  $^{\circ}$  | 4.40 lb @ 90  $^{\circ}$ 

Optical Specifications

Fiber Mode Singlemode

**Fiber Type** G.657.A2, TeraSPEED®

## **Environmental Specifications**

Operating Temperature  $-10 \,^{\circ}\text{C}$  to  $+60 \,^{\circ}\text{C}$  (+14  $^{\circ}\text{F}$  to +140  $^{\circ}\text{F}$ )

Environmental Space Dual Rated LSZH/Riser | Indoor

**COMMSCOPE®** 

## **UJGMXUCAM**

## Regulatory Compliance/Certifications

Classification **Agency ANATEL** Compliant

CHINA-ROHS Above maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system **REACH-SVHC** Compliant as per SVHC revision on www.commscope.com/ProductCompliance

**ROHS** Compliant/Exempted **UK-ROHS** Compliant/Exempted




#### Included Products

760237978 N-144-MP-8G1-F12YL/D

Fiber indoor cable, Low Smoke Zero Halogen Riser MPO Trunk, 144 fiber multi-unit with 12 fiber subunits, Gel-free, Singlemode G.657.A2/B2, Feet jacket marking, Yellow jacket color, Dca flame

rating

MPO12, ULTRA LOW LOSS, MALE, Singlemode, GREEN, 3mm 860638317



## 760237978 | N-144-MP-8G1-F12YL/D



Fiber indoor cable, Low Smoke Zero Halogen Riser MPO Trunk, 144 fiber multi-unit with 12 fiber subunits, Gel-free, Singlemode G.657.A2/B2, Feet jacket marking, Yellow jacket color, Dca flame rating

### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North

America

Portfolio CommScope®

**Product Type** Fiber indoor cable

**Product Series** N-MP

General Specifications

Cable Type MPO trunk cable

Construction Type Non-armored

Subunit Type Gel-free

Jacket Color Yellow

Jacket Marking Feet

Subunit, quantity 12

Fibers per Subunit, quantity 12

Total Fiber Count 144

**Dimensions** 


**Buffer Tube/Subunit Diameter** 3 mm | 0.118 in

**Diameter Over Jacket** 14.22 mm | 0.56 in

Representative Image



# 760237978 | N-144-MP-8G1-F12YL/D



### Mechanical Specifications

Minimum Bend Radius, loaded200 mm7.874 inMinimum Bend Radius, unloaded133 mm5.236 in

Tensile Load, long term, maximum 400 N | 89.924 lbf

Tensile Load, short term, maximum 1335 N | 300.12 lbf

 Compression
 10 N/mm | 57.101 lb/in

 Compression Test Method
 FOTP-41 | IEC 60794-1 E3

Flex 300 cycles

Flex Test Method FOTP-104 | IEC 60794-1 E6

**Impact** 2.94 N-m | 26.021 in lb

Impact Test Method FOTP-25 | IEC 60794-1 E4

Strain See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

**Vertical Rise, maximum** 280 m | 918.635 ft

Optical Specifications

**Fiber Type** G.657.A2/B2 | G.657.A2/B2

**Environmental Specifications** 

Installation temperature  $-20 \,^{\circ}\text{C}$  to  $+60 \,^{\circ}\text{C}$  (-4  $^{\circ}\text{F}$  to  $+140 \,^{\circ}\text{F}$ )

Page 5 of 8

# 760237978 | N-144-MP-8G1-F12YL/D

**Operating Temperature**  $-20 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \, (-4 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$ 

Storage Temperature  $-40 \,^{\circ}\text{C}$  to  $+70 \,^{\circ}\text{C}$  (-40  $^{\circ}\text{F}$  to  $+158 \,^{\circ}\text{F}$ )

Cable Qualification Standards ANSI/ICEA S-83-596 | Telcordia GR-409

EN50575 CPR Cable EuroClass Fire PerformanceDcaEN50575 CPR Cable EuroClass Smoke Ratings1aEN50575 CPR Cable EuroClass Droplets Ratingd1EN50575 CPR Cable EuroClass Acidity Ratinga1

Environmental Space Low Smoke Zero Halogen (LSZH) | Riser

Flame Test Listing NEC OFNR-ST1 (ETL) and c(ETL)

Flame Test Method | IEC 60332-3 | IEC 60754-2 | IEC 61034-2 | UL 1666 | UL 1685

**Environmental Test Specifications** 

**Heat Age**  $-20 \,^{\circ}\text{C}$  to  $+85 \,^{\circ}\text{C}$   $(-4 \,^{\circ}\text{F}$  to  $+185 \,^{\circ}\text{F})$ 

Heat Age Test Method IEC 60794-1 F9

Low High Bend $-20 \,^{\circ}\text{C to} + 70 \,^{\circ}\text{C (-4 °F to} + 158 °F)$ Low High Bend Test MethodFOTP-37 | IEC 60794-1 E11Temperature Cycle $-20 \,^{\circ}\text{C to} + 70 \,^{\circ}\text{C (-4 °F to} + 158 °F)$ 

**Temperature Cycle Test Method** FOTP-3 | IEC 60794-1 F1

Packaging and Weights

**Cable weight** 146 kg/km | 98.107 lb/kft

### Regulatory Compliance/Certifications

Agency Classification

CENELEC EN 50575 compliant, Declaration of Performance (DoP) available

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

ROHS Compliant UK-ROHS Compliant



### \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable

COMMSCOPE®



### MPO12, ULTRA LOW LOSS, MALE, Singlemode, GREEN, 3mm

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

 Portfolio
 CommScope®

 Product Type
 Fiber connector

 Product Brand
 TeraSPEED®

General Specifications

ColorGreenColor, bootBlackFerrule GeometryAngled

Interface MPO/APC Male

Interface FeaturePinnedTotal Fiber Count12

**Dimensions** 

Length 60.1 mm | 2.366 in Compatible Cable Diameter 3 mm | 0.118 in

Material Specifications

Ferrule Material Polymer

Mechanical Specifications

Cable Retention Strength, maximum $11.24 \text{ lb} @ 0 \degree$ Mechanical Components StandardIEC 61754-7

**Optical Specifications** 

**Fiber Mode** Singlemode

Fiber Type G.652.D and G.657.A1, TeraSPEED® | OS2

**Insertion Loss Change, mating** 0.3 dB

Page 7 of 8

## 860638317

Optical Components Standard ANSI/TIA-568-C.3

Insertion Loss Change, temperature0.3 dBInsertion Loss, maximum0.35 dBReturn Loss, minimum65 dB

## Packaging and Weights

Packaging quantity

## Regulatory Compliance/Certifications

#### Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



#### \* Footnotes

**Insertion Loss Change, mating**TIA-568: Maximum insertion loss change after 500 matings

**Insertion Loss Change, temperature** Maximum insertion loss change from -10 °C to +60 °C (+14 °F to +140 °F)

