## **MAXMXMVLU**

#### **Base Product**



Ultra Low Loss (ULL) OM5, MPO12 Pinned to MPO12 Pinned, Fiber Trunk Cable Assembly, 144-Fiber, Low Smoke Zero Halogen

### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | China | Europe | India | Latin

America | Middle East/Africa | North America

Portfolio CommScope®

**Product Type** Fiber trunk cable assembly

Product Brand SYSTIMAX ULL

Ordering Note Not available in the United States or Canada

## General Specifications

Color, boot A Black

Color, connector A Lime green

Color, boot B Black

Color, connector BLime greenConstruction TypeStranded

Furcation Color Lime green

Interface, Connector A MPO-12/UPC Male

Interface, Connector B MPO-12/UPC Male

Jacket Color Lime green

Polarity Method B Enhanced (ULL)

Fibers per Subunit, quantity 12

Total Fibers, quantity 144

### Dimensions

Breakout Length 33 in

Cable Assembly Length Range (m) 3 - 999

Cable Assembly Length Range (ft) 10 - 999



# **MAXMXMVLU**

## Ordering Tree



## Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0  $^{\circ}$  | 4.40 lb @ 90  $^{\circ}$ 

**Optical Specifications** 

Fiber Mode Multimode

**Fiber Type** OM5, LazrSPEED®

## **Environmental Specifications**

Operating Temperature -10 °C to +60 °C (+14 °F to +140 °F)

Environmental Space Dual Rated LSZH/Riser | Indoor

Page 2 of 8



# **MAXMXMVLU**

## Regulatory Compliance/Certifications

Agency Classification

ANATEL Compliant

CHINA-ROHS Above maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted



### Included Products

760229104 – Fiber indoor cable, LazrSPEED® Low Smoke Zero Halogen Riser MPO Trunk, 144 fiber multi-N-144-MP-5G-F12LM/D unit with 12 fiber subunits, Gel-free, Multimode OM5, Feet jacket marking, Lime green jacket

color, Dca flame rating

860617240 – MPO12, ULTRA LOW LOSS, MALE, OM5, LIME, 3mm



# 760229104 | N-144-MP-5G-F12LM/D



Fiber indoor cable, LazrSPEED® Low Smoke Zero Halogen Riser MPO Trunk, 144 fiber multi-unit with 12 fiber subunits, Gel-free, Multimode OM5, Feet jacket marking, Lime green jacket color, Dca flame rating

### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North

America

 Portfolio
 CommScope®

 Product Type
 Fiber indoor cable

**Product Series** N-MP

General Specifications

Cable Type MPO trunk cable

Construction Type Non-armored

Subunit Type Gel-free

Jacket Color Lime green

Jacket Marking Feet

Subunit, quantity 12

Fibers per Subunit, quantity 12

Total Fiber Count 144

**Dimensions** 


**Buffer Tube/Subunit Diameter** 3 mm | 0.118 in

**Diameter Over Jacket** 14.22 mm | 0.56 in

Representative Image



# 760229104 | N-144-MP-5G-F12LM/D



## Mechanical Specifications

Minimum Bend Radius, loaded 200 mm | 7.874 in

Minimum Bend Radius, unloaded 133 mm | 5.236 in

**Tensile Load, long term, maximum** 400 N | 89.924 lbf

Tensile Load, short term, maximum 1335 N | 300.12 lbf

**Compression** 10 N/mm | 57.101 lb/in

Compression Test Method FOTP-41 | IEC 60794-1 E3

Flex 300 cycles

Flex Test Method FOTP-104 | IEC 60794-1 E6

**Impact** 2.94 N-m | 26.021 in lb

Impact Test Method FOTP-25 | IEC 60794-1 E4

**Strain** See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

**Vertical Rise, maximum** 280 m | 918.635 ft

**Optical Specifications** 

Fiber Type OM5, LazrSPEED® wideband | OM5, LazrSPEED® wideband

**Environmental Specifications** 

Installation temperature  $-20 \,^{\circ}\text{C}$  to  $+60 \,^{\circ}\text{C}$  (-4 °F to +140 °F)

Operating Temperature  $-20 \,^{\circ}\text{C}$  to  $+70 \,^{\circ}\text{C}$  (-4 °F to +158 °F)

Page 5 of 8



# 760229104 | N-144-MP-5G-F12LM/D

Storage Temperature  $-40 \,^{\circ}\text{C}$  to  $+70 \,^{\circ}\text{C}$  (-40  $^{\circ}\text{F}$  to  $+158 \,^{\circ}\text{F}$ )

Cable Qualification Standards ANSI/ICEA S-83-596 | Telcordia GR-409

EN50575 CPR Cable EuroClass Fire PerformanceDcaEN50575 CPR Cable EuroClass Smoke Ratings1aEN50575 CPR Cable EuroClass Droplets Ratingd1EN50575 CPR Cable EuroClass Acidity Ratinga1

Environmental Space Low Smoke Zero Halogen (LSZH) | Riser

Flame Test Listing NEC OFNR-ST1 (ETL) and c(ETL)

Flame Test Method | IEC 60332-3 | IEC 60754-2 | IEC 61034-2 | UL 1666 | UL 1685

**Environmental Test Specifications** 

**Heat Age**  $-20 \,^{\circ}\text{C}$  to  $+85 \,^{\circ}\text{C}$   $(-4 \,^{\circ}\text{F}$  to  $+185 \,^{\circ}\text{F})$ 

**Heat Age Test Method** IEC 60794-1 F9

**Low High Bend**  $-20 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \, (-4 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$ 

**Low High Bend Test Method** FOTP-37 | IEC 60794-1 E11

**Temperature Cycle**  $-20 \,^{\circ}\text{C}$  to  $+70 \,^{\circ}\text{C}$  (-4  $^{\circ}\text{F}$  to  $+158 \,^{\circ}\text{F}$ )

**Temperature Cycle Test Method** FOTP-3 | IEC 60794-1 F1

Packaging and Weights

**Cable weight** 146 kg/km | 98.107 lb/kft

## Regulatory Compliance/Certifications

### Agency Classification

CENELEC EN 50575 compliant, Declaration of Performance (DoP) available

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



### \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable

COMMSC PE®



### MPO12, ULTRA LOW LOSS, MALE, OM5, LIME, 3mm

### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

 Portfolio
 CommScope®

 Product Type
 Fiber connector

 Product Brand
 LazrSPEED®

General Specifications

ColorLime greenColor, bootBlackFerrule GeometryFlat

Interface MPO/UPC Male

Interface Feature Pinned

Total Fiber Count 12

**Dimensions** 

Length60.1 mm | 2.366 inCompatible Cable Diameter3 mm | 0.118 in

Material Specifications

Ferrule Material Polymer

Mechanical Specifications

Cable Retention Strength, maximum  $11.24 \text{ lb} @ 0 ^{\circ}$ 

**Optical Specifications** 

**Fiber Mode** Multimode

**Fiber Type** OM5, LazrSPEED® wideband

**Insertion Loss Change, mating** 0.3 dB

Optical Components Standard ANSI/TIA-568-C.3

Page 7 of 8

# 860617240

Insertion Loss Change, temperature0.3 dBInsertion Loss, maximum0.2 dBReturn Loss, minimum27 dB

## Packaging and Weights

Packaging quantity 1

## Regulatory Compliance/Certifications

### Agency Classification

CHINA-ROHS Above maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted

UK-ROHS Compliant



### \* Footnotes

**Insertion Loss Change, mating**TIA-568: Maximum insertion loss change after 500 matings

**Insertion Loss Change, temperature** Maximum insertion loss change from -10 °C to +60 °C (+14 °F to +140 °F)

