FEXL9L921

Base Product



OM4 LC/UPC Keyed Rose to LC/UPC Keyed Rose Fiber Patch Cord, 1.6 mm Simplex, Riser

Product Classification

Regional Availability

Asia | Australia/New Zealand | Europe | Latin America | Middle East

/Africa | North America

Portfolio CommScope®

Product Type Fiber patch cord, simplex

Product Brand SYSTIMAX InstaPATCH® 360

Product Series FEX

Ordering Note For lengths greater than 999 ft (304 m), orders must be in meters | Minimum length

may vary based on cable configuration

General Specifications

Color, boot AAquaColor, connector ARoseColor, boot BAquaColor, connector BRose

Interface, Connector A LC/UPC
Interface Feature, connector A Keyed

Interface, Connector B LC/UPC

Interface Feature, connector B Keyed

Jacket Color Aqua

Polarity Method B

Total Fibers, quantity 1

Dimensions

Cable Assembly Length Range (m) 1 - 999


Cable Assembly Length Range (ft) 1 - 999

Diameter Over Jacket 1.6 mm | 0.063 in

COMMSC PE®

FEXL9L921

Ordering Tree



Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0 ° | 4.40 lb @ 90 °

Optical Specifications

Fiber Mode Multimode

Fiber Type OM4, LazrSPEED®

Environmental Specifications

Operating Temperature $-10 \,^{\circ}\text{C}$ to $+60 \,^{\circ}\text{C}$ (+14 $^{\circ}\text{F}$ to +140 $^{\circ}\text{F}$)

Environmental Space Riser

Regulatory Compliance/Certifications

Agency Classification
ANATEL Compliant

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system



Included Products

760102376 – LazrSPEED®, OptiSPEED® Pre-Radiused Keyed LC Connector for 1.6 mm Fiber, simplex

MFC-LCR-16-KRO multimode, rose

R-001-SP-5K-F16 – Fiber indoor cable, LazrSPEED® 1.6 mm Riser Simplex, Multimode OM4, Feet jacket marking

COMMSC PE®

760102376 | MFC-LCR-16-KRO



LazrSPEED®, OptiSPEED® Pre-Radiused Keyed LC Connector for 1.6 mm Fiber, simplex multimode, rose

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

Product Type Fiber connector

General Specifications

Body Style Simplex
Color Rose

Ferrule Geometry Pre-radiused

InterfaceLC/UPCInterface FeatureKeyed

Dimensions

 Length
 52 mm | 2.047 in

 Compatible Cable Diameter
 1.6 mm | 0.063 in

Material Specifications

Ferrule Material Zirconia

Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0 °

Optical Specifications

Fiber ModeMultimodeInsertion Loss Change, mating0.3 dB

Optical Components Standard ANSI/TIA-568-C.3

COMMSCOPE®

760102376 | MFC-LCR-16-KRO

Insertion Loss Change, temperature0.3 dBInsertion Loss, typical0.2 dBReturn Loss, minimum50 dB

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

* Footnotes

Insertion Loss Change, matingTIA-568: Maximum insertion loss change after 500 matings

Insertion Loss Change, temperature Maximum insertion loss change from -10 °C to +60 °C (+14 °F to +140 °F)



R-001-SP-5K-F16

Fiber indoor cable, LazrSPEED® 1.6 mm Riser Simplex, Multimode OM4, Feet jacket marking

Product Classification

Regional Availability

Asia | Australia/New Zealand | Latin America | Middle East/Africa | North

America

1

 Portfolio
 CommScope®

 Product Type
 Fiber indoor cable

Product Series R-SP

General Specifications


Cable TypeCordageConstruction TypeNon-armoredSubunit TypeGel-freeJacket MarkingFeet

Dimensions

Total Fiber Count

Diameter Over Jacket 1.7 mm | 0.067 in

Representative Image



Mechanical Specifications

Minimum Bend Radius, loaded 38 mm | 1.496 in

Page 5 of 7

R-001-SP-5K-F16

Minimum Bend Radius, unloaded 15 mm | 0.591 in

Tensile Load, long term, maximum 29 N | 6.519 lbf

Tensile Load, short term, maximum 7 N | 1.574 lbf

 Compression
 10 N/mm | 57.101 lb/in

 Compression Test Method
 FOTP-41 | IEC 60794-1 E3

Flex 300 cycles

Flex Test Method FOTP-104 | IEC 60794-1 E6

Impact 0.74 N-m | 6.55 in lb

Impact Test Method FOTP-25 | IEC 60794-1 E4

Strain See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

Vertical Rise, maximum 500 m | 1,640.42 ft

Optical Specifications

Fiber Type OM4, LazrSPEED® 550 | OM4, LazrSPEED® 550

Environmental Specifications

Installation temperature $-20 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ (-4 °F to $+158 \,^{\circ}\text{F}$)

Operating Temperature $-20 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ (-4 °F to $+158 \,^{\circ}\text{F}$)

Storage Temperature $-40 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ (-40 °F to $+158 \,^{\circ}\text{F}$)

Cable Qualification Standards ANSI/ICEA S-83-596 | Telcordia GR-409

Environmental Space Riser

Flame Test Listing NEC OFNR (ETL) and c(ETL)

Flame Test Method UL 1666

Environmental Test Specifications

Heat Age -20 °C to +85 °C (-4 °F to +185 °F)

Heat Age Test Method IEC 60794-1 F9

Low High Bend $-20 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \, (-4 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$

Low High Bend Test Method FOTP-37 | IEC 60794-1 E11

Temperature Cycle -20 °C to +70 °C (-4 °F to +158 °F)

COMMSC PE®

R-001-SP-5K-F16

Temperature Cycle Test Method FOTP-3 | IEC 60794-1 F1

Packaging and Weights

Cable weight 3 kg/km | 2.016 lb/kft

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable

