FFWLCLC42

Base Product



Singlemode LC/UPC to LC/UPC, Fiber Patch Cord, 1.6 mm Duplex, Low Smoke Zero Halogen (LSZH)

 *Product complies with the Build America, Buy America Act (BABAA) requirements of the Infrastructure Investment and Jobs Act of 2021 (Pub. L. 117-58, §§ 70901-70953), or is the subject of a waiver approved by the Secretary of Commerce or designee. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

Product Classification

Regional Availability

Asia | Australia/New Zealand | China | Europe | India | Latin

America | Middle East/Africa | North America

Portfolio CommScope®

Product Type Fiber patch cord, duplex

Product Brand SYSTIMAX InstaPATCH® 360

Product Series FFW

Government Requirements Build America Buy America (BABA) compliant*

Ordering Note For lengths greater than 999 ft (304 m), orders must be in meters | Minimum length

may vary based on cable configuration

General Specifications

Color, boot A Blue

Color, connector A Blue

Color, boot B Blue

Color, connector B Blue

Interface, Connector A LC/UPC

Interface, Connector B LC/UPC

Jacket Color Yellow

Location of ManufacturingClaremont, North Carolina

Polarity Pairs, flipped

Total Fibers, quantity 2

Transmission Standards TIA/EIA-568-C.3

Dimensions

COMMSCOPE®


FFWLCLC42

Cable Assembly Length Range (m) 1 - 999

Cable Assembly Length Range (ft) 1 - 999

Diameter Over Jacket 1.6 mm | 0.063 in

Ordering Tree



Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0 ° | 4.40 lb @ 90 °

Optical Specifications

Fiber Mode Singlemode

Fiber Type G.652.D | G.657.A1, TeraSPEED®

Environmental Specifications

Operating Temperature -10 °C to +60 °C (+14 °F to +140 °F)

Environmental Space Dual Rated LSZH/Riser

Packaging and Weights

Packaging quantity

Regulatory Compliance/Certifications

Agency	Classification
ANATEL	Compliant
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant



FFWLCLC42

UK-ROHS

Compliant



Included Products

760021675 N-002-ZC-8W-F16YL/E


860655488

Singlemode G.652.D and G.657.A1, Feet jacket marking, Yellow jacket color, Eca Flame Rating LC/UPC Connector, Singlemode, Blue

Fiber Indoor Cable, TeraSPEED® 1.6mm Low Smoke Zero Halogen Riser, 2-fiber Zipcord,

Page 3 of 8

760021675 | N-002-ZC-8W-F16YL/E



Fiber Indoor Cable, TeraSPEED® 1.6mm Low Smoke Zero Halogen Riser, 2-fiber Zipcord, Singlemode G.652.D and G.657.A1, Feet jacket marking, Yellow jacket color, Eca Flame Rating

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North

America

Portfolio CommScope®

Product Type Fiber indoor cable

Product Series N-ZC

General Specifications

Cable Type Cordage

Construction Type Non-armored

Subunit Type Gel-free

Jacket Color Yellow

Jacket Marking Feet

Total Fiber Count 2

Dimensions


Height Over Jacket 1.7 mm | 0.067 in

Width Over Jacket 3.5 mm | 0.138 in

Representative Image



760021675 | N-002-ZC-8W-F16YL/E



Mechanical Specifications

Minimum Bend Radius, loaded38 mm | 1.496 inMinimum Bend Radius, unloaded15 mm | 0.591 inTensile Load, long term, maximum53 N | 11.915 lbfTensile Load, short term, maximum178 N | 40.016 lbf

 Compression
 10 N/mm | 57.101 lb/in

 Compression Test Method
 FOTP-41 | IEC 60794-1 E3

Flex 300 cycles

Flex Test Method FOTP-104 | IEC 60794-1 E6

Impact 0.74 N-m | 6.55 in lb

Impact Test Method FOTP-25 | IEC 60794-1 E4

Strain See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

Vertical Rise, maximum 500 m | 1,640.42 ft

Optical Specifications

Fiber Type G.652.D and G.657.A1, TeraSPEED®

Environmental Specifications

Installation temperature $-20 \,^{\circ}\text{C}$ to $+60 \,^{\circ}\text{C}$ (-4 $^{\circ}\text{F}$ to $+140 \,^{\circ}\text{F}$)

Page 5 of 8

760021675 | N-002-ZC-8W-F16YL/E

Operating Temperature $-20 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \left(-4 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F}\right)$

Storage Temperature $-40 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ (-40 $^{\circ}\text{F}$ to $+158 \,^{\circ}\text{F}$)

Cable Qualification Standards ANSI/ICEA S-83-596 | Telcordia GR-409

EN50575 CPR Cable EuroClass Fire Performance Eca

Environmental Space Low Smoke Zero Halogen (LSZH) | Riser

Flame Test Listing NEC OFNR-ST1 (ETL) and c(ETL)

Flame Test Method | IEC 60332-1-2 | IEC 60332-3 | IEC 60754-2 | IEC 61034-2 | UL

1666 | UL 1685

Environmental Test Specifications

Heat Age -20 °C to +85 °C (-4 °F to +185 °F)

Heat Age Test Method IEC 60794-1 F9

Low High Bend $-20 \,^{\circ}\text{C to } +70 \,^{\circ}\text{C } (-4 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$

Low High Bend Test Method FOTP-37 | IEC 60794-1 E11

Temperature Cycle $-20 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ (-4 $^{\circ}\text{F}$ to $+158 \,^{\circ}\text{F}$)

Temperature Cycle Test Method FOTP-3 | IEC 60794-1 F1

Packaging and Weights

Cable weight 6 kg/km | 4.032 lb/kft

Regulatory Compliance/Certifications

Agency Classification

CENELEC EN 50575 compliant, Declaration of Performance (DoP) available

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable





LC/UPC Connector, Singlemode, Blue

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

Product Type Fiber connector

General Specifications

Color, bootBlueColor, housingBlueInterfaceLC/UPC

Dimensions

Length 41.6 mm | 1.638 in

Compatible Cable Diameter 1.6 mm | 0.063 in | 2 mm | 0.079 in

Material Specifications

Ferrule Material Zirconia

Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0 °

Optical Specifications

Fiber Mode Singlemode

Insertion Loss Change, mating 0.2 dB

Optical Components Standard ANSI/TIA-568. 3-D | IEC 61753-1

Insertion Loss Change, temperature0.2 dBInsertion Loss, maximum0.34 dBReturn Loss, minimum50 dB



860655488

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



* Footnotes

Insertion Loss Change, matingTIA-568: Maximum insertion loss change after 500 matings

Insertion Loss Change, temperature Maximum insertion loss change from -10 °C to +60 °C (+14 °F to +140 °F)

