F1-XMHM-2-SGW1-D



D-CLASS FSJ1-50A SureFlex ${\Bbb R}$ Jumper with interface types NEX10 Male and 4.3-10 Male with HELIAX ${\Bbb R}$ SureGuard weatherproofing boot (boot with HM end), 2 ft

WARNING: DO NOT MATE WITH 4.1-9.5 DIN

Product Classification

Product Type SureFlex® D-CLASS, dynamic PIM

Product Brand HELIAX® | SureFlex®

Product Series FSJ1-50A

General Specifications

Body Style, Connector AStraightBody Style, Connector BStraightInterface, Connector ANEX10 MaleInterface, Connector B4.3-10 Male

Specification Sheet Revision Level

Dimensions

Length 0.61 m | 2.001 ft

Nominal Size 1/4 in

Logo Image



F1-XMHM-2-SGW1-D



Electrical Specifications

3rd Order IMD Dynamic -119 dBm

3rd Order IMD Dynamic Test MethodTwo +43 dBm carriers per IEC 62037

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
698-960 MHz	1.065	30.04
1700-2200 MHz	1.083	27.99
2500-2700 MHz	1.106	25.96
3400-3800 MHz	1.222	20.01

Jumper Assembly Sample Label





Environmental Specifications

Immersion Test MethodMeets IEC 60529:2001, IP68 in mated condition

Weatherproofing Method HELIAX® SureGuard weatherproofing boot

Packaging and Weights

Included Weatherproofing boot

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.andrew.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant/Exempted

