

# H4-NMNM-90-P

HL4-50™ Jumper with interface types N Male and N Male, 90 ft



## Product Classification

|                       |                        |
|-----------------------|------------------------|
| <b>Product Type</b>   | Cable assembly, plenum |
| <b>Product Series</b> | HL4-50A                |

## General Specifications

|   |          |
|---|----------|
| <b>Body Style, Connector A</b>            | Straight |
| <b>Body Style, Connector B</b>            | Straight |
| <b>Interface, Connector A</b>             | N Male   |
| <b>Interface, Connector B</b>             | N Male   |
| <b>Specification Sheet Revision Level</b> | A        |

## Dimensions

|                     |                  |
|---------------------|------------------|
| <b>Length</b>       | 27.432 m   90 ft |
| <b>Nominal Size</b> | 1/2 in           |

## Electrical Specifications

|  |                                    |
|--|------------------------------------|
| <b>3rd Order IMD Dynamic</b>             | -110 dBm                           |
| <b>3rd Order IMD Dynamic Test Method</b> | Two +43 dBm carriers per IEC 62037 |
| <b>DTF, Connector A</b>                  | -34 dB                             |
| <b>DTF, Connector B</b>                  | -34 dB                             |

## VSWR/Return Loss

| Frequency Band | VSWR | Return Loss (dB) |
|----------------|------|------------------|
| 800–960 MHz    | 1.25 | 19.08            |
| 1700–2200 MHz  | 1.25 | 19.08            |
| 2500–2700 MHz  | 1.25 | 19.08            |

# H4-NMNM-90-P

---

## Environmental Specifications

### **Immersion Test Method**

Meets IEC 60529:2001, IP68 in mated condition

## Regulatory Compliance/Certifications

### **Agency**

ISO 9001:2015

### **Classification**

Designed, manufactured and/or distributed under this quality management system

