# **ULVSCSCCG**

#### **Base Product**



Ultra Low Loss ULL LazrSPEED® 550 OM5 SC/UPC to SC/UPC Ruggedized fanout Cable, 36-Fiber, Plenum, 12 fiber PmP 2.0 mm Dca

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | Europe | Latin America | Middle

East/Africa | North America

Portfolio CommScope®

Product Type Ruggedized fanout

Product Brand SYSTIMAX ULL

Ordering Note For additional jacket colors, please contact a CommScope Sales

Representative | For lengths greater than 999 ft (304 m), orders must be in meters | Minimum length may vary based on cable configuration

### General Specifications

Color, boot A Blue

Color, connector A Black

Color, boot B Blue

Color, connector B Black

Construction Type Stranded

Furcation Color Lime green

Interface, Connector A SC/UPC

Interface, Connector B SC/UPC

Interface Feature, connector B ULL

Jacket Color Lime green

Fibers per Subunit, quantity 12

Total Fibers, quantity 36

#### Dimensions


Cable Assembly Length Range (m) 3 - 305

Cable Assembly Length Range (ft) 10 - 999

**COMMSCOPE®** 

## ULVSCSCCG

### Ordering Tree



### **Optical Specifications**

**Fiber Mode** Multimode

Fiber Type OM5, LazrSPEED®

### **Environmental Specifications**

Operating Temperature -10 °C to +60 °C (+14 °F to +140 °F)

EN50575 CPR Cable EuroClass Fire Performance Dca

Environmental Space Indoor | Plenum

## Regulatory Compliance/Certifications

Agency	Classification
ANATEL	Compliant
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

Page 2 of 6



# ULVSCSCCG

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant

UK-ROHS Compliant



### Included Products

760242117 – Fiber indoor cable, LazrSPEED® Plenum MPO Trunk, 36 fiber multi-unit with 12 fiber subunits, P-036-MP-5G-F12LM/20T Multimode OM5, Gel-free, Feet jacket marking, Lime green jacket color



# 760242117 | P-036-MP-5G-F12LM/20T



Fiber indoor cable, LazrSPEED® Plenum MPO Trunk, 36 fiber multi-unit with 12 fiber subunits, Multimode OM5, Gel-free, Feet jacket marking, Lime green jacket color

### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | Latin America | Middle East

/Africa | North America

 Portfolio
 CommScope®

 Product Type
 Fiber indoor cable

Product Series P-MP

General Specifications

Cable Type MPO trunk cable

Construction Type Non-armored

**Subunit Type** Gel-free

Filler, quantity 1

Jacket Color Lime green

Jacket Marking Feet

Subunit, quantity 3

Fibers per Subunit, quantity 12

Total Fiber Count 36


**Dimensions** 

Buffer Tube/Subunit Diameter2 mm | 0.079 inDiameter Over Jacket7.7 mm | 0.303 in

Representative Image



## 760242117 | P-036-MP-5G-F12LM/20T



### Mechanical Specifications

Minimum Bend Radius, loaded 116 mm | 4.567 in

Minimum Bend Radius, unloaded 77 mm | 3.031 in

Tensile Load, long term, maximum 200 N | 44.962 lbf

**Tensile Load, short term, maximum** 667 N | 149.948 lbf

**Compression** 10 N/mm | 57.101 lb/in

Compression Test Method FOTP-41 | IEC 60794-1 E3

Flex 300 cycles

Flex Test Method FOTP-104 | IEC 60794-1 E6

**Impact** 0.74 N-m | 6.55 in lb

Impact Test Method FOTP-25 | IEC 60794-1 E4

**Strain** See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

**Vertical Rise, maximum** 320 m | 1,049.869 ft

**Optical Specifications** 

Fiber Type OM5, LazrSPEED® wideband | OM5, LazrSPEED® wideband

### **Environmental Specifications**

Installation temperature  $0 \,^{\circ}\text{C to} + 70 \,^{\circ}\text{C (+32 °F to} + 158 \,^{\circ}\text{F)}$ Operating Temperature  $0 \,^{\circ}\text{C to} + 70 \,^{\circ}\text{C (+32 °F to} + 158 \,^{\circ}\text{F)}$ 

Page 5 of 6



## 760242117 | P-036-MP-5G-F12LM/20T

Storage Temperature  $-40 \,^{\circ}\text{C}$  to  $+70 \,^{\circ}\text{C}$  ( $-40 \,^{\circ}\text{F}$  to  $+158 \,^{\circ}\text{F}$ )

Cable Qualification Standards ANSI/ICEA S-83-596 | Telcordia GR-409

Environmental Space Plenum

Flame Test Listing NEC OFNP (ETL) and c(ETL)

Flame Test Method NFPA 130 | NFPA 262

**Environmental Test Specifications** 

**Heat Age** 0 °C to +85 °C (+32 °F to +185 °F)

Heat Age Test Method IEC 60794-1 F9

**Low High Bend** 0 °C to +70 °C (+32 °F to +158 °F)

**Low High Bend Test Method** FOTP-37 | IEC 60794-1 E11

**Temperature Cycle**  $0 \,^{\circ}\text{C to } +70 \,^{\circ}\text{C (+32 °F to } +158 \,^{\circ}\text{F)}$ 

**Temperature Cycle Test Method** FOTP-3 | IEC 60794-1 F1

Packaging and Weights

Cable weight 64 kg/km | 43.006 lb/kft

### Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

### \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable

