



Sigma-Link™ Universal Connectivity Platform Q-Fit Patch Cord, cassette-cassette with POF, class EA, 2 m

- Sigma-Link is a pre-terminated factory-tested copper system for networking infrastructures and guarantees a 100% throughput performance
- Sigma-Link cable assemblies are offered in Housing-to-Housing, Housing-to-Jacks, Housing-to-Plugs and Housing to stub tail configurations
- Ranging from Category 6 to Category 7A, Sigma-Link supports up to 10GbE (10 Gigabit Ethernet) transmission and beyond
- Housing-to-Housing version features integrated Plastic Optical Fiber (POF) for easy tracing of far end

OBSOLETE

This product was discontinued on: **September 1, 2016**

Replaced By:

2153400-2

Sigma-Link™ Universal Connectivity Platform Q-Fit Cable Assembly, STP, class EA, H to H, POF, 2 m

Product Classification

| | |
|------------------------------|---|
| Regional Availability | Asia Australia/New Zealand EMEA Latin America |
| Portfolio | NETCONNECT® |
| Product Type | Copper trunk cable assembly |
| Product Brand | Sigma-Link™ |
| Product Series | Sigma-Link UCP |

General Specifications

| | |
|---------------------------------------|-------------------------------|
| ANSI/TIA Category | 6A |
| Cable Type | S/FTP (shielded) |
| Conductor Type | Solid |
| Interface, Connector A | Information outlet |
| Interface Feature, connector A | Single row Standard density |
| Interface, Connector B | Information outlet |
| Interface Feature, connector B | Single row Standard density |
| Jacket Color | White |
| Link Count | 6 |

2153146-2

Transmission Standards ISO/IEC 11801 Class EA

Dimensions

Cord Length 2 m | 6.562 ft

Material Specifications

Conductor Material Bare copper

Environmental Specifications

Operating Temperature -10 °C to +60 °C (+14 °F to +140 °F)

Storage Temperature -20 °C to +80 °C (-4 °F to +176 °F)

Environmental Space Low Smoke Fire Retardant Zero Halogen (LSFRZH)

Packaging and Weights

Packaging quantity 1