

F4-DMDM-12M-SGW-D



D-CLASS HELIAX® 1/2" SureFlex® Jumper with interface types 7-16 DIN Male and 7-16 DIN Male with HELIAX® SureGuard weatherproofing, 12 m

- If there are threads along the entire device port length, the HELIAX® SureGuard weatherproofing solutions will only seal properly if the HSG-M29-ADPT adapter is installed on the device port

Product Classification

Product Type SureFlex® D-CLASS, dynamic PIM

General Specifications

Body Style, Connector A Straight
Body Style, Connector B Straight
Interface, Connector A 7-16 DIN Male
Interface, Connector B 7-16 DIN Male
Specification Sheet Revision Level A

Dimensions

Length 12 m | 39.37 ft
Nominal Size 1/2 in

Electrical Specifications

3rd Order IMD Dynamic -116 dBm
3rd Order IMD Dynamic Test Method Two +43 dBm carriers per IEC 62037
DTF, Connector A -34 dB
DTF, Connector B -34 dB

Logo Image

F4-DMDM-12M-SGW-D



VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
698-960 MHz	1.101	26.36
1700-2200 MHz	1.101	26.36
2200-2700 MHz	1.135	23.98
3400-3800 MHz	1.222	20.01

Jumper Assembly Sample Label

Batch Manufacturing Date (two digit year and week)

Manufacturing Plant Product Revision

0123456789 US22 1240 /A

COMMSCOPE® Andrew Solutions™

F4-DMDM-2M-D — Part Number

2 M (6.562 FT)
SUREFLEX ASSEMBLY
U.S. PATENT 5802710

Product of UNITED STATES 12US220001242 — Serial Number



F4-DMDM-12M-SGW-D

Environmental Specifications

Immersion Test Method Meets IEC 60529:2001, IP68 in mated condition

Weatherproofing Method HELIAX® SureGuard weatherproofing boot

Packaging and Weights

Included Weatherproofing boot

Regulatory Compliance/Certifications

Agency

ISO 9001:2015

Classification

Designed, manufactured and/or distributed under this quality management system

