

# F4S-HPNMNM-M25

---

RSJ4-50 SureFlex® Jumper with interface types N Male and N Male,  
0.25m



## Product Classification

|                       |                               |
|-----------------------|-------------------------------|
| <b>Product Type</b>   | SureFlex® Premium, static PIM |
| <b>Product Series</b> | RSJ4-50                       |

## General Specifications

|   |          |
|---|----------|
| <b>Body Style, Connector A</b>            | Straight |
| <b>Body Style, Connector B</b>            | Straight |
| <b>Interface, Connector A</b>             | N Male   |
| <b>Interface, Connector B</b>             | N Male   |
| <b>Specification Sheet Revision Level</b> | A        |

## Dimensions

|                     |                  |
|---------------------|------------------|
| <b>Length</b>       | 0.25 m   0.82 ft |
| <b>Nominal Size</b> | 1/2 in           |

## Electrical Specifications

|   |                      |
|---|----------------------|
| <b>3rd Order IMD Static</b>             | -112 dBm             |
| <b>3rd Order IMD Static Test Method</b> | Two +43 dBm carriers |
| <b>DTF, Connector A</b>                 | 34 dB                |
| <b>DTF, Connector B</b>                 | 34 dB                |

## VSWR/Return Loss

| Frequency Band | VSWR  | Return Loss (dB) |
|----------------|-------|------------------|
| 698–960 MHz    | 1.065 | 30.04            |
| 1700–2200 MHz  | 1.065 | 30.04            |
| 2200–2700 MHz  | 1.106 | 25.96            |

# F4S-HPNMNM-M25

## Jumper Assembly Sample Label



## Environmental Specifications

**Immersion Test Method** Meets IEC 60529:2001, IP68 in mated condition

## Regulatory Compliance/Certifications

| Agency        | Classification   |
|---------------|--|
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |



## Included Products

|         |   |   |
|---------|---|---|
| RSJ4-50 | - | RSJ4-50, HELIAX® Superflexible Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket |
|---------|---|---|