

# F2A-PDFDR-5

---

FSJ2-50 SureFlex® Jumper with interface types 7-16 DIN Female and 7-16 DIN Male Right Angle, 1.52 m



## Product Classification

|                       |                    |
|-----------------------|--------------------|
| <b>Product Type</b>   | SureFlex® standard |
| <b>Product Series</b> | FSJ2-50            |

## General Specifications

|   |                 |
|---|-----------------|
| <b>Body Style, Connector A</b>            | Bulkhead        |
| <b>Body Style, Connector B</b>            | Right angle     |
| <b>Interface, Connector A</b>             | 7-16 DIN Female |
| <b>Interface, Connector B</b>             | 7-16 DIN Male   |
| <b>Orientation</b>                        | 0°              |
| <b>Specification Sheet Revision Level</b> | A               |

## Dimensions

|                     |                   |
|---------------------|-------------------|
| <b>Length</b>       | 1.52 m   4.987 ft |
| <b>Nominal Size</b> | 3/8 in            |

## VSWR/Return Loss

| Frequency Band | VSWR | Return Loss (dB) |
|----------------|------|------------------|
| 700–3000 MHz   | 1.29 | 18               |

## Jumper Assembly Sample Label

# F2A-PDFDR-5



## Environmental Specifications

**Immersion Test Method** Meets IEC 60529:2001, IP68 in mated condition

## Regulatory Compliance/Certifications

| Agency        | Classification   |
|---------------|--|
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |



## Included Products

- |          |  |
|----------|--|
| 35422-42 | - Heat Treated FSJ2-50, HELIAX® Superflexible Foam Coaxial Cable, corrugated copper, 3/8 in, black PE jacket |
| FSJ2-50  | - FSJ2-50, HELIAX® Superflexible Foam Coaxial Cable, corrugated copper, 3/8 in, black PE jacket              |