
FNZLCLCAG

Base Product



OM3 LC/UPC to LC/UPC 36-Fiber InstaPATCH® 360 Ruggedized Fanout Cable, Low Smoke Zero Halogen

Product Classification

Regional Availability

Asia | Australia/New Zealand | China | Europe | India | Latin

America | Middle East/Africa | North America

Portfolio CommScope®

Product Type Ruggedized fanout

Product Brand SYSTIMAX InstaPATCH® 360

Ordering Note For lengths greater than 999 ft (304 m), orders must be in meters | Minimum length

may vary based on cable configuration | Not available in the United States or Canada

General Specifications

Color, boot AAquaColor, connector ABlackColor, boot BAquaColor, connector BBlackConstruction TypeStrandedFurcation ColorAqua

Interface, Connector A LC/UPC
Interface, Connector B LC/UPC

Jacket Color Aqua
Fibers per Subunit, quantity 12

Total Fibers, quantity 36


Dimensions

Cable Assembly Length Range (m)3 - 305Cable Assembly Length Range (ft)7 - 999

Ordering Tree



FNZLCLCAG



Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0 ° | 4.40 lb @ 90 °

Optical Specifications

Fiber Mode Multimode

Fiber Type OM3, LazrSPEED®

Environmental Specifications

Operating Temperature $-10 \,^{\circ}\text{C to } +60 \,^{\circ}\text{C (+14 }^{\circ}\text{F to } +140 \,^{\circ}\text{F)}$

Environmental Space Dual Rated LSZH/Riser | Indoor

Regulatory Compliance/Certifications

Agency	Classification
ANATEL	Compliant
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

Page 2 of 8



FNZLCLCAG



Included Products


760118372 N-036-MP-5L-F12AQ/D Fiber indoor cable, LazrSPEED® Low Smoke Zero Halogen Riser MPO Trunk, 36 fiber multi-unit with 12 fiber subunits, Gel-free, Multimode OM3, Feet jacket marking, Aqua jacket color, Dca flame rating

860637378

- LazrSPEED® Elite LC Connector duplex for 1.6 mm Fiber, multimode



760118372 | N-036-MP-5L-F12AQ/D



Fiber indoor cable, LazrSPEED® Low Smoke Zero Halogen Riser MPO Trunk, 36 fiber multi-unit with 12 fiber subunits, Gel-free, Multimode OM3, Feet jacket marking, Aqua jacket color, Dca flame rating

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North

America

 Portfolio
 CommScope®

 Product Type
 Fiber indoor cable

Product Series N-MP

General Specifications

Cable Type MPO trunk cable

Construction Type Non-armored

Subunit Type Gel-free

Jacket Color Aqua

Jacket Marking Feet

Subunit, quantity 3

Fibers per Subunit, quantity 12

Total Fiber Count 36

Dimensions

Buffer Tube/Subunit Diameter 3 mm | 0.118 in

Diameter Over Jacket 9.2 mm | 0.362 in

Representative Image



760118372 | N-036-MP-5L-F12AQ/D



Mechanical Specifications

Minimum Bend Radius, loaded 138 mm | 5.433 in

Minimum Bend Radius, unloaded 92 mm | 3.622 in

Tensile Load, long term, maximum 400 N | 89.924 lbf

Tensile Load, short term, maximum 1335 N | 300.12 lbf

Compression 10 N/mm | 57.101 lb/in

Compression Test Method FOTP-41 | IEC 60794-1 E3

Flex 300 cycles

FIEX Test Method FOTP-104 | IEC 60794-1 E6

Impact 5.88 N-m | 52.042 in lb

Impact Test Method FOTP-25 | IEC 60794-1 E4

Strain See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

Vertical Rise, maximum 500 m | 1,640.42 ft

Optical Specifications

Fiber Type OM3, LazrSPEED® 300 | OM3, LazrSPEED® 300

Environmental Specifications

Installation temperature $-20 \,^{\circ}\text{C}$ to $+60 \,^{\circ}\text{C}$ (-4 °F to +140 °F)

Operating Temperature $-20 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ (-4 °F to +158 °F)

Storage Temperature $-40 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ (-40 °F to +158 °F)

Page 5 of 8



760118372 | N-036-MP-5L-F12AQ/D

Cable Qualification Standards ANSI/ICEA S-83-596 | Telcordia GR-409

EN50575 CPR Cable EuroClass Fire PerformanceDcaEN50575 CPR Cable EuroClass Smoke Ratings2EN50575 CPR Cable EuroClass Droplets Ratingd1EN50575 CPR Cable EuroClass Acidity Ratinga1

Environmental Space Low Smoke Zero Halogen (LSZH) | Riser

Flame Test Listing NEC OFNR-ST1 (ETL) and c(ETL)

Flame Test Method | IEC 60332-3 | IEC 60754-2 | IEC 61034-2 | UL 1666 | UL 1685

Environmental Test Specifications

Heat Age $-20 \,^{\circ}\text{C}$ to $+85 \,^{\circ}\text{C}$ $(-4 \,^{\circ}\text{F}$ to $+185 \,^{\circ}\text{F})$

Heat Age Test Method IEC 60794-1 F9

Low High Bend $-20 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ (-4 °F to +158 °F)Low High Bend Test MethodFOTP-37 | IEC 60794-1 E11Temperature Cycle $-20 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ (-4 °F to +158 °F)

Temperature Cycle Test Method FOTP-3 | IEC 60794-1 F1

Packaging and Weights

Cable weight 71.1 kg/km | 47.777 lb/kft

Regulatory Compliance/Certifications

Agency Classification

CENELEC EN 50575 compliant, Declaration of Performance (DoP) available

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

CENELEC

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable



860637378

LazrSPEED® Elite LC Connector duplex for 1.6 mm Fiber, multimode

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

PortfolioCommScope®Product TypeFiber connectorProduct BrandLazrSPEED®

General Specifications

Body StyleDuplexColorBeige

Ferrule Geometry Pre-radiused

Interface LC/UPC

Dimensions

 Length
 50.3 mm | 1.98 in

 Compatible Cable Diameter
 1.6 mm | 0.063 in

Material Specifications

Ferrule Material Zirconia

Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0 °

Optical Specifications

Fiber Mode Multimode

Optical Components Standard ANSI/TIA-568-C.3

Insertion Loss, ULL, maximum0.15 dBReturn Loss, minimum35 dB

Packaging and Weights

Packaging quantity 2

Regulatory Compliance/Certifications



860637378

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

