5NPX1006F



10-port multibeam antenna, 10x 1710–2180 MHz, 5x 10-14° HPBW, fixed electrical tilt

This product will be discontinued on: December 31, 2025

Replaced By:

6V-10M-F6 12-port multibeam antenna, 12x 1695–2690 MHz, 6x 10-14° HPBW, fixed electrical tilt

6VV-10A-F6 24-port multibeam antenna, 24x 1695–2690 MHz, 6x 10-14° HPBW, fixed electrical tilt, 1.3m length

General Specifications

Antenna Type Multibeam

Band Single band

Color Light Gray (RAL 7035)

Grounding TypeRF connector inner conductor and body grounded to reflector and mounting bracket

Performance NoteOutdoor usageRadome MaterialASA, UV stabilized

Radiator Material Brass | Low loss circuit board

Reflector Material Aluminum

RF Connector Interface 7-16 DIN Female

RF Connector Location Bottom

RF Connector Quantity, high band 10
RF Connector Quantity, mid band 0
RF Connector Quantity, low band 0
RF Connector Quantity, total 10

Dimensions

 Width
 864 mm | 34.016 in

 Depth
 202 mm | 7.953 in

 Length
 889 mm | 35 in

 Net Weight, without mounting kit
 29.5 kg | 65.036 lb



Page 1 of 3

5NPX1006F

Electrical Specifications

Impedance 50 ohm

Operating Frequency Band 1710 – 2180 MHz

Polarization ±45°

Electrical Specifications

Frequency Band, MHz	1710-1920	1920-2180
Gain, dBi	21.7	22.3
Beamwidth, Horizontal, degrees	13	12
Beamwidth, Vertical, degrees	11.9	10.9
Beam Tilt, degrees	6	6
USLS (First Lobe), dB	14	16
Front-to-Back Ratio at 180°, dB	32	34
CPR at Boresight, dB	10	10
Isolation, Same Beam, dB	25	25
VSWR Return loss, dB	1.43 15.0	1.43 15.0
PIM, 3rd Order, 2 x 20 W, dBc	-150	-150
Input Power per Port, maximum, watts	300	300

Mechanical Specifications

Wind Loading @ Velocity, frontal 931.0 N @ 150 km/h (209.3 lbf @ 150 km/h)

Wind Speed, maximum 250 km/h (155 mph)

Packaging and Weights

 Width, packed
 977 mm | 38.465 in

 Depth, packed
 349 mm | 13.74 in

 Length, packed
 1038 mm | 40.866 in

 Weight, gross
 46.5 kg | 102.515 lb

Regulatory Compliance/Certifications

Agency	Classification
CE	Compliant with the relevant CE product directives
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



Page 2 of 3

5NPX1006F

REACH-SVHC Compliant as per SVHC revision on www.andrew.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



Included Products

T-045-GL-E – Adjustable Tilt Pipe Mounting Kit for 2.0"-4.5" (60-115mm) OD round members for panel antennas. Includes 2 clamp sets.

* Footnotes

Performance Note Severe environmental conditions may degrade optimum performance

