1-port omni antenna, 450–470 MHz, 360° HPBW, fixed electrical tilt

Invert mountable

General Specifications

Antenna Type Omni

Band Single band
Color Off-white

Grounding Type RF connector inner conductor and body grounded to reflector and mounting bracket

Performance Note Outdoor usage

Radome Material Fiberglass, UV resistant

Radiator MaterialBrassRF Connector InterfaceN FemaleRF Connector LocationBottom

RF Connector Quantity, high band 0

RF Connector Quantity, mid band 0

RF Connector Quantity, low band 1

RF Connector Quantity, total 1

Dimensions

 Length
 5588 mm | 220 in

 Net Weight, without mounting kit
 10 kg | 22.046 lb

 Outer Diameter
 76.2 mm | 3 in

Electrical Specifications

Impedance 50 ohm

Operating Frequency Band 450 – 470 MHz

Polarization Vertical

Electrical Specifications

Frequency Band, MHz 450-470



ASP705K

Gain, dBi 12.1

Beamwidth, Horizontal,

degrees

360

Beam Wilt, Vertical, degrees 7 **Beam Tilt, degrees** 0

VSWR | Return loss, dB 1.5 | 14.0 Input Power per Port, 500

maximum, watts

Mechanical Specifications

Wind Loading @ Velocity, maximum 364.8 N @ 100 mph (82.0 lbf @ 100 mph)

Wind Speed, maximum 201 km/h (125 mph)

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

Included Products

ASPR616 – Pipe Mounting Kit for 1.25 - 3.5 in (35 - 89.0 mm) OD round

members

* Footnotes

Performance Note Severe environmental conditions may degrade optimum performance

