

ATJB200-A01-004



Four-way Junction Box

- Divides data and power on main RET control cable up to 4-ways
- Equipped with a grounding stud for added lightning protection
- Easily mounts to a pole or wall
- AISG and RoHS compliant

OBSOLETE

This product was discontinued on: March 31, 2021

Product Classification

Product Type RET junction box

General Specifications

AISG Input Connector	8-pin DIN Male
AISG Input Connector Quantity	1
AISG Output Connector	8-pin DIN Female
AISG Output Connector Quantity	4
Color	Gray
EU Certification	CB CE Low Voltage Directive 73/23/EEC
Grounding Lug Thread Size	M8

Dimensions

Height	50.8 mm 2 in
Width	185.42 mm 7.3 in
Depth	157.48 mm 6.2 in

Electrical Specifications

Electrical Safety Standard	EN 60950 UL 60950
Electromagnetic Compatibility (EMC)	EN 55011 EN 61326-1 ETS 300 386 V1.3.2 2003
Interface Protocol Signal	Data dc
Lightning Surge Capability	10 times @ 600 A

ATJB200-A01-004

Lightning Surge Capability Test Method	IEC 61312-1 Annex B Current Pulse Profile
Lightning Surge Capability Waveform	10/350 waveform
Protocol	AISG 1.1 AISG 2.0

Material Specifications

Material Type	Aluminum Stainless steel
---------------	----------------------------

Environmental Specifications

Operating Temperature	-40 °C to +65 °C (-40 °F to +149 °F)
Relative Humidity	Up to 100%
Ingress Protection Test Method	IEC 60529:2001, IP65
Rain Simulation Test Method	IEC 60068-2-18, Test Condition Ra, Method 1
UV Resistance Test Method	IEC 60068-2-5, Test Condition B

Packaging and Weights

Included	Band clamp Carriage bolts Hex nuts Junction box Lock washers Pipe mount bracket Wall mount brackets
Weight, net	0.998 kg 2.2 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.andrew.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

