


L6600D-2



2-port Distribution Manifold, wall mountable, 0–5.0 psig, 25 ft of tubing per port

This product will be discontinued on: September 1, 2023

Product Classification

Product Type Manifold

General Specifications

Distribution System Manifold
Mounting Wall
Port Count 2
Port Type 3/8 in PE tube
Regulated Output Pressure, maximum 34.474 kPa | 5 psig
Regulated Output Pressure, minimum 0 kPa | 0 psig

Dimensions

Product Height 160.02 mm | 6.3 in
Product Width 236.22 mm | 9.3 in
Product Depth 88.9 mm | 3.5 in

Environmental Specifications

Operating Temperature +1 °C to +40 °C (+33 °F to +104 °F)

Packaging and Weights

Height, packed 406.4 mm | 16 in
Width, packed 177.8 mm | 7 in
Depth, packed 558.8 mm | 22 in
Included 3/8 in polyethylene tubing | 90° elbow fitting | Cable tie | Instruction sheet | Male connector fitting | PTFE tape

L6600D-2

Weight, gross 3.63 kg | 8.003 lb

Weight, net 3.63 kg | 8.003 lb

Regulatory Compliance/Certifications

Agency

CHINA-ROHS

ISO 9001:2015

REACH-SVHC

ROHS

UK-ROHS

Classification

Below maximum concentration value

Designed, manufactured and/or distributed under this quality management system

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

Compliant

Compliant

