URX2XLUHF

Base Product



Ultra Low Loss OM4 MPO24 Pinned to LC/UPC Uniboot 24-Fiber Low Smoke Zero Halogen/Riser Array Cord

Product Classification

Regional Availability

Asia | Australia/New Zealand | Europe | Latin America | Middle East

/Africa | North America

Portfolio CommScope®

Product Type Fiber array cable assembly

Product Brand SYSTIMAX ULL

Ordering Note For additional jacket colors, please contact a CommScope Sales Representative | For

lengths greater than 999 ft (304 m), orders must be in meters | Minimum length may

vary based on cable configuration

General Specifications

Color, boot ARedColor, connector AAquaColor, boot BAquaColor, connector BBeigeConstruction TypeStranded

Furcation Color Aqua

Interface, Connector A MPO-24/UPC Male

Interface, Connector BLC/UPCInterface Feature, connector BUnibootJacket ColorAqua

Polarity Method B Enhanced (ULL)

Fibers per Subunit, quantity 24

Total Fibers, quantity 24

Dimensions

Breakout Length 12 in | 24 in | 36 in | 48 in | 60 in | 72 in


COMMSCOPE®

URX2XLUHF

Cable Assembly Length Range (m) 1 - 304

Cable Assembly Length Range (ft) 2 - 999

Ordering Tree



Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0 ° | 4.40 lb @ 90 °

Optical Specifications

Fiber Mode Multimode

Fiber Type OM4, LazrSPEED®

Environmental Specifications

Operating Temperature $-10 \,^{\circ}\text{C}$ to $+60 \,^{\circ}\text{C}$ (+14 $^{\circ}\text{F}$ to +140 $^{\circ}\text{F}$)

Environmental Space Indoor | Low Smoke Zero Halogen (LSZH)

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

Included Products

760256685 – Fiber indoor cable, LazrSPEED® Low Smoke Zero Halogen Riser Light Duty for MPO
N-024-MP-5K-F30AQ/D Patchcords, 24 fiber, Multimode OM4, Gel-free, Feet jacket marking, Aqua jacket color, Dca

Page 2 of 3

URX2XLUHF

flame rating

860658161 – 2.0 mm LC/UPC Uniboot GEN 1.5, Aqua 860662278 – MPO24,MALE,OM3/4,AQUA,3.0MM

