## NNH4-65C-R6N17



12-port sector antenna, 4x 698–896 and 8x 1695–2360 MHz, 65° HPBW, 6x RET.

- Features broadband Low Band (698-896 MHz) and High Band (1695-2360 MHz) arrays for 4T4R (4X MIMO) capability for Band 14, AWS, PCS and WCS applications
- Independent tilt for all arrays
- Array configuration provides capability for 4T4R (4x MIMO) on Low band and Dual 4T4R (4x MIMO) on High band
- Optimized SPR performance across all operating bands
- Excellent wind loading characteristics
- Supports re-configurable antenna sharing capability enabling control of the internal RET system using up to two separate RET compatible OEM radios
- The antenna is supplied with mounting kits that provide 0 degree of mechanical downtilt; optional downtilt mounting kits are available

#### General Specifications

Antenna Type Sector

Band Multiband

**Grounding Type**RF connector inner conductor and body grounded to reflector and

mounting bracket

Performance Note Outdoor usage

Radome Material Fiberglass, UV resistant

Radiator Material Low loss circuit board

Reflector Material Aluminum

**RF Connector Interface** 4.3-10 Female

**RF Connector Location** Bottom

RF Connector Quantity, high band 8
RF Connector Quantity, mid band 0
RF Connector Quantity, low band 4
RF Connector Quantity, total 12

#### Remote Electrical Tilt (RET) Information

**RET Hardware** CommRET v2

RET Interface 8-pin DIN Female | 8-pin DIN Male

**RET Interface, quantity** 2 female | 2 male

Input Voltage 10-30 Vdc

ANDREW® an Amphenol company

Page 1 of 6

# NNH4-65C-R6N17

Internal RET High band (4) | Low band (2)

Power Consumption, idle state, maximum 1 W

Power Consumption, normal conditions, maximum 8 W

**Protocol** 3GPP/AISG 2.0 (Multi-RET)

**Dimensions** 


 Width
 430 mm | 16.929 in

 Depth
 197 mm | 7.756 in

 Length
 2438 mm | 95.984 in

 Net Weight, without mounting kit
 42.2 kg | 93.035 lb

#### Array Layout



Array	Freq (MHz)	Conns	RET (MRET)	AISG RET UID
R1	698-896	1-2	1	CPxxxxxxxxxxxxxxxxmm.1
R2	698-896	3-4	2	CPxxxxxxxxxxxxxxxxmm.2
Y1	1695-2360	5-6	3	CPxxxxxxxxxxxxxxxmm.3
Y2	1695-2360	7-8	4	CPxxxxxxxxxxxxxxxmm.4
Y3	1695-2360	9-10	5	CPxxxxxxxxxxxxxxxmm.5
Y4	1695-2360	11-12	6	CPxxxxxxxxxxxxxxxmm.6

(Sizes of colored boxes are not true depictions of array sizes)

## Port Configuration



## **Electrical Specifications**

**Impedance** 50 ohm

**Operating Frequency Band** 1695 – 2360 MHz | 698 – 896 MHz

Polarization ±45°

**Total Input Power, maximum** 900 W @ 50 °C

## **Electrical Specifications**

· •						
Frequency Band, MHz	698-806	806-896	1695-1880	1850-1990	1920-2180	2300-2360
Gain, dBi	14.9	15.7	16.4	17.2	17.6	17.7
Beamwidth, Horizontal, degrees	59	55	65	64	62	63
Beamwidth, Vertical, degrees	9.7	8.5	8	7.4	7	6.2
Beam Tilt, degrees	2-12	2-12	2-12	2-12	2-12	2-12
USLS (First Lobe), dB	18	19	16	16	18	22
Front-to-Back Ratio at 180°, dB	29	29	32	34	34	32
Isolation, Cross Polarization, dB	25	25	25	25	25	25
Isolation, Inter-band, dB	25	25	25	25	25	25
VSWR   Return loss, dB	1.5   14.0	1.5   14.0	1.5   14.0	1.5   14.0	1.5   14.0	1.5   14.0

Page 3 of 6



## NNH4-65C-R6N17

PIM, 3rd Order, 2 x 20 W, dBc	-150	-150	-150	-150	-150	-150
Input Power per Port at 50°C,	300	300	250	250	250	200
maximum, watts						

### Mechanical Specifications

Effective Projective Area (EPA), frontal $0.61 \text{ m}^2 + 6.566 \text{ ft}^2$ Effective Projective Area (EPA), lateral $0.32 \text{ m}^2 + 3.444 \text{ ft}^2$ 

Mechanical Tilt Range 0°-12°

 Wind Loading @ Velocity, frontal
 651.0 N @ 150 km/h (146.4 lbf @ 150 km/h)

 Wind Loading @ Velocity, lateral
 339.0 N @ 150 km/h (76.2 lbf @ 150 km/h)

 Wind Loading @ Velocity, maximum
 1,052.0 N @ 150 km/h (236.5 lbf @ 150 km/h)

 Wind Loading @ Velocity, rear
 1,182.0 N @ 150 km/h (265.7 lbf @ 150 km/h)

Wind Speed, maximum 241 km/h (150 mph)

#### Packaging and Weights

 Width, packed
 530 mm | 20.866 in

 Depth, packed
 349 mm | 13.74 in

 Length, packed
 2620 mm | 103.15 in

 Weight, gross
 55.2 kg | 121.695 lb

#### Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant
UK-ROHS	Compliant



#### Included Products

BSAMNT-3F – Mounting bracket for cylindrical pipe installations (60-115mm pipe diameter) for fix mechanical tilt applications.

#### \* Footnotes

**Performance Note** Severe environmental conditions may degrade optimum performance



# BSAMNT-3F



Mounting bracket for cylindrical pipe installations (60-115mm pipe diameter) for fix mechanical tilt applications.

#### Product Classification

**Product Type** Fixed tilt mounting kit

General Specifications

ApplicationOutdoorColorSilver

**Dimensions** 

Compatible Diameter, maximum115 mm | 4.528 inCompatible Diameter, minimum60 mm | 2.362 inWeight, net5.6 kg | 12.346 lb

Material Specifications

Material Type Galvanized steel

#### Packaging and Weights

Included Brackets | Hardware

Packaging quantity 1

**Weight, gross** 5.8 kg | 12.787 lb

### Regulatory Compliance/Certifications

Agency	Classification
CE	Compliant with the relevant CE product directives
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.andrew.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



Page 5 of 6

