### RRV4-65D-R6-V3



# 12-port sector antenna, 4x 694–960 and 8x 1695–2690 MHz, 65° HPBW, 6x RET

- All Internal RET actuators are connected in "Cascaded SRET" configuration
- Supports re-configurable antenna sharing capability enabling control of the internal RET system using up to two separate RET compatible OEM radios
- Site sharing preset: R1, Y1, Y3 assigned to AISG2 / R2, Y2, Y4 assigned to AISG1

This product will be discontinued on: December 31, 2025

#### General Specifications

Antenna Type	Sector
Band	Multiband
Grounding Type	RF connector inner conductor and body grounded to reflector and mounting bracket
Performance Note	Outdoor usage
Radome Material	Fiberglass, UV resistant
Radiator Material	Aluminum   Low loss circuit board
Reflector Material	Aluminum
RF Connector Interface	4.3-10 Female
RF Connector Location	Bottom
RF Connector Quantity, high band	8
RF Connector Quantity, mid band	0
RF Connector Quantity, low band	4
RF Connector Quantity, total	12

#### Remote Electrical Tilt (RET) Information

RET Hardware	CommRET v2
RET Interface	8-pin DIN Female   8-pin DIN Male
RET Interface, quantity	2 female   2 male
Input Voltage	10-30 Vdc
Internal RET	High band (4)   Low band (2)
Power Consumption, idle state, maximum	1 W

Page 1 of 6



©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: May 6, 2025

### RRV4-65D-R6-V3

Power Consumption, normal conditions, maximum	8 W
Protocol	3GPP/AISG 2.0 (Single RET)
Dimensions	
Width	498 mm   19.606 in
Depth	197 mm   7.756 in
Length	2688 mm   105.827 in
Net Weight, without mounting kit	48 kg   105.822 lb

### Array Layout

Y2	Y4
Y1	Y3
R1	R2
Left	Right

Array	Freq (MHz)	Conns	RET (SRET)	AISG RET UID
R1	694-960	1-2	1	CPxxxxxxxxxxxxR1
R2	694-960	3-4	2	CPxxxxxxxxxxxxxR2
Y1	1695-2690	5-6	3	CPxxxxxxxxxxxxxXXXXXXXXY1
Y2	1695-2690	7-8	4	CPxxxxxxxxxxxxxXXXXXY2
Y3	1695-2690	9-10	5	CPxxxxxxxxxxxxxXXXXXXXXXXXXXXXXXXXXXXXX
¥4	1695-2690	11-12	6	CPxxxxxxxxxxxxxXY4

Left Right Bottom

(Sizes of colored boxes are not true depictions of array sizes)

### Port Configuration



©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: May 6, 2025



### Electrical Specifications

Impedance	50 ohm
Operating Frequency Band	1695 – 2690 MHz   694 – 960 MHz
Polarization	±45°
Total Input Power, maximum	900 W @ 50 °C

### **Electrical Specifications**

Frequency Band, MHz	694-790	790-890	890-960	1695-188	0 1850–199	0 1920–218	0 2300–250	0 2500-2690
Gain, dBi	16.2	16.7	16.8	17.3	17.8	18.1	18.3	18
Beamwidth, Horizontal, degrees	71	65	61	60	55	57	63	69
Beamwidth, Vertical, degrees	8.4	7.5	6.9	7.6	7	6.6	5.7	5.4
Beam Tilt, degrees	2-12	2-12	2-12	2-12	2-12	2-12	2-12	2-12
USLS (First Lobe), dB	13	15	15	19	19	19	17	15
Front-to-Back Ratio at 180°, dB	33	32	34	35	37	37	34	31
Isolation, Cross Polarization, dB	28	28	28	28	28	28	28	28
Isolation, Inter-band, dB	28	28	28	28	28	28	28	28
VSWR   Return loss, dB	1.5   14.0	1.5   14.0	1.5   14.0	1.5   14.0	1.5   14.0	1.5   14.0	1.5   14.0	1.5   14.0

Page 3 of 6



©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: May 6, 2025

## RRV4-65D-R6-V3

PIM, 3rd Order, 2 x 20 W, dBc Input Power per Port at 50°C, maximum, watts	-150 300	-150 300	-150 300	-150 250	-150 250	-150 250	-150 250	-150 200	
Mechanical Specifica	itions								
Effective Projective Area (EPA),	frontal		1 m²	10.764 ft	2				
Effective Projective Area (EPA),	lateral		0.35	0.35 m²   3.767 ft²					
Mechanical Tilt Range				0°-12°					
Wind Loading @ Velocity, frontal				1,070.0 N @ 150 km/h (240.5 lbf @ 150 km/h)					
Wind Loading @ Velocity, lateral				375.0 N @ 150 km/h (84.3 lbf @ 150 km/h)					
Wind Loading @ Velocity, maximum				1,385.0 N @ 150 km/h (311.4 lbf @ 150 km/h)					
Wind Loading @ Velocity, rear				880.0 N @ 150 km/h (197.8 lbf @ 150 km/h)					
Wind Speed, maximum			241	m/h (150 m	ph)				

### Packaging and Weights

Width, packed	565 mm   22.244 in
Depth, packed	309 mm   12.165 in
Length, packed	2935 mm   115.551 in
Weight, gross	68.9 kg   151.898 lb

#### Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted



#### Included Products

BSAMNT-4	-	Wide Profile Antenna Downtilt Mounting Kit for 2.4 - 4.5 in (60 - 115 mm) OD round members. Kit contains one scissor top bracket set and one bottom bracket set.
BSAMNT-M4	-	Middle Downtilt Mounting Kit for Long Antennas for 2.4 - 4.5 in (60 - 115 mm) OD round members. Kit contains one scissor bracket set.

### \* Footnotes

**Performance Note** 

Severe environmental conditions may degrade optimum performance

Page 4 of 6



©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: May 6, 2025

### BSAMNT-4



Wide Profile Antenna Downtilt Mounting Kit for 2.4 - 4.5 in (60 - 115 mm) OD round members. Kit contains one scissor top bracket set and one bottom bracket set.

Product Classification	
Product Type	Downtilt mounting kit
General Specifications	
Application	Outdoor
Color	Silver
Dimensions	
Compatible Diameter, maximum	115 mm   4.528 in
Compatible Diameter, minimum	60 mm   2.362 in
Weight, net	6.5 kg   14.33 lb
Material Specifications	
Material Type	Galvanized steel
Packaging and Weights	
Included	Brackets   Hardware
Packaging quantity	1
Regulatory Compliance/	Certifications

Agency	Classification	
CHINA-ROHS	Below maximum concentration value	
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system	
REACH-SVHC	Compliant as per SVHC revision on www.andrew.com/ProductCompliance	
ROHS	Compliant	
UK-ROHS	Compliant	



Page 5 of 6



©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 2, 2025

## BSAMNT-M4



Middle Downtilt Mounting Kit for Long Antennas for 2.4 - 4.5 in (60 - 115 mm) OD round members. Kit contains one scissor bracket set.

Product Classification		
Product Type	Downtilt mounting kit	
General Specifications		
Application	Outdoor	
Color	Silver	
Dimensions		
Compatible Diameter, maximum	115 mm   4.528 in	
Compatible Diameter, minimum	60 mm   2.362 in	
Weight, net	4.6 kg   10.141 lb	
Material Specifications		
Material Type	Galvanized steel	
Packaging and Weights		
Included	Brackets   Hardware	
Packaging quantity	1	
Dogulatory Compliance /Cortifications		

#### Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.andrew.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



Page 6 of 6



©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 2, 2025